




CRYSTEK
CRYSTALS
A DIVISION OF CRYSTEK CORPORATION

CCHD-950 Model
9×14 mm SMD, 3.3V, HCMOS




CCHD-950 Ultra-Low Phase Noise Oscillator


50 MHz HCMOS 3.3V




80 MHz HCMOS 3.3V



100 MHz HCMOS 3.3V



130 MHz HCMOS 3.3V



Model CCHD-950 is a 45 MHz to 130 MHz HCMOS Clock Oscillator. High Q crystal and 3rd overtone technology provides Ultra-Low Phase Noise and Low-Jitter performance with an HCMOS output. Features include -165 dBc/Hz phase noise floor with 3.3 Vdc input voltage, -40°C to +85°C operating temperature, and 9×14 mm SMT package. The oscillator has no sub-harmonics.

Applications include High Definition TV, Avionics
Low Phase Signal Sources, and Test and Measurement.

Rev: P
Date: 19-Sep-2017
Page 1 of 2



16850 ORIOLE ROAD • FORT MYERS, FLORIDA 33912
PHONE: 239-561-3311 • 800-237-3061
WWW.CRYSTEK.COM

CCHD-950

Ultra-Low Phase Noise Oscillator



CCHD-950 Model



9x14 mm SMD, 3.3V, HCMOS

Frequency Range: 45 MHz to 130 MHz
Temperature Range: 0°C to +70°C
 (Option M) -20°C to +70°C
 (Option X) -40°C to +85°C
Storage: -45°C to 90°C
Input Voltage: 3.3V ±0.3V
Input Current: 15mA Typical, 25mA Max
Output: HCMOS
 Symmetry: 45/55% Max @ 50% Vdd
 Rise/Fall Time: 3ns Max @ 20% to 80% Vdd
 Logic: "0" = 10% Vdd Max
 "1" = 90% Vdd Min
 Load: 15pF
 Output Current: ±24mA Max
Phase Jitter (12kHz~20MHz): 40 fs Typical @ 100MHz
Phase Noise Typical: See plots
Phase Noise Floor: -165 dBc/Hz Typical, -160 dBc/Hz Max
Sub-harmonics: None
Aging: <3ppm 1st year, <1ppm thereafter

CCHD-950 Options:
Temperature Range: 0°C to +70°C (±20ppm, ±25ppm, ±50ppm)
 -20°C to +70°C (±25ppm, ±50ppm)
 -40°C to +85°C (±25ppm, ±50ppm)

Part Number Example:
 CCHD-950X-25-100.000 = 3.3V, 45/55, -40°C to +85°C (±25ppm), 100 MHz



Mechanical:	
Shock:	MIL-STD-883, Method 2002, Condition B
Solderability:	MIL-STD-883, Method 2003
Vibration:	MIL-STD-883, Method 2007, Condition A
Solvent Resistance:	MIL-STD-202, Method 215
Resistance to Soldering Heat:	MIL-STD-202, Method 210, Condition I or J
Environmental:	
Thermal Shock:	MIL-STD-883, Method 1011, Condition A
Moisture Resistance:	MIL-STD-883, Method 1004



RECOMMENDED REFLOW SOLDERING PROFILE

900034 (See App Note listed on website)
<http://www.crystek.com/specification/reflow/900034.pdf>

SUGGESTED PAD LAYOUT



Pad	Connection
1	NC
2	GND
3	OUT
4	Vdd

PAD FINISH: Immersion Gold (ENIG); 5 micro inches maximum

Crystek Corporation reserves the right to make changes to its products and/or information contained herein without notice.
 No liability is assumed as a result of its use or application.

Rev: P
 Date: 19-Sep-2017
 Page 2 of 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Crystek:

<u>CCHD-950-25-70.000</u>	<u>CCHD-950-25-54.000</u>	<u>CCHD-950-25-60.000</u>	<u>CCHD-950-25-74.1758</u>	<u>CCHD-950-25-74.250</u>
<u>CCHD-950-25-100.000</u>	<u>CCHD-950-25-80.000</u>	<u>CCHD-950-50-100.000</u>	<u>CCHD-950-50-80.000</u>	<u>CCHD-950X-25-100.000</u>
<u>CCHD-950-50-65.000</u>	<u>CCHD-950-50-105.000</u>	<u>CCHD-950-50-95.000</u>	<u>CCHD-950-25-61.440</u>	<u>CCHD-950-25-52.000</u>
<u>CCHD-950-20-104.000</u>	<u>CCHD-950-50-45.1584</u>	<u>CCHD-950-50-49.152</u>	<u>CCHD-950X-50-80.000</u>	<u>CCHD-950X-25-80.000</u>
<u>CCHD-950X-50-100.000</u>				