


## Trench™ Power MOSFET


## IXTA80N10T IXTP80N10T

N-Channel Enhancement Mode  
Avalanche Rated




$$\begin{aligned} V_{DSS} &= 100V \\ I_{D25} &= 80A \\ R_{DS(on)} &\leq 14m\Omega \end{aligned}$$

TO-263  
(IXTA)



TO-220  
(IXTP)



G = Gate      D = Drain  
S = Source    Tab = Drain

| Symbol     | Test Conditions                                                          | Maximum Ratings    |                  |
|------------|--------------------------------------------------------------------------|--------------------|------------------|
| $V_{DSS}$  | $T_J = 25^\circ\text{C}$ to $175^\circ\text{C}$                          | 100                | V                |
| $V_{DGR}$  | $T_J = 25^\circ\text{C}$ to $175^\circ\text{C}$ , $R_{GS} = 1M\Omega$    | 100                | V                |
| $V_{GSS}$  | Continuous                                                               | $\pm 20$           | V                |
| $V_{GSM}$  | Transient                                                                | $\pm 30$           | V                |
| $I_{D25}$  | $T_C = 25^\circ\text{C}$                                                 | 80                 | A                |
| $I_{DM}$   | $T_C = 25^\circ\text{C}$ , Pulse Width Limited by $T_{JM}$               | 220                | A                |
| $I_A$      | $T_C = 25^\circ\text{C}$                                                 | 25                 | A                |
| $E_{AS}$   | $T_C = 25^\circ\text{C}$                                                 | 400                | mJ               |
| $dv/dt$    | $I_S \leq I_{DM}$ , $V_{DD} \leq V_{DSS}$ , $T_J \leq 175^\circ\text{C}$ | 10                 | V/ns             |
| $P_D$      | $T_C = 25^\circ\text{C}$                                                 | 230                | W                |
| $T_J$      |                                                                          | -55 ... +175       | $^\circ\text{C}$ |
| $T_{JM}$   |                                                                          | 175                | $^\circ\text{C}$ |
| $T_{stg}$  |                                                                          | -55 ... +175       | $^\circ\text{C}$ |
| $T_L$      | Maximum Lead Temperature for Soldering                                   | 300                | $^\circ\text{C}$ |
| $T_{SOLD}$ | 1.6 mm (0.062in.) from Case for 10s                                      | 260                | $^\circ\text{C}$ |
| $F_C$      | Mounting Force (TO-263)                                                  | 10..65 / 2.2..14.6 | N/lb             |
| $M_d$      | Mounting Torque (TO-220)                                                 | 1.13 / 10          | Nm/lb.in         |
| Weight     | TO-263                                                                   | 2.5                | g                |
|            | TO-220                                                                   | 3.0                | g                |

### Features

- Ultra-Low On Resistance
- Avalanche Rated
- Low Package Inductance
  - Easy to Drive and to Protect
- $175^\circ\text{C}$  Operating Temperature
- Fast Intrinsic Diode

### Advantages

- Easy to Mount
- Space Savings
- High Power Density

### Applications

- Automotive
  - Motor Drives
  - 42V Power Bus
  - ABS Systems
- DC/DC Converters and Off-line UPS
- Primary Switch for 24V and 48V Systems
- Distributed Power Architectures and VRMs
- Electronic Valve Train Systems
- High Current Switching Applications
- High Voltage Synchronous Rectifier

| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ Unless Otherwise Specified) | Characteristic Values |      |                   |
|--------------|---------------------------------------------------------------------------|-----------------------|------|-------------------|
|              |                                                                           | Min.                  | Typ. | Max.              |
| $BV_{DSS}$   | $V_{GS} = 0V$ , $I_D = 250\mu\text{A}$                                    | 105                   |      | V                 |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 50\mu\text{A}$                                 | 2.5                   |      | 4.5 V             |
| $I_{GSS}$    | $V_{GS} = \pm 20V$ , $V_{DS} = 0V$                                        |                       |      | $\pm 200$ nA      |
| $I_{DSS}$    | $V_{DS} = 105V$ , $V_{GS} = 0V$<br>$T_J = 150^\circ\text{C}$              |                       |      | 5 $\mu\text{A}$   |
|              |                                                                           |                       |      | 150 $\mu\text{A}$ |
| $R_{DS(on)}$ | $V_{GS} = 10V$ , $I_D = 25A$ , Notes 1 & 2                                |                       |      | 14 m $\Omega$     |


| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified)                                                                  | Characteristic Values |      |                        |
|--------------|----------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|------|------------------------|
|              |                                                                                                                                              | Min.                  | Typ. | Max.                   |
| $g_{fs}$     | $V_{DS} = 10\text{V}$ , $I_D = 40\text{A}$ , Note 1                                                                                          | 33                    | 55   | S                      |
| $C_{iss}$    | $V_{GS} = 0\text{V}$ , $V_{DS} = 25\text{V}$ , $f = 1\text{MHz}$                                                                             |                       | 3040 | pF                     |
| $C_{oss}$    |                                                                                                                                              |                       | 420  | pF                     |
| $C_{rss}$    |                                                                                                                                              |                       | 90   | pF                     |
| $t_{d(on)}$  | <b>Resistive Switching Times</b><br>$V_{GS} = 10\text{V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = 10\text{A}$<br>$R_G = 15\Omega$ (External) |                       | 31   | ns                     |
| $t_r$        |                                                                                                                                              |                       | 54   | ns                     |
| $t_{d(off)}$ |                                                                                                                                              |                       | 40   | ns                     |
| $t_f$        |                                                                                                                                              |                       | 48   | ns                     |
| $Q_{g(on)}$  | $V_{GS} = 10\text{V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = 10\text{A}$                                                                    |                       | 60   | nC                     |
| $Q_{gs}$     |                                                                                                                                              |                       | 21   | nC                     |
| $Q_{gd}$     |                                                                                                                                              |                       | 15   | nC                     |
| $R_{thJC}$   | TO-220                                                                                                                                       |                       | 0.50 | $0.65^\circ\text{C/W}$ |
| $R_{thCH}$   |                                                                                                                                              |                       |      | $^\circ\text{C/W}$     |

### Source-Drain Diode

| Symbol   | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified)                          | Characteristic Values |      |       |
|----------|------------------------------------------------------------------------------------------------------|-----------------------|------|-------|
|          |                                                                                                      | Min.                  | Typ. | Max.  |
| $I_S$    | $V_{GS} = 0\text{V}$                                                                                 |                       |      | 80 A  |
| $I_{SM}$ | Repetitive, Pulse Width Limited by $T_{JM}$                                                          |                       |      | 220 A |
| $V_{SD}$ | $I_F = 25\text{A}$ , $V_{GS} = 0\text{V}$ , Note 1                                                   |                       |      | 1.1 V |
| $t_{rr}$ | $I_F = 25\text{A}$ , $V_{GS} = 0\text{V}$<br>$-di/dt = 100\text{A}/\mu\text{s}$ , $V_R = 50\text{V}$ |                       | 100  | ns    |


- Notes: 1. Pulse test,  $t \leq 300\mu\text{s}$ ; duty cycle,  $d \leq 2\%$ .  
2. On through-hole packages,  $R_{DS(on)}$  Kelvin test contact location must be 5mm or less from the package body.

### TO-263 Outline



| SYM | INCHES   |      | MILLIMETER |       |
|-----|----------|------|------------|-------|
|     | MIN      | MAX  | MIN        | MAX   |
| A   | .170     | .185 | 4.30       | 4.70  |
| A1  | .000     | .008 | 0.00       | 0.20  |
| A2  | .091     | .098 | 2.30       | 2.50  |
| b   | .028     | .035 | 0.70       | 0.90  |
| b2  | .046     | .060 | 1.18       | 1.52  |
| C   | .018     | .024 | 0.45       | 0.60  |
| C2  | .049     | .060 | 1.25       | 1.52  |
| D   | .340     | .370 | 8.63       | 9.40  |
| D1  | .300     | .327 | 7.62       | 8.30  |
| E   | .380     | .410 | 9.65       | 10.41 |
| E1  | .270     | .330 | 6.86       | 8.38  |
| e   | .100 BSC |      | 2.54 BSC   |       |
| H   | .580     | .620 | 14.73      | 15.75 |
| L   | .075     | .105 | 1.91       | 2.67  |
| L1  | .039     | .060 | 1.00       | 1.52  |
| L2  | —        | .070 | —          | 1.77  |
| L3  | .010 BSC |      | 0.254 BSC  |       |

### TO-220 Outline




| SYM  | INCHES   |      | MILLIMETERS |       |
|------|----------|------|-------------|-------|
|      | MIN      | MAX  | MIN         | MAX   |
| A    | .169     | .185 | 4.30        | 4.70  |
| A1   | .047     | .055 | 1.20        | 1.40  |
| A2   | .079     | .106 | 2.00        | 2.70  |
| b    | .024     | .039 | 0.60        | 1.00  |
| b2   | .045     | .057 | 1.15        | 1.45  |
| c    | .014     | .026 | 0.35        | 0.65  |
| D    | .587     | .626 | 14.90       | 15.90 |
| D1   | .335     | .370 | 8.50        | 9.40  |
| (D2) | .500     | .531 | 12.70       | 13.50 |
| E    | .382     | .406 | 9.70        | 10.30 |
| (E1) | .283     | .323 | 7.20        | 8.20  |
| e    | .100 BSC |      | 2.54 BSC    |       |
| e1   | .200 BSC |      | 5.08 BSC    |       |
| H1   | .244     | .268 | 6.20        | 6.80  |
| L    | .492     | .547 | 12.50       | 13.90 |
| L1   | .110     | .154 | 2.80        | 3.90  |
| ØP   | .134     | .150 | 3.40        | 3.80  |
| Q    | .106     | .126 | 2.70        | 3.20  |


IXYS reserves the right to change limits, test conditions, and dimensions.

|                                                                                  |           |           |           |           |              |              |              |              |              |             |
|----------------------------------------------------------------------------------|-----------|-----------|-----------|-----------|--------------|--------------|--------------|--------------|--------------|-------------|
| IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: | 4,835,592 | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665    | 6,404,065 B1 | 6,683,344    | 6,727,585    | 7,005,734 B2 | 7,157,338B2 |
|                                                                                  | 4,860,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123 B1 | 6,534,343    | 6,710,405 B2 | 6,759,692    | 7,063,975 B2 |             |
|                                                                                  | 4,881,106 | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728 B1 | 6,583,505    | 6,710,463    | 6,771,478 B2 | 7,071,537    |             |


**Fig. 1. Output Characteristics @  $T_J = 25^\circ\text{C}$**




**Fig. 2. Extended Output Characteristics @  $T_J = 25^\circ\text{C}$**




**Fig. 3. Output Characteristics @  $T_J = 150^\circ\text{C}$**




**Fig. 4.  $R_{DS(on)}$  Normalized to  $I_D = 40\text{A}$  Value vs. Junction Temperature**




**Fig. 5.  $R_{DS(on)}$  Normalized to  $I_D = 40\text{A}$  Value vs. Drain Current**




**Fig. 6. Drain Current vs. Case Temperature**




**Fig. 7. Input Admittance**




**Fig. 8. Transconductance**




**Fig. 9. Forward Voltage Drop of Intrinsic Diode**




**Fig. 10. Gate Charge**




**Fig. 11. Capacitance**




**Fig. 12. Maximum Transient Thermal Impedance**




**Fig. 13. Resistive Turn-on  
Rise Time vs. Junction Temperature**




**Fig. 14. Resistive Turn-on  
Rise Time vs. Drain Current**




**Fig. 15. Resistive Turn-on  
Switching Times vs. Gate Resistance**




**Fig. 16. Resistive Turn-off  
Switching Times vs. Junction Temperature**



**Fig. 17. Resistive Turn-off  
Switching Times vs. Drain Current**



**Fig. 18. Resistive Turn-off  
Switching Times vs. Gate Resistance**





---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).