


**CRYSTEK**  
MICROWAVE  
A DIVISION OF CRYSTEK CORPORATION

# BNC POCKET REFERENCE OSCILLATOR



**New BNC  
PRO Series**



Crystek has expanded its Pocket Reference Oscillator family to now include a BNC version. The larger package allows Crystek to offer its higher performance CLOCK oscillators in the BNC housing. The family will be offered from 10 MHz to 1090 MHz in single frequencies. Output waveforms include Sinewave and HCMOS. Supply voltages will be +3.3V or +5.0V.

## Product Control:


Crystek Part Number:	CPROBS5-0010	Release Date:	05-Feb-2019
Revision Level:	B	Responsible:	C. Vales

Page 1 of 2



**CRYSTEK**  
CORPORATION


12730 COMMONWEALTH DRIVE • FORT MYERS, FLORIDA 33913  
PHONE: 239-561-3311 • 800-237-3061  
FAX: 239-561-1025 • WWW.CRYSTEK.COM



**Model CPROBS5-0010**

BNC PRO, 5V, Sinewave Clock

Frequency:	10.000 MHz
Frequency Stability:	±25 ppm
Temperature Range:	0°C to +70°C
Storage Temperature:	-40°C to +85°C
Input Voltage:	5.0V ± 0.25V
Input Current:	30mA Max
Output Power:	True sinewave, +8 dBm Min, +10 dBm Typical
Second Harmonic:	-25 dBc Max
Sub-Harmonics:	None
Typical Phase Noise:	See Plot on page 1
Frequency Aging:	<3ppm 1 <sup>st</sup> year, <1ppm every year thereafter



**Product Control:**

Crystek Part Number:	CPROBS5-0010	Release Date:	05-Feb-2019
Revision Level:	B	Responsible:	C. Vales

Crystek Corporation reserves the right to make changes to its products and/or information contained herein without notice.  
No liability is assumed as a result of its use or application.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Crystek:](#)

[CPROBS5-0010](#)