


CVPD-034 LVPECL

Voltage Controlled Crystal Oscillator

5×7mm SMD

3.3 Volts



Rev: AB
Date: 19-Jan-2017
Page 1 of 3



CVPD-034 LVPECL
Voltage Controlled Crystal Oscillator
5×7mm SMD
3.3 Volts



Frequency Range:	77.760 MHz to 200.000 MHz
Frequency Pulling (APR*) Min:	±50ppm
Temperature Range: (standard)	0°C to +70°C
(Option M)	-20°C to +70°C
(Option X)	-40°C to +85°C
Storage:	-45°C to +90°C
Input Voltage:	3.3V ±5%
Control Voltage:	1.65V ±1.65V
Input Current:	55mA Typical, 88mA Max
Output:	Differential LVPECL
Symmetry:	45/55% Max @ zero crossing point
Rise/Fall Time:	1ns Max (20% to 80%)
Linearity:	±10% Max
Logic: Terminated to Vdd-2V into 50 Ω	
Temp. 0°C to 85°C	“0”=1.490 Min, 1.680 Max “1”=2.275 Min, 2.420 Max
Temp. -40°C to 0°C	“0”=1.490 Min, 1.745 Max “1”=2.215 Min, 2.420 Max
Disable Time:	200ns Max
Enable Time:	20us Max
Phase Jitter: 12 kHz~80 MHz	0.5ps Typical, 1ps RMS Max
Phase Noise: 10 Hz	-70 dBc/Hz Typical
100 Hz	-98 dBc/Hz Typical
1 kHz	-125 dBc/Hz Typical
10 kHz	-145 dBc/Hz Typical
100 kHz	-149 dBc/Hz Typical
Sub-harmonics:	None
Aging:	<5ppm 1st year, <2ppm every year thereafter

*** Inclusive of calibration, frequency stability, and aging**

Rev: AB
Date: 19-Jan-2017
Page 2 of 3

Specifications subject to change without notice.





CVPD-034 LVPECL

Voltage Controlled Crystal Oscillator

5×7mm SMD

3.3 Volts



Crystek Part Number Guide

CVPD - 034 X - 50 - 155.520

#1 #2 #3 #4 #5

#1 Crystek PECL VCXO
#2 Model 034
#3 Temp Range: Blank = 0/70°C, M = -20/70°C, X = -40/85°C
#4 Pullability: (see Table 1)
#5 Frequency in MHz: 3 or 6 decimal places

Pullability Indicator

50 ± 50ppm

Table 1

Example:

CVPD-034X-50-155.520

3.3V, -40/85°C, ±50ppm (APR), 155.520 MHz

Standard Frequencies

(±50ppm, 0/70°C)

77.760 MHz

155.520 MHz

156.250 MHz

161.132800 MHz

200.000 MHz

Mechanical:

Shock: MIL-STD-883, Method 2002, Condition B

Solderability: MIL-STD-883, Method 2003

Vibration: MIL-STD-883, Method 2007, Condition A

Solvent Resistance: MIL-STD-202, Method 215


Resistance to Soldering Heat: MIL-STD-202, Method 210, Condition I or J

Environmental:


Thermal Shock: MIL-STD-883, Method 1011, Condition A

Moisture Resistance: MIL-STD-883, Method 1004

RECOMMENDED REFLOW SOLDERING PROFILE




NOTE: Reflow Profile with 240°C peak also acceptable.




Dimensions inches (mm)

All dimensions are Max unless otherwise specified.




Enable/Disable

Function pin 2	Output pin
Open or N/C	Active
"1" level 0.7×Vdd Min	Active
"0" level 0.3×Vdd Max	High Z



SUGGESTED PAD LAYOUT



0.01μF Bypass Capacitor Recommended

PIN	Connection
1	Volt Control
2	Enable/Disable
3	GND
4	Output
5	Comp Output
6	Vcc

Rev: AB

Date: 19-Jan-2017

Page 3 of 3



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Crystek:

[CVPD-034X-50-161.1328](#) [CVPD-034X-50-155.52](#) [CVPD-034X-50-156.25](#) [CVPD-034X-50-167.3316](#) [CVPD-034X-50-166.6286](#) [CVPD-034X-50-77.76](#) [CVPD-034-50-155.52](#) [CVPD-034-50-156.25](#) [CVPD-034-50-161.13](#) [CVPD-034-50-77.76](#)