G12LAC-P08LJG0-0000

series l

type_g1

General information

Part number	G12LAC-P08LJG0-0000
Termination	solder
Size	2
Locking principle	break , push
Coding	a_key

Illustrations may differ from original product.
Dimensions, unless otherwise specified, in mm.

CODING: 30 °



POSITIONS: 8 positions



PANEL CUT OUT:



DIMENSIONS:



The pin layout corresponds to the view on the termination area

Contact insert description

Number of contacts	8
Contact type	sockets
Contact diameter	09mm
Insulator material	peek
Wire cross section	22_awg
Termination	solder
Termination diameter	085mm

reverse_gender_on_request

Technical information

Max. creepage and air clearance distance	12_mm	11_mm
Nominal current single contact	075_a	iec_60512_5_2
Nominal current insert	4,875 A	vde_0298_4
Test voltage	15_kv_ac	sae_13441

safety_text

Mechanical and environmental data

Degree of protection*	ip50
Operating temperature	40_120_c
Mating cycles	5000

mated_unmated

Material and surface treatments

Housing	m_chrome
Contact	cu_alloy_gold

safety_text_2
ul_text
illustrative_text

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ODU:

G12LAC-P08LJG0-0000