


Für diese Unterlage behalten wir uns alle Rechte vor, auch fuer den Fall der Patenterteilung oder Gebrauchsmustererteilung. Sie darf ohne unsere vorherige schriftliche Zustimmung weder vervielfaeltigt noch sonstwie benutzt, noch Dritten zugaenglich gemacht werden.

Nur rol gestempelte oder auf Laufkarte gedruckte Dokumente unterliegen dem Aenderungsdienst und sind zur Fertigung freigegeben. Only red stamped or on jobcard printed documents are managed. These documents are approved for production.


All Rights reserved, including possible patents or trademarks. Documents shall not be provided to a third party or duplicated in any form without prior written permission.

CAD: Creo Parametric


Additional coding
View in direction B






A1CWB-P04MBC0-0000
Mechanical coding: B
Color coding: red



A1CWC-P04MBC0-0000
Mechanical coding: C
Color coding: blue




A1CWD-P04MBC0-0000
Mechanical coding: D
Color coding: green



A1CWA-P04MBC0-0000
Mechanical coding: A
Color coding: light brown

Only insert
View in direction A
10:1



Technical information

- Max. cable Ø5.0mm (Based on cable with one braided shield)
- Solder contacts: AWG28
- Current load: 1A@Δt40° (Single contact)
- Test voltage: 900V (acc. SAE AS 13441:1998, Contact to contact)
- Rated voltage: 300V (acc. SAE AS 13441:1998) 2)

1) For crimp information, torque, etc. see assembly instruction 010.650.001.000.001 (www.odu.de/downloads)

2) Maximal operating voltage at sea level up to 2.000m. Rated voltage applies no other electrical safety standard. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. This must be evaluated in the frame of equipment engineering.

Bei den hier dargestellten ODU-Steckverbindern handelt es sich nach DIN EN 61984:2009 um Steckverbinder ohne Schaltleistung (COC) !
/the pictured ODU-connectors are in relation to DIN EN 61984:2009 connectors without switching capacity (COC) !

 Allgemeintoleranz/general tol.: DIN ISO 2768-mH Tolerierung / Tolerancing: DIN ISO 8015	Version: revision: -	Benennung/description: Abreissstecker cpl. Break-Away Plug		Werkstoff: material: see BOM
		CAD-Nr.: design-ID:	00101630	
Status/state: Approved	Erstellt/prepared 12.01.2016 spantze	Teile-ID: part-ID:		Format: size: A3
Freigabe/released 28.01.2016 mmeier	Geaendert/revised 12.01.2016 spantze	Oxaion-Nr.:	A1CW_C-P04MBC0-0000	Einheit: dim.: mm
ODU-MUEHLDORF	Datum/date	Name/name	Ursprung/origin.:	Bl.: sheet: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ODU USA:

[A1CWBC-P04MBC0-0000](#)