



Model 377

HFF LVDS VCXO

Features

- Ceramic Surface Mount Package
- Ultra-Low Phase Jitter Performance
- High Frequency Fundamental Crystal Design
- Frequency Range 100 – 250MHz *
- +2.5V or +3.3V Operation
- Output Enable Standard
- Tape and Reel Packaging, EIA-418

Applications

- Small Cells
- Wireless Communication
- Broadband Access
- SONET/SDH/DWDM
- Base Stations
- Ethernet/GbE/SyncE
- Digital Video
- Test and Measurement

Description

CTS Model 377 is a low cost, small size, high performance VCXO. Employing the latest IC technology, coupled with a high frequency fundamental crystal, M377 has excellent stability and low jitter/phase noise performance.

Ordering Information

Model	Supply Voltage	Absolute Pull Range	Frequency Stability	Temperature Range	Frequency Code [MHz]	Packaging																		
377	L	B	3	I	XXX or XXXX	T																		
<table><tr><th>Code</th><th>Voltage</th></tr><tr><td>L</td><td>+3.3V ±5%</td></tr><tr><td>N</td><td>+2.5V ±5%</td></tr></table>		Code	Voltage	L	+3.3V ±5%	N	+2.5V ±5%	<table><tr><th>Code</th><th>Stability</th></tr><tr><td>5</td><td>±25ppm ¹</td></tr><tr><td>4</td><td>±30ppm</td></tr><tr><td>3</td><td>±50ppm</td></tr></table>		Code	Stability	5	±25ppm ¹	4	±30ppm	3	±50ppm	<table><tr><th>Code</th><th>Frequency</th></tr><tr><td colspan="2">Product Frequency Code ²</td></tr></table>			Code	Frequency	Product Frequency Code ²	
Code	Voltage																							
L	+3.3V ±5%																							
N	+2.5V ±5%																							
Code	Stability																							
5	±25ppm ¹																							
4	±30ppm																							
3	±50ppm																							
Code	Frequency																							
Product Frequency Code ²																								
<table><tr><th>Code</th><th>APR</th></tr><tr><td>B</td><td>±50ppm ³</td></tr></table>		Code	APR	B	±50ppm ³	<table><tr><th>Code</th><th>Temp. Range</th></tr><tr><td>C</td><td>-20°C to +70°C</td></tr><tr><td>I</td><td>-40°C to +85°C</td></tr></table>		Code	Temp. Range	C	-20°C to +70°C	I	-40°C to +85°C	<table><tr><th>Code</th><th>Packing</th></tr><tr><td>T</td><td>1k pcs./reel</td></tr></table>		Code	Packing	T	1k pcs./reel					
Code	APR																							
B	±50ppm ³																							
Code	Temp. Range																							
C	-20°C to +70°C																							
I	-40°C to +85°C																							
Code	Packing																							
T	1k pcs./reel																							

Notes:

- 1] Check factory availability with "I" temperature range.
- 2] Refer to document 016-1454-0, Frequency Code Tables. 3-digits for frequencies <100MHz, 4-digits for frequencies 100MHz or greater.
- 3] Frequencies ≥200MHz, APR is ±30ppm.

**Not all performance combinations and frequencies may be available.
Contact your local CTS Representative or CTS Customer Service for availability.**

This product is specified for use only in standard commercial applications. Supplier disclaims all express and implied warranties and liability in connection with any use of this product in any non-commercial applications or in any application that may expose the product to conditions that are outside of the tolerances provided in its specification.



Part Dimensions:
7.0 × 5.0 × 2.0mm • 178.462mg

Standard Frequencies

- 100.00MHz
- 122.88MHz
- 125.00MHz
- 153.60MHz
- 155.52MHz
- 156.25MHz
- 160.00MHz
- 166.00MHz
- 200.00MHz
- 204.80MHz

* Check with factory for availability of frequencies not listed.

Electrical Specifications

Operating Conditions

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Maximum Supply Voltage	V_{CC}	-	-0.3	-	5.0	V
Maximum Control Voltage	V_C	-	-0.5	-	V_{CC}	V
Supply Voltage	V_{CC}	$\pm 5\%$	3.14 2.38	3.3 2.5	3.47 2.63	V
Supply Current	I_{CC}	LVDS Load	-	20	55	mA
Output Load	R_L	Between Outputs	-	100	-	Ohms
Operating Temperature	T_A	-	-20 -40	+25	+70 +85	°C
Storage Temperature	T_{STG}	-	-40	-	+100	°C

Frequency Stability

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Frequency Range	f_0	-		100 - 250		MHz
Frequency Stability [Note 1]	$\Delta f/f_0$	± 25 ppm stability, -20°C to +70°C only		25, 30 or 50		\pm ppm
Absolute Pull Range [Note 2]	APR	Frequencies <200MHz	50	-	-	\pm ppm
	APR	Frequencies ≥ 200 MHz	30	-	-	\pm ppm
Aging	$\Delta f/f_{25}$	First Year @ +25°C, nominal V_{CC} and V_C	-3	-	3	ppm

1.] Inclusive of initial tolerance at time of shipment, changes in supply voltage, load, temperature and 1st year aging.

2.] Minimum guaranteed frequency shift from f_0 over variations in temperature, aging, power supply and load.

Output Parameters

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Output Type	-	-		LVDS		-
Output Voltage Levels	V_{OH}	LVDS Load	-	1.43	1.60	V
	V_{OL}	LVDS Load	0.90	1.10	-	
Differential Output Voltage	V_{OD}	$R_L = 100$ Ohms	247	350	454	mV
Offset Voltage	V_{OS}	$R_L = 100$ Ohms	1.125	1.25	1.375	V
Output Duty Cycle	SYM	@ 1.25V	45	-	55	%
Rise and Fall Time	T_R, T_F	@ 20%/80% Levels	-	0.4	1.0	ns
Start Up Time	T_S	Application of V_{CC}	-	5	10	ms
Enable Function						
Enable Input Voltage	V_{IH}	Pin 2 Logic '1', Output Enabled	0.7 V_{CC}	-	-	V
Disable Input Voltage	V_{IL}	Pin 2 Logic '0', Output Disabled	-	-	0.3 V_{CC}	V
Standby Current	I_{STB}	Pin 2 Logic '0', Output Standby	-	-	10	μ A
Enable Time	T_{PLZ}	Pin 2 Logic '1'	-	-	20	μ s
Phase Jitter, RMS	t_{jrms}	Bandwidth 12kHz - 20MHz	-	70	200	fs
Phase Noise	-	See Typical Plots	-	-	-	-

Electrical Specifications

Enable Truth Table


Pin 2	Pin 4 & 5	Pin 2	Pin 4 & 5	Pin 2	Pin 4 & 5
Logic '1'	Output	Open	Output	Logic '0'	High Imp.

Control Voltage

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Control Voltage	V_C	$V_{CC} = +3.3V$	0.00	1.65	3.30	V
		$V_{CC} = +2.5V$	0.25	1.25	2.25	V
Frequency Deviation	$\Delta f/f_0$	$V_C = 0.0V$		-155 to -75		ppm
		$V_C = +3.3V$		75 to 155		ppm
		$V_C = 0.0V$		-140 to -50		ppm
		$V_C = +2.5V$		50 to 140		ppm
Linearity	L	Best Straight Line Fit	-	5	10	%
Gain Transfer	K_V	Pull Sensitivity; @ +1.65V, +25°C	-	75	-	ppm/V
		Pull Sensitivity; @ +1.25V, +25°C	-	75	-	ppm/V
Input Impedance	Z_{V_C}	-	10	-	-	MOhms
Modulation Roll-off	-	@ -3dB	20	-	-	kHz
Transfer Function	-	-		Positive		-


Test Circuit

LVDS



Output Waveform

LVDS




Electrical Specifications


Performance Data

Frequency Deviation – Over Temperature [typical]

122.88MHz, $V_{CC} = 3.3V$, $V_C = 1.65V$




156.25MHz, $V_{CC} = 3.3V$, $V_C = 1.65V$




Frequency Deviation – Pulling Range [typical]

122.88MHz, $V_{CC} = 3.3V$, $T_A = +25^\circ V$




156.25MHz, $V_{CC} = 3.3V$, $T_A = +25^\circ V$




Frequency Deviation – Gain Transfer [typical]

122.88MHz, $V_{CC} = 3.3V$, $T_A = +25^\circ V$



156.25MHz, $V_{CC} = 3.3V$, $T_A = +25^\circ V$




Electrical Specifications


Performance Data

Phase Noise [typical]

122.88MHz, $V_{CC} = 3.3V$, $V_C = 1.65V$, $T_A = +25^\circ C$




156.25MHz, $V_{CC} = 3.3V$, $V_C = 1.65V$, $T_A = +25^\circ C$



Mechanical Specifications


Package Drawing



Marking Information

1. ** - Manufacturing Site Code.
2. D - Date Code. See Table I for codes.
3. ST - Frequency Stability/Temperature Code. [Refer to Ordering Information]
4. V - Voltage Code. L = 3.3V, N = 2.5V
5. xxxx - Frequency Code. 4-digits required for frequencies 100MHz and above. [See document 016-1454-0, Frequency Code Tables.]

Recommended Pad Layout



Notes

1. JEDEC termination code (e4). Barrier-plating is nickel [Ni] with gold [Au] flash plate.
2. Reflow conditions per JEDEC J-STD-020; +260°C maximum, 20 seconds.
3. MSL = 1.

Pin Assignments


Pin	Symbol	Function
1	V _C	Control Voltage
2	EOH	Enable
3	GND	Circuit & Package
4	Output	RF Output
5	Output	RF Output, Complementary
6	V _{CC}	Supply Voltage

Table I - Date Code


MONTH					JAN	FEB	MAR	APR	MAY	JUN	JUL	AUG	SEP	OCT	NOV	DEC
YEAR					A	B	C	D	E	F	G	H	J	K	L	M
2001	2005	2009	2013	2017	A	B	C	D	E	F	G	H	J	K	L	M
2002	2006	2010	2014	2018	N	P	Q	R	S	T	U	V	W	X	Y	Z
2003	2007	2011	2015	2019	a	b	c	d	e	f	g	h	j	k	l	m
2004	2008	2012	2016	2020	n	p	q	r	s	t	u	v	w	x	y	z

Packaging - Tape and Reel

Tape Drawing



Reel Drawing



Notes

1. Device quantity is 1k pieces maximum per 180mm reel.
2. Complete CTS part number, frequency value and date code information must appear on reel and carton labels.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CTS:

[377NB3C1555T](#) [377NB6C1660T](#) [377LB5C1555T](#) [377LB3I1250T](#) [377LB5C2048T](#) [377LB6C1555T](#) [377LB5C1250T](#)
[377NB5C1000T](#) [377LB5I1228T](#) [377LB5C1000T](#) [377NB5I1555T](#) [377LB3C1000T](#) [377LB5I1555T](#) [377NB3C1228T](#)
[377NB6C1228T](#) [377LB6C1250T](#) [377NB3I1555T](#) [377NB3I1250T](#) [377LB6C1562T](#) [377LB3C1228T](#) [377NB6C1250T](#)
[377NB3I2048T](#) [377LB6C1000T](#) [377LB5I1000T](#) [377NB5C1562T](#) [377LB5I2000T](#) [377LB3C1562T](#) [377LB5C1228T](#)
[377NB5C1555T](#) [377NB3I2000T](#) [377LB6C1228T](#) [377LB6C2000T](#) [377NB3C1250T](#) [377LB3I1562T](#) [377LB5I1562T](#)
[377LB3I1000T](#) [377NB5I2048T](#) [377LB3C2000T](#) [377NB3I1228T](#) [377NB3C1536T](#) [377NB5I1660T](#) [377NB5C1250T](#)
[377NB5I1536T](#) [377NB5I1228T](#) [377LB3I1228T](#) [377LB5I1536T](#) [377LB3I1536T](#) [377LB5C1660T](#) [377NB3C1000T](#)
[377NB5C1228T](#) [377LB3C1536T](#) [377NB6C1562T](#) [377NB3C1562T](#) [377LB5I1660T](#) [377LB6C2048T](#) [377NB5C2000T](#)
[377NB5I1250T](#) [377NB3C1660T](#) [377NB3I1562T](#) [377NB5I1000T](#) [377LB3C1660T](#) [377NB3I1000T](#) [377NB3C2000T](#)
[377LB6C1536T](#) [377NB5I1562T](#) [377NB5C1660T](#) [377NB6C2000T](#) [377NB5C1536T](#) [377LB5I1250T](#) [377NB3C2048T](#)
[377LB3I1555T](#) [377NB3I1536T](#) [377LB5C1562T](#) [377LB5C2000T](#) [377LB6C1660T](#) [377LB3I2000T](#) [377NB5C2048T](#)
[377NB6C2048T](#) [377NB6C1555T](#) [377LB3C1250T](#) [377LB3I2048T](#) [377LB3C1555T](#) [377LB5C1536T](#) [377LB3I1660T](#)
[377NB6C1000T](#) [377NB5I2000T](#) [377NB6C1536T](#) [377LB3C2048T](#) [377LB5I2048T](#) [377NB3I1660T](#)