

MARKETING SALES DRAWING

Electrical Testing per Tusonix standard test plans and Mil-Std-202 Test Methods.



ORIENTATION

CIRCUIT



←.110 ±.010

[2.79 ±0.25]

NOTES:

1. TUSONIX STANDARD PART

NUMBER: 4100-002.

TUSONIX RoHS COMPLIANT PART

NUMBER: 4100-002 LF.

CUSTOMER MUST SPECIFY STANDARD OR

RoHS PART NUMBER WHEN ORDERING.

2. LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED.

RoHS PART #: SILVER PLATED.

3. EYELET FINISH: STANDARD PART #: 60/40 SOLDER PLATED.

RoHS PART #: SILVER PLATED.

4. PART MARKING: STANDARD, NO MARKING.

RoHS PART: GREEN DOT ON INSULATION BAND,

TYPICAL LOCATION.

			MIN. CAP.			WORKING VOLTAGE			CURRENT	I.R. MIN. @		WV						
			pF 1500			85°C	: 1	125°C	ldc.	MIN. @ 100 (VDC.)	(V	DC)	10 MHz	100 MF	lz 1	1 GHz	10 GHz	
						350		200	15 A	10 G	7	00	5	25		60	60	
RECORD	0	A" ADDED	-	FMT.	5 2	t, DWV & 06-05	9						TOLERANCES Unless Otherwise Specified DECIMAL ± .031 [0.79]		EYELET STYLE EMI FILTER			
12	ease 653	UNIT ".		OMP F	-5-06	TES, I	-4-06					ANG	LES ± /	///	Drawr	n S.I	M. 07-13-00	Scale 6 X
Rev-0	Rele	CURRENT UI L.E. 08-20-85	2595	TO C	00071	IU	526					TUSONIX		1777	Approved T.C. 07-13-00			
X-2015 Rev-0 REVISIOI	Original C.O.						20050					-	UĐUN CSON, ARIZ		Α		4100-	002

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

<u>Tusonix / CTS</u>: 4100-002LF