





DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



ORIENTATION



1. TUSONIX STANDARD PART NUMBER: 4251-001.
TUSONIX RoHS COMPLIANT PART NUMBER: 4251-001 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
3. SUPPLIED WITH SILVER PLATED COPPER ALLOY HEX NUT AND INTERNAL TOOTH LOCK WASHER.

15,000		50 VDC		10 GΩ		250 VDC		10 A		5		9		18		45		65		70		70	
MIN. CAP.(pf)		+125 °C DC WORKING VOLTAGE		I.R. MIN. @ 100 VDC		DWV		CURRENT		1 MHz		3 MHz		10 MHz		30 MHz		100 MHz		300 MHz		1GHz	
MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220																							
REVISION RECORD Original Release C.O. 6611 HDIM'S REVISED .81 WAS .812 6.7 WAS 6.75. TITLE CHGD. E.C. 5-26-92 6667 RDN TO COMP FMT. S.M. 06-03-02 20020528-3-02 DWV 250 WAS 125. S.M. 09-22-03 20030922-5-03 ADDED NOTES 1-3. S.M. 10-06-05 20050927-7-03						--TOLERANCES-- Unless Otherwise Specified DECIMAL ± .031 [0.79] ANGLES ±  TUSONIX TUCSON, ARIZONA						Title MULTI LAYER BUSHING STYLE EMI FILTER											
												Drawn S. M. 02-28-02						Scale 4 X					
												Approved T.C. 02-58-02											
												A		4251-001									

X-2015 Rev-0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[4251-001LF](#)