




Model CHT25

HIGH TEMPERATURE HCMOS CLOCK



Features

- Ceramic Surface Mount Package
- Extended-Industrial Temperature Ranges
- Fundamental and 3rd Overtone Crystal Designs
- Frequency Range 1.25 – 156.25MHz
- +1.8V, +2.5V and +3.3V Operation
- Output Enable Standard
- Tape and Reel Packaging, EIA-418

Part Dimensions:
2.5 × 2.0 × 1.0mm • 14.25851mg

Standard Frequencies

* See Page 6 for common frequencies.
Check with factory for availability of frequencies not listed.

Applications

- Industrial IoT [IIoT]
- Industrial Controls
- Commercial Military & Aerospace
- M2M Communication
- Energy Industry
- Test and Measurement

Description

CTS Model CHT25 is a low cost, small size, Clock Oscillator [XO] that operates over extended-industrial temperature ranges. CHT25 has an HCMOS/TTL compatible output, offers excellent stability and low jitter/phase noise performance.

Ordering Information

Model		Output Type	Frequency Code [MHz]	Frequency Stability	Temperature Range	Supply Voltage	Packaging						
CHT	25	C	XXX or XXXX	2	P	3	T						
↓		↓	↓	↓	↓	↓	↓						
Code	Package Size		Code		Frequency			Code	Temp. Range	Code	Packing		
25	2.5x2.0mm		Product Frequency Code ¹		P			-55°C to +105°C ¹	T	1k pcs./reel			
		↓	↓	↓	↓	↓	↓						
								Code	Output	Code	Stability	Code	Voltage
								C	HCMOS	2	±100ppm	M	+1.8Vdc
		↓	↓	↓	↓	↓	↓						
								7	±150ppm	N	+2.5Vdc		
										L	+3.3Vdc		

Notes:

1] Stability codes 2 and 7. Contact factory for availability.

Not all performance combinations and frequencies may be available.
Contact your local CTS Representative or CTS Customer Service for availability.

This product is specified for use only in standard commercial applications. Supplier disclaims all express and implied warranties and liability in connection with any use of this product in any non-commercial applications or in any application that may expose the product to conditions that are outside of the tolerances provided in its specification.



Electrical Specifications

Operating Conditions

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Maximum Supply Voltage	V _{CC}	-	-0.5	-	4.0	V
Supply Voltage	V _{CC}	±5%	1.710	1.8	1.890	V
			2.375	2.5	2.665	
			3.135	3.3	3.465	
Typical @ Nominal Vcc, C _L = 15 pF, T _A = +25°C						
Supply Current	I _{CC}	@ +1.8V	-	10	15	mA
		@ +2.5V	-	15	20	
		@ +3.3V	-	15	20	
Output Load	C _L	-	-	-	15	pF
Operating Temperature	T _A	-	-55	+25	+105	°C
			-55		+125	
Storage Temperature	T _{STG}	-	-55	-	+125	°C

Frequency Stability

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Frequency Range	f_O	Temperature Range -55°C to $+105^\circ\text{C}$		1.25 - 156.25		MHz
		Temperature Range -55°C to $+125^\circ\text{C}$		40 - 156.26		
Frequency Stability [Note 1]	$\Delta f/f_O$	-		25, 30, 50, 100 or 150		$\pm\text{ppm}$
Aging	$\Delta f/f_{25}$	First Year @ $+25^\circ\text{C}$, nominal V_{CC}	-5	-	5	ppm

1.] Inclusive of initial tolerance at time of shipment, changes in supply voltage, load, temperature and 1st year aging.

Output Parameters

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Output Type	-	-		HCMOS		-
Output Voltage Levels	V_{OH}	Logic '1' Level, CMOS Load	$0.9V_{CC}$	-	-	V
	V_{OL}	Logic '0' Level, CMOS Load	-	-	$0.1V_{CC}$	
Output Current Levels	I_{OH}	$V_{OH} = 90\%V_{CC}$ [1.8V, 2.5V, 3.3V]	-	-	-4, -4, -8	mA
	I_{OL}	$V_{OL} = 10\%V_{CC}$ [1.8V, 2.5V, 3.3V]	-	-	+4, +4, +8	
Output Duty Cycle	SYM	@ 50% Level	45	-	55	%
@ 10%/90% Levels, Nominal V_{CC} , $C_L = 15$ pF						
Rise and Fall Time [Note 2]	T_R, T_F	@ +1.8V	-	5	7	ns
		@ +2.5V	-	5	7	
		@ +3.3V	-	6	7	
Start Up Time	T_S	Application of V_{CC}	-	2	5	ms

2.] Parameters are worst case and account for comprehensive range of product specification. Performance may vary by application and must be validated by end user.

Electrical Specifications

Output Parameters


PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Enable Function Standby						
Enable Input Voltage	V_{IH}	Pin 1 Logic '1', Output Enabled	$0.7V_{CC}$	-	-	V
Disable Input Voltage	V_{IL}	Pin 1 Logic '0', Output Standby	-	-	$0.3V_{CC}$	V
Enable Current	I_{STB}	Pin 1 Logic '0', Output Standby	-	-	10	μA
Enable Time	T_{PLZ}	Pin 1 Logic '1'	-	-	5	ms
Phase Jitter, RMS	tjrms	Bandwidth 12 kHz - 20 MHz	-	0.5	<1	ps

Enable Truth Table

Pin 1	Pin 3
Logic '1'	Output
Open	Output
Logic '0'	High Imp.


Test Circuit

HCMOS




Output Waveform

HCMOS



Mechanical Specifications


Package Drawing



Marking Information

1. CHT25 – CTS model.
2. ** – Manufacturing Site Code.
3. ● – Pin 1 identifier.
4. D – Date Code. See Table I for codes.
5. xxxx – Frequency Code.
3-digits for frequencies <100MHz
4-digits for frequencies 100MHz or greater
[See document 016-1454-0, Frequency Code Tables.]

Recommended Pad Layout



Notes

1. Termination pads (e4). Barrier-plating is nickel [Ni] with gold [Au] flash plate.
2. Reflow conditions per JEDEC J-STD-020; +260°C maximum, 20 seconds.
3. MSL = 1.

Pin Assignments


Pin	Symbol	Function
1	EOH	Enable
2	GND	Circuit & Package
3	Output	RF Output
4	V _{CC}	Supply Voltage

Table I - Date Code


MONTH					JAN	FEB	MAR	APR	MAY	JUN	JUL	AUG	SEP	OCT	NOV	DEC
YEAR																
2001	2005	2009	2013	2017	A	B	C	D	E	F	G	H	J	K	L	M
2002	2006	2010	2014	2018	N	P	Q	R	S	T	U	V	W	X	Y	Z
2003	2007	2011	2015	2019	a	b	c	d	e	f	g	h	j	k	l	m
2004	2008	2012	2016	2020	n	p	q	r	s	t	u	v	w	x	y	z

Packaging - Tape and Reel

Tape Drawing



Reel Drawing



Notes

1. Device quantity is 1k pieces minimum and 3k pieces maximum per 180mm reel.
2. Complete CTS part number, frequency value and date code information must appear on reel and carton labels.



Addendum

Common Frequencies Available – MHz

FREQUENCY	FREQUENCY CODE	FREQUENCY	FREQUENCY CODE	FREQUENCY	FREQUENCY CODE	FREQUENCY	FREQUENCY CODE
4.000000	040	24.000000	240	40.000000	400		
8.000000	080	24.576000	24C	48.000000	480		
10.000000	100	25.000000	250	50.000000	500		
12.000000	120	26.000000	260				
12.288000	122	27.000000	270				
14.318180	143	30.000000	300				
14.745600	147	32.000000	320				
16.000000	160	33.333000	33E				
20.000000	200	37.400000	374				
22.118400	221	38.400000	384				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CTS:

<u>CHT25C1227PNT</u>	<u>CHT25C2002PMT</u>	<u>CHT25C2602PMT</u>	<u>CHT25C2607PNT</u>	<u>CHT25C3207PLT</u>	<u>CHT25C4807MNT</u>
<u>CHT25C5002PNT</u>	<u>CHT25C4007PLT</u>	<u>CHT25C4007PNT</u>	<u>CHT25C2402PNT</u>	<u>CHT25C3007PMT</u>	<u>CHT25C5002MLT</u>
<u>CHT25C4802MLT</u>	<u>CHT25C0402PMT</u>	<u>CHT25C0407PLT</u>	<u>CHT25C1007PNT</u>	<u>CHT25C24C7PLT</u>	<u>CHT25C2702PLT</u>
<u>CHT25C33E2PMT</u>	<u>CHT25C3847PLT</u>	<u>CHT25C4802PLT</u>	<u>CHT25C1222PMT</u>	<u>CHT25C1602PLT</u>	<u>CHT25C2217PMT</u>
<u>CHT25C2402PLT</u>	<u>CHT25C2507PNT</u>	<u>CHT25C4007MMT</u>	<u>CHT25C1432PLT</u>	<u>CHT25C2217PLT</u>	<u>CHT25C24C7PNT</u>
<u>CHT25C3002PMT</u>	<u>CHT25C3202PNT</u>	<u>CHT25C33E7PLT</u>	<u>CHT25C3842PNT</u>	<u>CHT25C24C7PMT</u>	<u>CHT25C3207PMT</u>
<u>CHT25C3847PMT</u>	<u>CHT25C4802PMT</u>	<u>CHT25C4002MMT</u>	<u>CHT25C4002PLT</u>	<u>CHT25C4007PMT</u>	<u>CHT25C2212PMT</u>
<u>CHT25C2407PMT</u>	<u>CHT25C3202PLT</u>	<u>CHT25C0802PNT</u>	<u>CHT25C33E7PNT</u>	<u>CHT25C1007PLT</u>	<u>CHT25C1477PMT</u>
<u>CHT25C2502PLT</u>	<u>CHT25C2502PNT</u>	<u>CHT25C2607PLT</u>	<u>CHT25C3842PMT</u>	<u>CHT25C4002MNT</u>	<u>CHT25C5002PLT</u>
<u>CHT25C0807PLT</u>	<u>CHT25C1002PLT</u>	<u>CHT25C2402PMT</u>	<u>CHT25C2602PLT</u>	<u>CHT25C3742PMT</u>	<u>CHT25C3747PLT</u>
<u>CHT25C4002PNT</u>	<u>CHT25C4007MLT</u>	<u>CHT25C4007MNT</u>	<u>CHT25C0802PLT</u>	<u>CHT25C1472PNT</u>	<u>CHT25C1607PNT</u>
<u>CHT25C2212PNT</u>	<u>CHT25C3202PMT</u>	<u>CHT25C33E7PMT</u>	<u>CHT25C3747PNT</u>	<u>CHT25C1437PLT</u>	<u>CHT25C1472PMT</u>
<u>CHT25C24C2PNT</u>	<u>CHT25C1202PMT</u>	<u>CHT25C1202PNT</u>	<u>CHT25C1437PNT</u>	<u>CHT25C2002PNT</u>	<u>CHT25C2007PLT</u>
<u>CHT25C2007PMT</u>	<u>CHT25C2007PNT</u>	<u>CHT25C24C2PMT</u>	<u>CHT25C2702PMT</u>	<u>CHT25C33E2PLT</u>	<u>CHT25C4802PNT</u>
<u>CHT25C5007MNT</u>	<u>CHT25C0807PNT</u>	<u>CHT25C1227PMT</u>	<u>CHT25C1602PNT</u>	<u>CHT25C0802PMT</u>	<u>CHT25C1007PMT</u>
<u>CHT25C1207PLT</u>	<u>CHT25C24C2PLT</u>	<u>CHT25C2607PMT</u>	<u>CHT25C2707PNT</u>	<u>CHT25C3842PLT</u>	<u>CHT25C3747PMT</u>
<u>CHT25C3002PNT</u>	<u>CHT25C4807MLT</u>	<u>CHT25C3007PNT</u>	<u>CHT25C1432PNT</u>		