




MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



NOTES:

- TUSONIX STANDARD PART NUMBER: 4206-023.
TUSONIX RoHS COMPLIANT PART NUMBER: 4206-023 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS PART #: SILVER PLATED.
- PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
- SUPPLIED WITH SILVER PLATED COPPER ALLOY HEX NUT AND INTERNAL TOOTH LOCKWASHER.

4500/ 9000	700	500	30	15	65	70	70
CAP. (pF)	85° C	125° C	MAX. CURRENT Adc	10 MHz	100 MHz	1 GHz	10 GHz
	WORKING VOLTAGE (VVdc)			MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220			

REVISION RECORD			Original Release C.O. 19980225-1-01 CORRECT TYP0 THREAD WAS 15/16". S.M. 06-11-98	1 19980611-4-01 REVISED NOTES. ADDED METRIC & CIRCUIT. S.M. 10-26-05	2 20051006-1-14 TABLE COLUMN REVISED 30 MAX. CURRENT Adc WAS 25 L.E. 01-24-11	B ECO-1924		--TOLERANCES-- Unless Otherwise Specified		Title BUSHING STYLE Pi TYPE EMI FILTER	
DECIMAL ±											
ANGLES ±		Drawn S.M. 02-26-98									
TUSONIX TUCSON, ARIZONA		Approved H.R. 02-26-98						A	4206-023		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[4206-023](#)