

# MC14070B, MC14077B

## CMOS SSI

### Quad Exclusive “OR” and “NOR” Gates

The MC14070B quad exclusive OR gate and the MC14077B quad exclusive NOR gate are constructed with MOS P-channel and N-channel enhancement mode devices in a single monolithic structure. These complementary MOS logic gates find primary use where low power dissipation and/or high noise immunity is desired.

#### Features

- Supply Voltage Range = 3.0 Vdc to 18 Vdc
- All Outputs Buffered
- Capable of Driving Two Low-Power TTL Loads or One Low-Power Schottky TTL Load Over the Rated Temperature Range
- Double Diode Protection on All Inputs
- MC14070B – Replacement for CD4030B and CD4070B Types
- MC14077B – Replacement for CD4077B Type
- NLV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

#### MAXIMUM RATINGS (Voltages Referenced to $V_{SS}$ )

| Symbol               | Parameter                                         | Value                  | Unit |
|----------------------|---------------------------------------------------|------------------------|------|
| $V_{DD}$             | DC Supply Voltage Range                           | -0.5 to +18.0          | V    |
| $V_{in}$ , $V_{out}$ | Input or Output Voltage Range (DC or Transient)   | -0.5 to $V_{DD} + 0.5$ | V    |
| $I_{in}$ , $I_{out}$ | Input or Output Current (DC or Transient) per Pin | $\pm 10$               | mA   |
| $P_D$                | Power Dissipation, per Package (Note 1)           | 500                    | mW   |
| $T_A$                | Ambient Temperature Range                         | -55 to +125            | °C   |
| $T_{stg}$            | Storage Temperature Range                         | -65 to +150            | °C   |
| $T_L$                | Lead Temperature (8-Second Soldering)             | 260                    | °C   |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Temperature Derating: “D/DW” Packages: -7.0 mW/°C From 65°C To 125°C

This device contains protection circuitry to guard against damage due to high static voltages or electric fields. However, precautions must be taken to avoid applications of any voltage higher than maximum rated voltages to this high-impedance circuit. For proper operation,  $V_{in}$  and  $V_{out}$  should be constrained to the range  $V_{SS} \leq (V_{in} \text{ or } V_{out}) \leq V_{DD}$ .

Unused inputs must always be tied to an appropriate logic voltage level (e.g., either  $V_{SS}$  or  $V_{DD}$ ). Unused outputs must be left open.



ON Semiconductor®

<http://onsemi.com>




SOIC-14  
D SUFFIX  
CASE 751A

#### PIN ASSIGNMENT

|                   |   |    |                   |
|-------------------|---|----|-------------------|
| IN 1 <sub>A</sub> | 1 | 14 | $V_{DD}$          |
| IN 2 <sub>A</sub> | 2 | 13 | IN 2 <sub>D</sub> |
| OUT <sub>A</sub>  | 3 | 12 | IN 1 <sub>D</sub> |
| OUT <sub>B</sub>  | 4 | 11 | OUT <sub>D</sub>  |
| IN 1 <sub>B</sub> | 5 | 10 | OUT <sub>C</sub>  |
| IN 2 <sub>B</sub> | 6 | 9  | IN 2 <sub>C</sub> |
| $V_{SS}$          | 7 | 8  | IN 1 <sub>C</sub> |

#### MARKING DIAGRAM





xx = Specific Device Code  
A = Assembly Location  
WL, L = Wafer Lot  
YY, Y = Year  
WW, W = Work Week  
G = Pb-Free Package


#### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 4 of this data sheet.

# MC14070B, MC14077B



**Figure 1. Power Dissipation Test Circuit and Waveform**



**Figure 2. Switching Time Test Circuit and Waveforms**

# MC14070B, MC14077B

## ELECTRICAL CHARACTERISTICS (Voltages Referenced to V<sub>SS</sub>)

| Characteristic                                                                                                                                                                                                                                                                                         | Symbol                                              | V <sub>DD</sub><br>Vdc | -55°C                                                                                                                                                       |      | 25°C  |                 |      | 125°C |      | Unit |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|------|-------|-----------------|------|-------|------|------|
|                                                                                                                                                                                                                                                                                                        |                                                     |                        | Min                                                                                                                                                         | Max  | Min   | Typ<br>(Note 2) | Max  | Min   | Max  |      |
| Output Voltage<br>V <sub>in</sub> = V <sub>DD</sub> or 0                                                                                                                                                                                                                                               | "0" Level<br>V <sub>OL</sub>                        | 5.0                    | –                                                                                                                                                           | 0.05 | –     | 0               | 0.05 | –     | 0.05 | Vdc  |
|                                                                                                                                                                                                                                                                                                        |                                                     | 10                     | –                                                                                                                                                           | 0.05 | –     | 0               | 0.05 | –     | 0.05 |      |
|                                                                                                                                                                                                                                                                                                        |                                                     | 15                     | –                                                                                                                                                           | 0.05 | –     | 0               | 0.05 | –     | 0.05 |      |
|                                                                                                                                                                                                                                                                                                        | "1" Level<br>V <sub>in</sub> = 0 or V <sub>DD</sub> | 5.0                    | 4.95                                                                                                                                                        | –    | 4.95  | 5.0             | –    | 4.95  | –    | Vdc  |
|                                                                                                                                                                                                                                                                                                        |                                                     | 10                     | 9.95                                                                                                                                                        | –    | 9.95  | 10              | –    | 9.95  | –    |      |
|                                                                                                                                                                                                                                                                                                        |                                                     | 15                     | 14.95                                                                                                                                                       | –    | 14.95 | 15              | –    | 14.95 | –    |      |
| Input Voltage<br>(V <sub>O</sub> = 4.5 or 0.5 Vdc)<br>(V <sub>O</sub> = 9.0 or 1.0 Vdc)<br>(V <sub>O</sub> = 13.5 or 1.5 Vdc)                                                                                                                                                                          | "0" Level<br>V <sub>IL</sub>                        | 5.0                    | –                                                                                                                                                           | 1.5  | –     | 2.25            | 1.5  | –     | 1.5  | Vdc  |
|                                                                                                                                                                                                                                                                                                        |                                                     | 10                     | –                                                                                                                                                           | 3.0  | –     | 4.50            | 3.0  | –     | 3.0  |      |
|                                                                                                                                                                                                                                                                                                        |                                                     | 15                     | –                                                                                                                                                           | 4.0  | –     | 6.75            | 4.0  | –     | 4.0  |      |
|                                                                                                                                                                                                                                                                                                        | "1" Level<br>V <sub>IH</sub>                        | 5.0                    | 3.5                                                                                                                                                         | –    | 3.5   | 2.75            | –    | 3.5   | –    | Vdc  |
|                                                                                                                                                                                                                                                                                                        |                                                     | 10                     | 7.0                                                                                                                                                         | –    | 7.0   | 5.50            | –    | 7.0   | –    |      |
|                                                                                                                                                                                                                                                                                                        |                                                     | 15                     | 11                                                                                                                                                          | –    | 11    | 8.25            | –    | 11    | –    |      |
| Output Drive Current<br>(V <sub>OH</sub> = 2.5 Vdc)<br>(V <sub>OH</sub> = 4.6 Vdc)<br>(V <sub>OH</sub> = 9.5 Vdc)<br>(V <sub>OH</sub> = 13.5 Vdc)                                                                                                                                                      | Source<br>I <sub>OH</sub>                           | 5.0                    | –3.0                                                                                                                                                        | –    | –2.4  | –4.2            | –    | –1.7  | –    | mAdc |
|                                                                                                                                                                                                                                                                                                        |                                                     | 5.0                    | –0.64                                                                                                                                                       | –    | –0.51 | –0.88           | –    | –0.36 | –    |      |
|                                                                                                                                                                                                                                                                                                        |                                                     | 10                     | –1.6                                                                                                                                                        | –    | –1.3  | –2.25           | –    | –0.9  | –    |      |
|                                                                                                                                                                                                                                                                                                        |                                                     | 15                     | –4.2                                                                                                                                                        | –    | –3.4  | –8.8            | –    | –2.4  | –    |      |
|                                                                                                                                                                                                                                                                                                        | Sink<br>I <sub>OL</sub>                             | 5.0                    | 0.64                                                                                                                                                        | –    | 0.51  | 0.88            | –    | 0.36  | –    | mAdc |
|                                                                                                                                                                                                                                                                                                        |                                                     | 10                     | 1.6                                                                                                                                                         | –    | 1.3   | 2.25            | –    | 0.9   | –    |      |
|                                                                                                                                                                                                                                                                                                        |                                                     | 15                     | 4.2                                                                                                                                                         | –    | 3.4   | 8.8             | –    | 2.4   | –    |      |
| Input Current                                                                                                                                                                                                                                                                                          | I <sub>in</sub>                                     | 15                     | –                                                                                                                                                           | ±0.1 | –     | ±0.00001        | ±0.1 | –     | ±1.0 | μAdc |
| Input Capacitance<br>(V <sub>in</sub> = 0)                                                                                                                                                                                                                                                             | C <sub>in</sub>                                     | –                      | –                                                                                                                                                           | –    | –     | 5.0             | 7.5  | –     | –    | pF   |
| Quiescent Current<br>(Per Package)                                                                                                                                                                                                                                                                     | I <sub>DD</sub>                                     | 5.0                    | –                                                                                                                                                           | 0.25 | –     | 0.0005          | 0.25 | –     | 7.5  | μAdc |
|                                                                                                                                                                                                                                                                                                        |                                                     | 10                     | –                                                                                                                                                           | 0.5  | –     | 0.0010          | 0.5  | –     | 15   |      |
|                                                                                                                                                                                                                                                                                                        |                                                     | 15                     | –                                                                                                                                                           | 1.0  | –     | 0.0015          | 1.0  | –     | 30   |      |
| Total Supply Current (Notes 3 & 4)<br>(Dynamic plus Quiescent,<br>Per Package)<br>(C <sub>L</sub> = 50 pF on all outputs, all buffers<br>switching)                                                                                                                                                    | I <sub>T</sub>                                      | 5.0<br>10<br>15        | I <sub>T</sub> = (0.3 μA/kHz) f + I <sub>DD</sub><br>I <sub>T</sub> = (0.6 μA/kHz) f + I <sub>DD</sub><br>I <sub>T</sub> = (0.9 μA/kHz) f + I <sub>DD</sub> |      |       |                 |      |       |      | μAdc |
| Output Rise and Fall Times (Note 3)<br>(C <sub>L</sub> = 50 pF)<br>t <sub>TLH</sub> , t <sub>THL</sub> = (1.35 ns/pF) C <sub>L</sub> + 33 ns<br>t <sub>TLH</sub> , t <sub>THL</sub> = (0.60 ns/pF) C <sub>L</sub> + 20 ns<br>t <sub>TLH</sub> , t <sub>THL</sub> = (0.40 ns/pF) C <sub>L</sub> + 20 ns | t <sub>TLH</sub> ,<br>t <sub>THL</sub>              | 5.0                    | –                                                                                                                                                           | –    | –     | 100             | 200  | –     | –    | ns   |
|                                                                                                                                                                                                                                                                                                        |                                                     | 10                     | –                                                                                                                                                           | –    | –     | 50              | 100  | –     | –    |      |
|                                                                                                                                                                                                                                                                                                        |                                                     | 15                     | –                                                                                                                                                           | –    | –     | 40              | 80   | –     | –    |      |
|                                                                                                                                                                                                                                                                                                        |                                                     |                        |                                                                                                                                                             |      |       |                 |      |       |      |      |
| Propagation Delay Times (Note 3)<br>(C <sub>L</sub> = 50 pF)<br>t <sub>PLH</sub> , t <sub>PHL</sub> = (0.90 ns/pF) C <sub>L</sub> + 130 ns<br>t <sub>PLH</sub> , t <sub>PHL</sub> = (0.36 ns/pF) C <sub>L</sub> + 57 ns<br>t <sub>PLH</sub> , t <sub>PHL</sub> = (0.26 ns/pF) C <sub>L</sub> + 37 ns   | t <sub>PLH</sub> ,<br>t <sub>PHL</sub>              | 5.0                    | –                                                                                                                                                           | –    | –     | 175             | 350  | –     | –    | ns   |
|                                                                                                                                                                                                                                                                                                        |                                                     | 10                     | –                                                                                                                                                           | –    | –     | 75              | 150  | –     | –    |      |
|                                                                                                                                                                                                                                                                                                        |                                                     | 15                     | –                                                                                                                                                           | –    | –     | 55              | 110  | –     | –    |      |
|                                                                                                                                                                                                                                                                                                        |                                                     |                        |                                                                                                                                                             |      |       |                 |      |       |      |      |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

2. Data labelled "Typ" is not to be used for design purposes but is intended as an indication of the IC's potential performance.

3. The formulas given are for the typical characteristics only at 25°C.

4. To calculate total supply current at loads other than 50 pF:

$$I_T(C_L) = I_T(50 \text{ pF}) + (C_L - 50) \text{ Vfk}$$

where: I<sub>T</sub> is in μH (per package), C<sub>L</sub> in pF, V = (V<sub>DD</sub> – V<sub>SS</sub>) in volts, f in kHz is input frequency, and k = 0.002.

## MC14070B, MC14077B

### ORDERING INFORMATION

| Device         | Package              | Shipping <sup>†</sup> |
|----------------|----------------------|-----------------------|
| MC14070BDG     | SOIC-14<br>(Pb-Free) | 55 Units / Rail       |
| MC14070BDR2G   | SOIC-14<br>(Pb-Free) | 2500 / Tape & Reel    |
| NLV14070BDR2G* | SOIC-14<br>(Pb-Free) | 2500 / Tape & Reel    |

|                |                      |                    |
|----------------|----------------------|--------------------|
| MC14077BDG     | SOIC-14<br>(Pb-Free) | 55 Units / Rail    |
| MC14077BDR2G   | SOIC-14<br>(Pb-Free) | 2500 / Tape & Reel |
| NLV14077BDR2G* | SOIC-14<br>(Pb-Free) | 2500 / Tape & Reel |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.




\*NLV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable.



SCALE 1:1

SOIC-14 NB  
CASE 751A-03  
ISSUE L

DATE 03 FEB 2016




NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION b DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE PROTRUSION SHALL BE 0.13 TOTAL IN EXCESS OF AT MAXIMUM MATERIAL CONDITION.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD PROTRUSIONS.
5. MAXIMUM MOLD PROTRUSION 0.15 PER SIDE.

| DIM | MILLIMETERS |      | INCHES    |       |
|-----|-------------|------|-----------|-------|
|     | MIN         | MAX  | MIN       | MAX   |
| A   | 1.35        | 1.75 | 0.054     | 0.068 |
| A1  | 0.10        | 0.25 | 0.004     | 0.010 |
| A3  | 0.19        | 0.25 | 0.008     | 0.010 |
| b   | 0.35        | 0.49 | 0.014     | 0.019 |
| D   | 8.55        | 8.75 | 0.337     | 0.344 |
| E   | 3.80        | 4.00 | 0.150     | 0.157 |
| e   | 1.27 BSC    |      | 0.050 BSC |       |
| H   | 5.80        | 6.20 | 0.228     | 0.244 |
| h   | 0.25        | 0.50 | 0.010     | 0.019 |
| L   | 0.40        | 1.25 | 0.016     | 0.049 |
| M   | 0°          | 7°   | 0°        | 7°    |


SOLDERING FOOTPRINT\*



DIMENSIONS: MILLIMETERS

\*For additional information on our Pb-Free strategy and soldering details, please download the onsemi Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

GENERIC  
MARKING DIAGRAM\*



XXXXXX = Specific Device Code  
A = Assembly Location  
WL = Wafer Lot  
Y = Year  
WW = Work Week  
G = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

STYLES ON PAGE 2

|                  |             |                                                                                                                                                                                     |
|------------------|-------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98ASB42565B | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | SOIC-14 NB  | PAGE 1 OF 2                                                                                                                                                                         |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

SOIC-14  
CASE 751A-03  
ISSUE L

DATE 03 FEB 2016

STYLE 1:  
PIN 1. COMMON CATHODE  
2. ANODE/CATHODE  
3. ANODE/CATHODE  
4. NO CONNECTION  
5. ANODE/CATHODE  
6. NO CONNECTION  
7. ANODE/CATHODE  
8. ANODE/CATHODE  
9. ANODE/CATHODE  
10. NO CONNECTION  
11. ANODE/CATHODE  
12. ANODE/CATHODE  
13. NO CONNECTION  
14. COMMON ANODE

STYLE 2:  
CANCELLED

STYLE 3:  
PIN 1. NO CONNECTION  
2. ANODE  
3. ANODE  
4. NO CONNECTION  
5. ANODE  
6. NO CONNECTION  
7. ANODE  
8. ANODE  
9. ANODE  
10. NO CONNECTION  
11. ANODE  
12. ANODE  
13. NO CONNECTION  
14. COMMON CATHODE

STYLE 4:  
PIN 1. NO CONNECTION  
2. CATHODE  
3. CATHODE  
4. NO CONNECTION  
5. CATHODE  
6. NO CONNECTION  
7. CATHODE  
8. CATHODE  
9. CATHODE  
10. NO CONNECTION  
11. CATHODE  
12. CATHODE  
13. NO CONNECTION  
14. COMMON ANODE

STYLE 5:  
PIN 1. COMMON CATHODE  
2. ANODE/CATHODE  
3. ANODE/CATHODE  
4. ANODE/CATHODE  
5. ANODE/CATHODE  
6. NO CONNECTION  
7. COMMON ANODE  
8. COMMON CATHODE  
9. ANODE/CATHODE  
10. ANODE/CATHODE  
11. ANODE/CATHODE  
12. ANODE/CATHODE  
13. NO CONNECTION  
14. COMMON ANODE

STYLE 6:  
PIN 1. CATHODE  
2. CATHODE  
3. CATHODE  
4. CATHODE  
5. CATHODE  
6. CATHODE  
7. CATHODE  
8. ANODE  
9. ANODE  
10. ANODE  
11. ANODE  
12. ANODE  
13. ANODE  
14. ANODE

STYLE 7:  
PIN 1. ANODE/CATHODE  
2. COMMON ANODE  
3. COMMON CATHODE  
4. ANODE/CATHODE  
5. ANODE/CATHODE  
6. ANODE/CATHODE  
7. ANODE/CATHODE  
8. ANODE/CATHODE  
9. ANODE/CATHODE  
10. ANODE/CATHODE  
11. COMMON CATHODE  
12. COMMON ANODE  
13. ANODE/CATHODE  
14. ANODE/CATHODE

STYLE 8:  
PIN 1. COMMON CATHODE  
2. ANODE/CATHODE  
3. ANODE/CATHODE  
4. NO CONNECTION  
5. ANODE/CATHODE  
6. ANODE/CATHODE  
7. COMMON ANODE  
8. COMMON ANODE  
9. ANODE/CATHODE  
10. ANODE/CATHODE  
11. NO CONNECTION  
12. ANODE/CATHODE  
13. ANODE/CATHODE  
14. COMMON CATHODE

|                  |             |                                                                                                                                                                                     |
|------------------|-------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98ASB42565B | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | SOIC-14 NB  | PAGE 2 OF 2                                                                                                                                                                         |

**onsemi** and **onsemi** are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)