




CTS[®]

STANDARD PRODUCTS CATALOG 2007-2008

Clock
Oscillators

Crystals

Termination &
Bias Networks
ClearOne

Leaded
Resistor
Networks

Leadless
Networks &
Chip Arrays

DIP Switches
Surface Mount

DIP Switches
Through Hole

Trimmers &
Heat Sinks

Distributors

EveryWhere. Every Day.

www.ctscorp.com

CLOCK OSCILLATORS





nWave
CP7 Programmable Clock Oscillator



Standard Models	nWave	CB3
Package	5 x 7mm Surface Mount	5 x 7mm Surface Mount
Frequency Range	2.0 to 200 MHz (Programmed by Authorized Distributors)	1.5 to 133 MHz
Tolerance	±.005% (50 PPM)	±.005% (50 PPM)
Operating Temperature	Commercial -20°C to 70°C Industrial -40°C to 85°C	-20°C to 70°C
Duty Cycle	45% to 55%	45% to 55%
Supply Voltage (DC)	2.5 volts ±10% & 3.3 volts ±10%	Std. 5.0 volts ±10%, LV 3.3 volts ±10%
Tristate Option	Output Enable (stand by)	Tri-State
Output Logic	LVC MOS	CMOS/TTL
Standard Packaging	See Packaging Options 8mm Pitch	1000pc Tape & Reel 8mm Pitch
RoHS Compliant	Yes	Yes

EXAMPLE PART NUMBER: CP7032M7680LABK



- YYWW - Date code, YY - year, WW - week.
- XXXXXXX - Frequency marked with 4 significant digits after the 'M'.
- P7VS
P7 - programmable 7x5mm package.
V - voltage/load/output code. (L, N)
S - stability/temperature code. (A, B)
- ** - Programming location identification code - optional.

NOTES


- Termination pads (e4), barrier-plating is nickel (Ni) with gold (Au) flash plate.

STANDARD PART NUMBERS - CB3 (frequencies in bold are most popular)

PART NUMBER*	FREQUENCY (MHz)
CB3-3C-1.5440-T	1.54400
CB3-3C-1.8432-T	1.84320
CB3-3C-3.6864-T	3.68640
CB3-3C-4.0000-T	4.00000
CB3-3C-6.1760-T	6.17600
CB3-3C-7.3728-T	7.37280
CB3-3C-8.0000-T	8.00000
CB3-3C-10.0000-T	10.00000
CB3-3C-12.0000-T	12.00000
CB3-3C-12.2880-T	12.88000
CB3-3C-12.3520-T	12.35200
CB3-3C-14.31818-T	14.31818
CB3-3C-15.3600-T	15.36000
CB3-3C-16.0000-T	16.00000
CB3-3C-16.3840-T	16.38400
CB3-3C-18.4320-T	18.43200
CB3-3C-19.4400-T	19.44000
CB3-3C-20.0000-T	20.00000
CB3-3C-20.4800-T	20.48000
CB3-3C-24.0000-T	24.00000
CB3-3C-24.7040-T	24.70400
CB3-3C-25.0000-T	25.00000
CB3-3C-29.4912-T	29.49120
CB3-3C-30.0000-T	30.00000
CB3-3C-32.0000-T	32.00000
CB3-3C-32.7680-T	32.76800
CB3-3C-33.3330-T	33.33300
CB3-3C-40.0000-T	40.00000
CB3-3C-44.7360-T	44.73600
CB3-3C-45.0000-T	45.00000
CB3-3C-49.1520-T	49.15200
CB3-3C-50.0000-T	50.00000
CB3-3C-51.8400-T	51.84000
CB3-3C-60.0000-T	60.00000
CB3-3C-64.0000-T	64.00000
CB3-3C-66.6666-T	66.66660
CB3-3C-72.0000-T	72.00000
CB3-3C-80.0000-T	80.00000

*For Low Voltage (3.3V) Part, Insert the letters "LV" after CB3 and before the frequency ie: CB3LV-3C-1.5440-T

CLOCK OSCILLATORS



Standard Models	MX045 & MX045HS (Half Size)	636	357 VCX0
Package	14 Pin DIP, 8 Pin DIP (HS)	3.2 x 5mm SMT	5 x 7mm SMT
Frequency Range	1.0 to 105 MHz	1.75 to 75 MHz	1.5 to 52 MHz
Tolerance	±.005% (50 PPM)	±.005% (50 PPM)	±.005% (50 PPM)
Operating Temperature	-20°C to 70°C	-20°C to 70°C	-40°C to 85°C
Duty Cycle	45% to 55%	45% to 55%	45% to 55%
Supply Voltage (DC)	5.0 volts +/-10%	3.3 volts	3.3 volts
Tristate Option	Optional	Tri-State	Tri-State
			APR>100 PPM
Output Logic	CMOS/TTL	CMOS/TTL	HCMOS
Standard Packaging	MX045/MX045T = 50pc Tray MX045HS/MX045HST = 50pc Tray	1000pc Tape & Reel 8mm Pitch	1000pc Tape & Reel 8mm Pitch
RoHS Compliant	Date Code 0540	Yes	Yes

STANDARD PART NUMBERS - MX045 & MX045HS (frequencies in **bold** are most popular)

PART NUMBER MX045	PART NUMBER MX045HS (Half Size)	FREQUENCY (MHz)
MX045-3C-1.0000	MX045HS-3C-1.0000	1.00000
MX045-3C-1.8432	MX045HS-3C-1.8432	1.84320
MX045-3C-2.0000	MX045HS-3C-2.0000	2.00000
MX045-3C-2.4576	MX045HS-3C-2.4576	2.45760
MX045-3C-3.6864	MX045HS-3C-3.6864	3.68640
MX045-3C-4.0000	MX045HS-3C-4.0000	4.00000
MX045-3C-4.9152	MX045HS-3C-4.9152	4.91520
MX045-3C-5.0000	MX045HS-3C-5.0000	5.00000
MX045-3C-5.0688	MX045HS-3C-5.0688	5.06880
MX045-3C-6.0000	MX045HS-3C-6.0000	6.00000
MX045-3C-6.1440	MX045HS-3C-6.1440	6.14400
MX045-3C-7.3728	MX045HS-3C-7.3728	7.37280
MX045-3C-8.0000	MX045HS-3C-8.0000	8.00000
MX045-3C-10.0000	MX045HS-3C-10.0000	10.00000
MX045-3C-12.0000	MX045HS-3C-12.0000	12.00000
MX045-3C-14.31818	MX045HS-3C-14.31818	14.31818
MX045-3C-16.0000	MX045HS-3C-16.0000	16.00000
MX045-3C-18.4320	MX045HS-3C-18.4320	18.43200
MX045-3C-19.6608	MX045HS-3C-19.6608	19.66080
MX045-3C-20.0000	MX045HS-3C-20.0000	20.00000
MX045-3C-24.0000	MX045HS-3C-24.0000	24.00000
MX045-3C-25.0000	MX045HS-3C-25.0000	25.00000
MX045-3C-25.1750	MX045HS-3C-25.1750	25.17500
MX045-3C-28.3220	MX045HS-3C-28.3220	28.32200
MX045-3C-32.0000	MX045HS-3C-32.0000	32.00000
MX045-3C-40.0000	MX045HS-3C-40.0000	40.00000
MX045-3C-50.0000	MX045HS-3C-50.0000	50.00000
MX045-3C-64.0000	MX045HS-3C-64.0000	64.00000
MX045-3C-66.66666	MX045HS-3C-66.66666	66.66666
MX045-3C-80.0000	MX045HS-3C-80.0000	80.00000

STANDARD PART NUMBERS - 636

PART NUMBER*	FREQUENCY (MHz)
636L3C014M31818	14.31818
636L3C014M74560	14.74560
636L3C016M00000	16.00000
636L3C016M38400	16.38400
636L3C018M43200	18.43200
636L3C020M00000	20.00000
636L3C020M48000	20.48000
636L3C024M00000	24.00000
636L3C025M00000	25.00000
636L3C032M76800	32.76800
636L3C033M00000	33.00000
636L3C044M00000	44.00000
636L3C048M00000	48.00000


STANDARD PART NUMBERS - 357

PART NUMBER*	FREQUENCY (MHz)
357LB3I001M5440	1.5540
357LB3I004M0960	4.0960
357LB3I006M1760	6.1760
357LB3I016M3840	16.3840
357LB3I019M4400	19.4400
357LB3I020M0000	20.0000
357LB3I027M0000	27.0000
357LB3I032M7680	32.7680
357LB3I035M3280	35.3280
357LB3I038M8800	38.8800
357LB3I040M0000	40.0000
357LB3I044M7360	44.7360

*For Tri-State Output, Insert the letter "T"
after MX045 and before the Frequency ie: MX045T-3C-1.0000

Many Other Frequencies Available upon request.

SMD CRYSTALS



Models	MODEL 403	MODEL 405	MODEL 406
Package	2.5 x 3.2 x 0.8mm	3.2 x 5 x 0.9mm	3.5 x 6 x 1.2mm
Frequency Range	13 TO 50 MHz	11 TO 44 MHz	8 TO 50 MHz
Frequency Tolerance @25°C	403C35 = +/- 30ppm 403C11 = +/- 10ppm	+/- 30ppm	+/- 30ppm
Frequency Stability	403C35 = +/- 50ppm 403C11 = +/- 10ppm	+/- 50ppm	+/- 50ppm
Operating Temperature	-20°C to +70°C	-20°C to +70°C	-20°C to +70°C
Aging	<5ppm per year	<5ppm per year	<5ppm per year
ESR	50 to 90 Ohms (frequency dependent)	Max 50 Ohms	40 to 0hms (frequency dependent)
Load Capacitance	20 pF	13 pF	13pF
Standard Packaging	1000pc Tape & Reel	1000pc Tape & Reel	1000pc Tape & Reel
RoHS Compliant	Yes	Yes	Yes

STANDARD PART NUMBERS - 403

PART NUMBER*	FREQUENCY (MHz)
403C35E13M00000	13.00000
403C11E16M00000	16.00000
403C35E26M00000	26.00000
403C35E27M00000	27.00000
403C11E32M00000	32.00000

STANDARD PART NUMBERS - 405

PART NUMBER*	FREQUENCY (MHz)
405C35B11M05920	11.05920
405C35B12M00000	12.00000
405C35B12M80000	12.80000
405C35B13M00000	13.00000
405C35B14M31818	14.31818
405C35B14M40000	14.40000
405C35B14M74560	14.74560
405C35B15M36000	15.36000
405C35B16M00000	16.00000
405C35B16M36800	16.36800
405C35B19M20000	19.20000
405C35B19M68000	19.68000
405C35B20M00000	20.00000
405C35B24M00000	24.00000
405C35B25M00000	25.00000
405C35B26M00000	26.00000
405C35B32M00000	32.00000
405C35B33M00000	33.00000
405C35B40M00000	40.00000
405C35B44M00000	44.00000

STANDARD PART NUMBERS - 406

PART NUMBER*	FREQUENCY (MHz)
406C35B10M00000	10.00000
406C35B10M24500	10.24500
406C35B12M28800	12.28800
406C35B12M68800	12.68800
406C35B13M00000	13.00000
406C35B13M22500	13.22500
406C35B14M00000	14.00000
406C35B14M31818	14.31818
406C35B14M85000	14.85000
406C35B18M43200	18.43200
406C35B19M44000	19.44000
406C35B20M48000	20.48000
406C35B22M00000	22.00000
406C35B24M57600	24.57600
406C35B27M00000	27.00000
406C35B30M00000	30.00000
406C35B32M76800	32.76800
406C35B35M32800	35.32800
406C35B38M88000	38.88000
406C35B44M54500	44.54500
406C35B48M00000	48.00000

CRYSTALS



Models	ATS	MP-MICROPROCESSOR
Package	HC/49U/S & Surface Mount	HC/49U
Frequency Range	3.5 to 40 MHz	1.8 TO 48 MHz
Frequency Tolerance @25°C	+/- 30ppm	+/- 50ppm
Frequency Stability	+/- 50ppm	+/- 50ppm
Operating Temperature	-20°C to + 70°C	-20°C to + 70°C
Aging	<5ppm per year	<10ppm per year
ESR	40 to 150 Ohms (frequency dependent)	35 to 750 Ohms (frequency dependent)
Load Capacitance	See Frequency Table	See Frequency Table
Standard Packaging	SM 1000pc T&R / 100pc Bulk	100pc Bulk
RoHS Compliant	Date Code 0514	Date Code 0514

STANDARD PART NUMBERS - ATS
(frequencies in **bold** are most popular)


PART NUMBER	FREQUENCY (MHz)	LOAD/SERIES
ATS036	3.57955	18pF
ATS036SM	3.57955	18pF
ATS036SM-1	3.57955	18pF
ATS037	3.68640	20pF
ATS037SM	3.68640	20pF
ATS037SM-1	3.68640	20pF
ATS040	4.00000	20pF
ATS040SM	4.00000	20pF
ATS040SM-1	4.00000	20pF
ATS042	4.91520	20pF
ATS042SM	4.91520	20pF
ATS042SM-1	4.91520	20pF
ATS050	5.06880	20pF
ATS050SM	5.06880	20pF
ATS050SM-1	5.06880	20pF
ATS060	6.00000	20pF
ATS060SM	6.00000	20pF
ATS060SM-1	6.00000	20pF
ATS08A	8.00000	20pF
ATS08ASM	8.00000	20pF
ATS08ASM-1	8.00000	20pF
ATS098	9.83040	20pF
ATS098SM	9.83040	20pF
ATS098SM-1	9.83040	20pF
ATS100	10.00000	Series
ATS100SM	10.00000	Series
ATS100SM-1	10.00000	Series
ATS111	11.05920	20pF

STANDARD PART NUMBERS -MP CRYSTALS
(frequencies in **bold** are most popular)

PART NUMBER	FREQUENCY (MHz)	LOAD/SERIES
MP018S	1.84320	13pF
MP020S	2.00000	20pF
MP024S	2.45760	32pF
MP036S	3.57955	18pF
MP037	3.68640	20pF
MP040	4.00000	20pF
MP04A	4.00000	Series
MP041	4.19430	12pF
MP042	4.91520	20pF
MP05A	5.00000	20pF
MP05B	5.00000	Series
MP050	5.06880	Series
MP060	6.00000	20pF
MP061	6.14400	20pF
MP073	7.37280	Series
MP080	8.00000	Series
MP080A	8.00000	20pF
MP098	9.83040	20pF
MP100	10.00000	Series
MP101	10.00000	30pF
MP107	10.73864	32pF
MP110	11.00000	18pF
MP111	11.05920	Series
MP120	12.00000	Series
MP122	12.28800	32pF
MP143	14.31818	Series
MP147	14.74560	Series
MP150	15.00000	Series
MP160	16.00000	Series
MP184	18.43200	Series
MP196	19.66080	Series
MP200	20.00000	Series
MP221	22.11840	Series
MP240	24.00000	Series
MP245	24.57600	Series
MP250	25.00000	Series


Many Other Frequencies Available upon request.

"-1" Indicates Tape & Reel (could also be indicated with a "T")




ClearONE® RT


STYLE C




STYLE D




STYLE E




STYLE F



STYLE G



STYLE H



ClearONE® RT Series Standard Part Numbers - Additional designs available upon request

Application	Standard Part No. 1.27 mm Pitch	Standard Part No. 1.00 mm Pitch	RoHS Part No. 1.27 mm Pitch	RoHS Part No. 1.00 mm Pitch	Style	Array Size	Bits	R1Ω	R2Ω
DDR SDRAM	RT 1400 B6	RT 1400 B7	RT 2400 B6	RT 2400 B7	H	3 X 9	9	50	25
	RT 1401 B6	RT 1401 B7	RT 2401 B6	RT 2401 B7	H	3 X 9	9	25	22
	RT 1402 B6	RT 1402 B7	RT 2402 B6	RT 2402 B7	F	3 X 9	9	50	-
	RT 1403 B6	RT 1403 B7	RT 2403 B6	RT 2403 B7	F	3 X 9	9	25	-
	RT 1404 B6	RT 1404 B7	RT 2404 B6	RT 2404 B7	C	4 X 9	9	25	-
	RT 1405 B6	RT 1405 B7	RT 2405 B6	RT 2405 B7	C	4 X 9	9	22	-
	RT 1407 B6	RT 1407 B7	RT 2407 B6	RT 2407 B7	F	3 X 9	9	35	-
	RT 1408 B6	RT 1408 B7	RT 2408 B6	RT 2408 B7	H	3 X 9	9	60	25
	RT 1430 B6	RT 1430 B7	RT 2430 B6	RT 2430 B7	F	3 X 9	9	60	-
	RT 1432 B6	RT 1432 B7	RT 2432 B6	RT 2432 B7	F	3 X 9	9	120	-
	RT 1460 B6	RT 1460 B7	RT 2460 B6	RT 2460 B7	C	4 X 9	9	50	-
	RT 1463 B6	RT 1463 B7	RT 2463 B6	RT 2463 B7	C	4 X 9	9	33	-
LVD SCSI	RT 1465 B6	RT 1465 B7	RT 2465 B6	RT 2465 B7	C	4 X 9	9	47	-
	RT 1300 B6	-	RT 2300 B6	-	E	4 X 9	9	475	121
COMPACT PCI, MEMORY & IDE	-	RT 1200 B7	-	RT 2200 B7	C	4 X 8	16	10	-
	-	RT 1201 B7	-	RT 2201 B7	C	4 X 16	32	10	-
	-	RT 1202 B7	-	RT 2202 B7	C	4 X 8	16	33	-
	-	RT 1232 B7	-	RT 2232 B7	C	4 X 8	16	22	-
	-	RT 1233 B7	-	RT 2233 B7	C	4 X 8	16	25	-
	-	RT 1235 B7	-	RT 2235 B7	C	4 X 8	16	50	-
	-	RT 1203 B7	-	RT 2203 B7	C	4 X 16	32	33	-
	-	RT 1205 B7	-	RT 2205 B7	C	4 X 16	32	50	-
PCI & PCI-X	-	RT 1236 B7	-	RT 2236 B7	C	4 X 16	32	100	-
	RT 1415 B6	RT 1415 B7	RT 2415 B6	RT 2415 B7	F	3 X 4	8	4.7K	-
	RT 1416 B6	RT 1416 B7	RT 2416 B6	RT 2416 B7	F	3 X 4	8	8.2K	-
	RT 1417 B6	RT 1417 B7	RT 2417 B6	RT 2417 B7	F	3 X 8	16	4.7K	-
	RT 1418 B6	RT 1418 B7	RT 2418 B6	RT 2418 B7	F	3 X 8	16	8.2K	-
GTL, GTL+ & AGTL+	RT 1450 B6	-	RT 2450 B6	-	D	3 X 3	8	25	-
	RT 1451 B6	-	RT 2451 B6	-	D	3 X 6	16	25	-
	RT 1452 B6	-	RT 2452 B6	-	D	3 X 12	32	25	-
	RT 1453 B6	-	RT 2453 B6	-	D	3 X 3	8	56	-
	RT 1454 B6	-	RT 2454 B6	-	D	3 X 6	16	56	-
	RT 1427 B6	-	RT 2427 B6	-	D	3 X 12	32	56	-
	RT 1410 B6	-	RT 2410 B6	-	D	3 X 3	8	150	-
	RT 1411 B6	-	RT 2411 B6	-	D	3 X 6	16	150	-
	RT 1412 B6	RT 1412 B7	RT 2412 B6	RT 2412 B7	D	3 X 12	32	150	-
VME64 & LVPECL	-	RT 1210 B7	-	RT 2210 B7	G	3 X 8	8	330	470
	-	RT 1211 B7	-	RT 2211 B7	G	3 X 8	8	220	1800
	RT 1250 B6	RT 1250 B7	RT 2250 B6	RT 2250 B7	G	3 X 8	8	127	8.25

ClearONE® RT Series Operating Temperature Range: -55°C to +125°C




ClearONE® RC


ClearONE® RC Series Standard Part Numbers

Application	1.27 mm Pitch Part No.	1.00 mm Pitch Part No.	Style	Array Size	R1 Ω	R1 Tol.	C1	C1 Tol.	Diel.	DF	Operating Temperature
Line Filter & Termination	-	RC 3002 B7	K	3 X 9	50	$\pm 1\%$	0.1uf	$\pm 10\%$	X5R	5% MAX.	-55°C TO +85°C
	RC 3005 B6	-	L	4 X 9	50	$\pm 1\%$	0.1uf	$\pm 10\%$	X5R	5% MAX.	-55°C TO +85°C
	RC 3007 B6	-	J	3 X 9	50	$\pm 1\%$	100pf	$\pm 10\%$	NPO	2.5% MAX.	-55°C TO +125°C
	RC 3008 B6	RC 3008 B7	J	3 X 9	50	$\pm 1\%$	33pf	$\pm 10\%$	NPO	2.5% MAX.	-55°C TO +125°C


STYLE J



STYLE K




STYLE L




Mechanical Outline

RT Series



RC Series



1.27 mm Pitch Package (B6 suffix)			
	mm	inch	
P	1.27 $\pm$ 0.25	.050 $\pm$.010	
D	0.76 $\pm$ 0.25	.030 $\pm$.002	
K	0.64 $\pm$ 0.25	.025 $\pm$.010	
H	1.32 $\pm$ 0.25	.052 $\pm$.006	
H (RC)	2.03 MAX.	.080 MAX.	
Array Size	L	W	
3x3	mm	3.81 $\pm$ 0.15	3.81 $\pm$ 0.15
	inch	.150 $\pm$.006	.150 $\pm$.006
3x4	mm	5.08 $\pm$ 0.15	3.81 $\pm$ 0.15
	inch	.200 $\pm$.006	.150 $\pm$.006
3x6	mm	7.62 $\pm$ 0.15	3.81 $\pm$ 0.15
	inch	.300 $\pm$.006	.150 $\pm$.006
3x8	mm	10.16 $\pm$ 0.15	3.81 $\pm$ 0.15
	inch	.400 $\pm$.006	.150 $\pm$.006
3x9	mm	11.43 $\pm$ 0.15	3.81 $\pm$ 0.15
	inch	.450 $\pm$.006	.150 $\pm$.006
3x12	mm	15.24 $\pm$ 0.15	3.81 $\pm$ 0.15
	inch	.600 $\pm$.006	.150 $\pm$.006
4x9	mm	11.43 $\pm$ 0.15	5.08 $\pm$ 0.15
	inch	.450 $\pm$.006	.200 $\pm$.006

1.00 mm Pitch Package (B7 suffix)			
	mm	inch	
P	1.00 $\pm$ 0.25	.039 $\pm$.010	
D	0.64 $\pm$ 0.25	.025 $\pm$.002	
K	0.50 $\pm$ 0.25	.020 $\pm$.010	
H	1.19 $\pm$ 0.15	.047 $\pm$.006	
H (RC)	1.83 MAX.	.072 MAX.	
Array Size	L	W	
3x4	mm	4.00 $\pm$ 0.15	3.00 $\pm$ 0.15
	inch	.157 $\pm$.006	.118 $\pm$.006
3x8	mm	8.00 $\pm$ 0.15	3.00 $\pm$ 0.15
	inch	.315 $\pm$.006	.118 $\pm$.006
3x9	mm	9.00 $\pm$ 0.15	3.00 $\pm$ 0.15
	inch	.354 $\pm$.006	.118 $\pm$.006
3x12	mm	12.00 $\pm$ 0.15	3.00 $\pm$ 0.15
	inch	.472 $\pm$.006	.118 $\pm$.006
4x8	mm	8.00 $\pm$ 0.15	4.00 $\pm$ 0.15
	inch	.315 $\pm$.006	.157 $\pm$.006
4x9	mm	9.00 $\pm$ 0.15	4.00 $\pm$ 0.15
	inch	.354 $\pm$.006	.157 $\pm$.006
4x16	mm	16.00 $\pm$ 0.15	4.00 $\pm$ 0.15
	inch	.630 $\pm$.006	.157 $\pm$.006


Tape and Reel Packaging

Suffix	RT Series TR7	RT Series TR13	RC Series TR7	RC Series TR13
Tape Width	24mm	24mm	24mm	24mm
Carrier Pitch	8mm	8mm	8mm	8mm
Reel Diameter	7 inch	13 inch	7 inch	13 inch
Parts/Reel	1,000	4,000	750	3,000


(Bulk Packaging Not Available)

Part Number Coding

7 inch reel, Add **TR7** to part number. Example: RT1200B7**TR7**
13 inch reel, Add **TR13** to part number. Example: RT1200B7**TR13**



SURFACE MOUNT



	Narrow Body, Small Outline		Medium Body		Medium Body, Low Profile		
SERIES	766		767		768		
Termination Leads/Pins	14	16	14	16	14	16	20
Type	Flat		Flat		Flat		
Dimensions: Inches (mm)							
Center	.050 (1.27)		.050 (1.27)		.050 (1.27)		
Length	.340 (8.65)	.390 (9.90)	.390 (9.91)	.440 (11.18)	.390(9.91)	.440(11.18)	.540(13.70)
Width	.154 (3.90)		.220 (5.59)		.220 (5.59)		
Height	.061 (1.55)		.085 (2.16)		.063 (1.60)		
Resistance: Range, Ohms	10 Ω to 1 Meg Ω		10 Ω to 1 Meg Ω		10 Ω to 1 Meg Ω		
Tolerance	±2%		±2%		±2%		
Temperature Coefficient,ppm/°C	100 Ω to 1 Meg ± 100ppm/°C Typical		100 Ω to 1 Meg ± 100ppm/°C Typical		100 Ω to 1 Meg ± 100ppm/°C Typical		
Maximum Operating Voltage	50V		50V		50V		
Power Rating (Total Network Power)							
@70°C	1.0W	1.2W	1.3W	1.5W	1.3W	1.5W	2.0W
@25°C	1.6W	1.8W	2.0W	2.3W	2.0W	2.3W	3.0W
Operating Temperature Range	-55°C to +125°C		-55°C to +125°C		-55°C to +125°C		
Dielectric Strength	100V		100V		100V		
Packaging/Parts per Reel	TR7=800 pcs		TR13=3,000 pcs		TR13=2,000 pcs		

STANDARD RESISTOR VALUES & CODE (1 & 3 SCHEMATICS) FOR 766, 767 & 768 ±2% TOLERANCE "G" SUFFIX (22 Ω AND UP) * ±5% TOLERANCE "J" SUFFIX (LESS THAN 22 Ω) ONLY

OHMS	CODE	OHMS	CODE	OHMS	CODE	OHMS	CODE	OHMS	CODE
10*	100	100	101	1200	122	12000	123	120000	124
12*	120	110	111	1500	152	15000	153	150000	154
15*	150	120	121	1800	182	18000	183	180000	184
18*	180	150	151	2000	202	20000	203	200000	204
22	220	180	181	2200	222	22000	223	220000	224
27	270	200	201	2700	272	27000	273	270000	274
33	330	220	221	3300	332	33000	333	330000	334
39	390	270	271	3900	392	39000	393	390000	394
47	470	330	331	4700	472	47000	473	470000	474
51	510	390	391	5100	512	56000	563	560000	564
56	560	470	471	5600	562	68000	683	680000	684
68	680	510	511	6800	682	82000	823	820000	824
82	820	560	561	8200	822	100000	104	1000000	105
		680	681	10000	103				
		820	821						
		1000	102						

DUAL TERMINATOR VALUES & CODE (5 SCHEMATIC)

Ohm	Eq.Re	Code
180/390	120	121A
220/330	130	131A
330/390	180	181A
330/470	190	191A

Note:
Other Values Available On Request:
All 5 schematics are
±2% Resistance Tolerance

PART NUMBER EXAMPLE: 767143101GPTR13

767	14	3	101	G	P	TR13
Series	Number of Pins	Schematic	Resistor Code	Tolerance	RoHS	Packaging
766 767 768	14 16 20* *Series 768 only	1 = Bussed Resistors 3 = Isolated Resistors 5 = Dual Terminator	(see Resistance Value Code above)	1 & 3 J = ± 5% G = ± 2%	RoHS Part Numbers are Standard	TR = Tape & Reel SP = Slide Pack For 766 Specify TR7 = 7" Reel TR13 = 13" Reel

THROUGH-HOLE



	Conformal Coated SIP		
SERIES	770		
Termination Leads/Pins	6	8	10
Type	Flat Copper Alloy Leads		
Dimensions: Inches (mm)			
Center	.100 (2.54)		
Length	.598 (15.19)	.798 (20.27)	.998 (25.35)
Width	.095 (2.41) Max.		
Height	.195 (4.95) Max		
Resistance: Range, Ohms	22Ω to 1MegΩ		
Tolerance	±2%		
Temperature Coefficient,ppm/°C	100Ωto1MegΩ +100ppm/°C Typical		
Maximum Operating Voltage	100V		
Power Rating (Total Network Power)			
@70°C	0.64W	0.88W	1.11W
@25°C	0.96W	1.32W	1.66W
Operating Temperature Range	-55°C to +125°C		
Dielectric Strength	100V		
Packaging/Parts per Reel	Bulk Pack = 250 parts/bag		

STANDARD RESISTOR VALUES & CODE (1 & 3 SCHEMATICS) FOR 770 ± 2% TOLERANCE

OHMS	CODE	OHMS	CODE	OHMS	CODE	OHMS	CODE
22.....	220	270.....	271	3900.....	392	56000.....	563
27.....	270	330.....	331	4700.....	472	68000.....	683
33.....	330	390.....	391	5100.....	512	82000.....	823
39.....	390	470.....	471	5600.....	562	100000.....	104
47.....	470	510.....	511	6800.....	682	120000.....	124
51.....	510	560.....	561	8200.....	822	150000.....	154
56.....	560	680.....	681	10000.....	103	180000.....	184
68.....	680	820.....	821	12000.....	123	220000.....	224
82.....	820	1000.....	102	15000.....	153	270000.....	274
100.....	101	1200.....	122	18000.....	183	330000.....	334
110.....	111	1500.....	152	20000.....	203	390000.....	394
120.....	121	1800.....	182	22000.....	223	470000.....	474
150.....	151	2000.....	202	27000.....	273	560000.....	564
180.....	181	2200.....	222	33000.....	333	680000.....	684
200.....	201	2700.....	272	39000.....	393	820000.....	824
220.....	221	3300.....	332	47000.....	473	1000000.....	105



DUAL TERMINATOR VALUES & CODE (5 SCHEMATIC)

81/130
121/195
162/260
180/390
220/330
330/390
330/470

PART NUMBER EXAMPLE: 770103103P

770	10	3	103	P
Series 770	Number of Leads 6 8 10	Circuit Type 1 = Bussed Resistors 3 = Isolated Resistors 5 = Dual Terminators	Resistance Code First 2 digits are significant. Third digit represents the number of trailing Zeros. Dual Terminator per value, e.g. 220/330	RoHS RoHS Part Numbers are Standard

LEADLESS NETWORKS



	Single Row Termination				Dual Row Termination				Single Row Termination				Dual Row Termination			
SERIES	752				752				753				753			
Termination: Pads (Resistors)	8	9	10	12	16	18	20	24	8	9	10	12	16	18	20	24
Type: C=Concave, X=Convex																
Dimensions: Inches (mm)																
Pitch	.050 (1.27)				.050 (1.27)				.025 (0.64)				.025 (0.64)			
Length	.465	.515	.565	.665	.465	.515	.565	.665	.245	.270	.295	.345	.245	.270	.295	.345
	(11.81)	(13.08)	(14.35)	(16.89)	(11.81)	(13.08)	(14.35)	(16.89)	(6.22)	(6.86)	(7.49)	(8.76)	(6.22)	(6.86)	(7.49)	(8.76)
Width	.080 (2.03)				.080 (2.03)				.080 (2.03)				.080 (2.03)			
Height	.095 (2.41)				.095 (2.41)				.095 (2.41)				.095 (2.41)			
Resistance: Range, Ohms	10Ω to 1MegΩ				10Ω to 1MegΩ				10Ω to 1MegΩ				10Ω to 1MegΩ			
Tolerance	±2%				±2%				±2%				±2%			
TCR ppm/°C	±200ppm/°C Typical				±200ppm/°C Typical				±200ppm/°C Typical				±200ppm/°C Typical			
Maximum Operating Voltage	25V				25V				25V				25V			
Power Rating (Per Resistor)																
@ 70°C	0.8W	.085W	0.9W	1.1W	0.9W	.095W	1.0W	1.3W	0.40W	.043W	0.45W	0.55W	0.40W	.043W	0.45W	0.55W
@ 25°C	1.2W	1.3W	1.4W	1.7W	1.4W	1.5W	1.6W	2.0W	0.60W	0.64W	0.68W	0.82W	0.60W	0.64W	0.68W	0.82W
Operating Temperature Range	-55° C to +125° C				-55° C to +125° C				-55° C to +125° C				-55° C to +125° C			
Dielectric Strength	100V				100V				100V				100V			
Packaging/Parts per Reel	TR7 = 1,000 pcs				TR7 = 1,000 pcs				TR7 = 1,000 pcs				TR7 = 1,000 pcs			
Packaging Bulk Plastic Bag	250				250				250				250			

STANDARD RESISTOR VALUES & CODE (1 & 3 SCHEMATICS) FOR 752 & 753

±2% TOLERANCE "G" SUFFIX (22 Ω AND UP) *±5% TOLERANCE "J" SUFFIX (LESS THAN 22 Ω) ONLY

OHMS	CODE	OHMS	CODE	OHMS	CODE	OHMS	CODE	OHMS	CODE
10*	100	110	111	1000	102	10000	103	120000	124
12*	120	120	121	1200	122	12000	123	150000	154
15*	150	150	151	1500	152	15000	153	180000	184
18*	180	180	181	1800	182	18000	183	200000	204
22	220	200	201	2000	202	20000	203	220000	224
27	270	220	221	2200	222	22000	223	270000	274
33	330	270	271	2700	272	27000	273	330000	334
39	390	330	331	3300	332	33000	333	390000	394
47	470	390	391	3900	392	39000	393	470000	474
51	510	470	471	4700	472	47000	473	560000	564
56	560	510	511	5100	512	56000	563	680000	684
68	680	560	561	5600	562	68000	683	820000	824
82	820	680	681	6800	682	82000	823	1000000	105
100	101	820	821	8200	822	100000	104		

DUAL TERMINATOR VALUES & CODE (5 SCHEMATIC)

Ohm	Eq.Re	Code
180/390	120	121A
220/330	130	131A
330/390	180	181A
330/470	190	191A
162/260	100	101B
81/130	50	500A

Note:
Other Values Available On Request:
All 5 schematics are
±2% Resistance Tolerance

PART NUMBER EXAMPLE: 752163101GPTR7

752	16	3	101	G	P	TR7
Series	Input/Outputs SRT DRT	Schematic	Resistor Code (see Resistance Value Code above)	Tolerance	RoHS RoHS Part Numbers are Standard	Packaging TR7 = Tape & Reel
752 753	08 16 09 18 10 20 12 24	1 = Bussed Resistors 3 = Isolated Resistors 5 = Dual Terminator		1 & 3 J = ± 5% G = ± 2%		

CHIP ARRAYS

	Chip Resistor Array			Chip Resistor Array			Chip Resistor Array		Chip Resistor Array		Chip Resistor Array	Chip Resistor Array
	741			742			743		744		745	746
	4(2)	8(4)	16(8)	4(2)	8(4)	4(2)	4(2)	8(4)	4(2)	8(4)	10(8)	10(8)
	X	C, X	X	C	C, X	C	C		C		C or X	X
	.026(.65)	.020(.50)		.032 (.80)			.050 (1.27)		.050 (1.27)		.050 (1.27)	.025 (.64)
	.039	.079	.150	.063	.126	.252	.100	.200	.100	.200	.252	.130
	(1.00)	(2.00)	(3.80)	(1.60)	(3.20)	(6.40)	(2.54)	(5.08)	(2.54)	(5.08)	(6.40)	(3.30)
	.039(1.0)		.063(1.60)	.063 (1.60)			.079 (2.00)		.126 (3.20)		.126 (3.20)	.065 (1.65)
	.014(.35)		.018(.45)	.024 (.60)			.024 (.60)		.024 (.60)		.024 (.60)	.024 (.60)
	10Ω to 1MegΩ			10Ω to 1MegΩ			10Ω to 1MegΩ		10Ω to 1MegΩ		33Ω to 470KΩ	33Ω to 100KΩ
	±5%			±5%			±5%		±5%		±5%	±5%
	±200ppm/°C			±200ppm/°C			±200ppm/°C		±200ppm/°C		±200ppm/°C	±200ppm/°C
	25V			50V			100V		200V		50V	25V
	.063W			.063W			.100W		.125W		.063W	.031W
	-55° C to +125°C			-55° C to +125°C			-55° C to +125°C		-55° C to +125°C		-55° C to +125°C	-55° C to +125°C
	10,000		5,000	5,000	4,000		4,000		4,000		4,000	5,000

STANDARD RESISTOR VALUES & CODE FOR SERIES 741, 742, 743, 744, 745, & 746

OHMS	CODE	OHMS	CODE	OHMS	CODE	OHMS	CODE	OHMS	CODE
0.....000X		82.....820		820.....821		8.2K.....822		82K.....823	
10.....100		100.....101		1K.....102		10K.....103		100K.....104	
12.....120		110.....111		1.2K.....122		12K.....123		120K.....124	
15.....150		120.....121		1.5K.....152		15K.....153		150K.....154	
18.....180		150.....151		1.8K.....182		18K.....183		180K.....184	
22.....220		180.....181		2.2K.....222		22K.....223		220K.....224	
27.....270		220.....221		2.7K.....272		27K.....273		270K.....274	
33.....330		270.....271		3.3K.....332		33K.....333		330K.....334	
39.....390		330.....331		3.9K.....392		39K.....393		390K.....394	
47.....470		390.....391		4.7K.....472		47K.....473		470K.....474	
51.....510		470.....471		5.1K.....512		51K.....513		510K.....514	
56.....560		510.....511		5.6K.....562		56K.....563		560K.....564	
68.....680		560.....561		6.8K.....682		68K.....683		680K.....684	
75.....750		680.....681						820K.....824	
								1M.....105	

NOTE:

Series 745
33Ω to 470KΩ
Series 746
33Ω to 100KΩ

PART NUMBER EXAMPLE: 742C043101JP

742	C	04	3	101	J	P
Series	Termination	No. Terminations	Schematic	Resistor Code	Tolerance	RoHS
741 742 743 744 745 746	C = Concave X = Convex	04 08 16 (741 & 742 only) 10 (745 & 746 only)	1 = Bussed (745 & 746 only) 3 = (741, 742, 743 & 744)	(see Resistance Value Code above)	J = ± 5%	RoHS Part Numbers are Standard



	Side Actuated Gull Wing	Side Actuated Gull Wing
SERIES	193	204
Positions	2 - 10 & 12	2 - 10 & 12
Initial Contact Resistance	50 Milliohms Max.	50 Milliohms Max.
Maximum Contact Resistance	100 Milliohms after 7,000 Cycles	100 Milliohms after 10,000 Cycles
Maximum Non-switching Rating	100 mA or 50 VDC	100 mA or 50 VDC
Insulation Resistance	1,000 Megaohms	1,000 Megaohms
Dielectric Breakdown	Min.: 500 VAC	Min.: 500 VAC
Switch Capacitance	Max.: 5.0 pF	Max.: 5.0 pF
Shock Mil-Std. 202F	No Damage with 25G Applied	< 1 microsecond
Vibration Mil-Std. 202F	No Damage at 60 Hz Constant Vibration	< 1 microsecond
Type of Actuation	Side Actuated	Slide (Top Actuated)
Circuitry Available	SPST	SPST; SPDT; 4PST; DPST; DPDT
Terminal Configuration	Gull Wing	Gull Wing
Dimensions: inches (mm)		
Length	"A" Dim. (See Table Below)	"A" Dim. (See Table Below)
Width	.410 (10.414)	.410* (10.414)
Height	.359 (9.12)	.359 (9.12)
Lead Centers	.100 (2.54)	.100 (2.54)
Contact Plating/Terminal Plating	Gold/Tin	Gold/Tin
Operating Temperature	-40° to +85°C	-55° to +85°C
Options:		
Bottom & Top Sealed	Bottom Seal Only Standard	Available
Low Profile Actuator	-	Available on SPST and SPDT
RoHS Compliant	Since June 2006	Since June 2006

* Gull Wing Terminal To Terminal

STANDARD PART NUMBERS FOR 193

"A" Overall Dimension	Number of Switch Sections	Series 193 Part Number
.286 (7.26)	2	193-2MS
.386 (9.80)	3	193-3MS
.486 (12.34)	4	193-4MS
.586 (14.88)	5	193-5MS
.686 (17.42)	6	193-6MS
.786 (19.96)	7	193-7MS
.886 (22.50)	8	193-8MS
.986 (25.04)	9	193-9MS
1.086 (27.58)	10	193-10MS
1.286 (32.66)	12	193-12MS

For Tape & Reel Add "R" to End of P/N
 EXAMPLE: 193-2MSR
 Even sizes only.

STANDARD PART NUMBERS FOR 204

"A" Overall Dimension	Number of Switch Sections	Actuation	Part Number	Both Bottom & Top Sealed	Low Profile Both Bottom & Top Sealed
.286 (7.26)	2	SPST	204-2	204-2ST	204-2LPST
.386 (9.80)	3	SPST	204-3	204-3ST	204-3LPST
.486 (12.34)	4	SPST	204-4	204-4ST	204-4LPST
.586 (14.88)	5	SPST	204-5	204-5ST	204-5LPST
.686 (17.42)	6	SPST	204-6	204-6ST	204-6LPST
.786 (19.96)	7	SPST	204-7	204-7ST	204-7LPST
.886 (22.50)	8	SPST	204-8	204-8ST	204-8LPST
.986 (25.04)	9	SPST	204-9	204-9ST	204-9LPST
1.086 (27.58)	10	SPST	204-10	204-10ST	204-10LPST
1.286 (32.66)	12	SPST	204-12	204-12ST	204-12LPST
.286 (7.26)	1	SPDT	204-121	204-121ST	
.486 (12.34)	2	SPDT	204-122	204-122ST	
.686 (17.42)	3	SPDT	204-123	204-123ST	
.886 (22.50)	4	SPDT	204-124	204-124ST	
1.086 (27.58)	5	SPDT	204-125	204-125ST	
1.286 (32.66)	6	SPDT	204-126	204-126ST	
.286 (7.26)	1	DPST	204-211	204-211ST	
.486 (12.34)	2	DPST	204-212	204-212ST	
.686 (17.42)	3	DPST	204-213	204-213ST	
.886 (22.50)	4	DPST	204-214	204-214ST	
1.086 (27.58)	5	DPST	204-215	204-215ST	
1.286 (32.66)	6	DPST	204-216	204-216ST	
.486 (12.34)	1	DPDT	204-221	204-221ST	
.886 (22.50)	2	DPDT	204-222	204-222ST	
1.286 (32.66)	3	DPDT	204-223	204-223ST	
.486 (12.34)	1	4PST	204-411	204-411ST	
.886 (22.50)	2	4PST	204-412	204-412ST	
1.286 (32.66)	3	4PST	204-413	204-413ST	

For Tape & Reel Add "R" to End of P/N
 Contact CTS for availability. EXAMPLE: 204-25TR



	Half Pitch (0.050")	Auto-Placeable
SERIES	218	219
Positions	2 - 10 & 12	2 - 10 & 12
Initial Contact Resistance	100 Milliohms Max.	25 Milliohms Max.
Maximum Contact Resistance	100 Milliohms after 1,000 Cycles	50 Milliohms after 2,000 Cycles
Maximum Non-switching Rating	100 mA or 50 VDC	100 mA or 50 VDC
Insulation Resistance	1,000 Megaohms	1,000 Megaohms
Dielectric Breakdown	Min.: 500 VDC	Min.: 500 VDC
Switch Capacitance	Max.: 10.0 pF	Max.: 5.0 pF
Shock Mil-Std. 202F	< 1 microsecond	< 1 microsecond
Vibration Mil-Std. 202F	< 1 microsecond	< 1 microsecond
Type of Actuation	Slide (Top Actuated)	Slide (Top Actuated)
Circuitry Available	SPST	SPST
Terminal Configuration	Gull Wing & J Bend	Gull Wing & J Bend
Dimensions: inches (mm)		
Length	"A" Dim. (See Table Below)	"A" Dim. (See Table Below)
Width	.332* (8.43)	.390* (9.91)
Height	.104 (2.65)	.148 (3.76)
Lead Centers	.050 (1.27)	.100 (2.54)
Contact Plating/Terminal Plating	Gold/Tin	Gold/Tin
Operating Temperature	-40° to +85°C	-40° to +85°C
Options:		
Bottom & Top Sealed	Standard	Standard
Low Profile Actuator	Standard	Standard
RoHS Compliant	Since June 2006	Since June 2006

* Gull Wing Terminal To Terminal

STANDARD PART NUMBERS FOR 218



"A" Overall Dimension	No. of Switch Sections	Both Bottom & Top Sealed
.146 (3.71)	2	218-2LPST
.246 (6.25)	4	218-4LPST
.346 (8.79)	6	218-6LPST
.446 (11.33)	8	218-8LPST
.546 (13.87)	10	218-10LPST
.646 (16.41)	12	218-12LPST

For Tape & Reel Add "R" to End of P/N
EXAMPLE: 218-2LPSTR

STANDARD PART NUMBERS FOR 219

"A" Overall Dimension	No. of Switch Sections	Low Profile** Both Bottom & Top Sealed
.258 (6.55)	2	219-2 LPST
.358 (9.09)	3	219-3 LPST
.458 (11.63)	4	219-4 LPST
.558 (14.17)	5	219-5 LPST
.658 (16.71)	6	219-6 LPST
.758 (19.25)	7	219-7 LPST
.858 (21.79)	8	219-8 LPST
.958 (24.33)	9	219-9 LPST
1.058 (26.87)	10	219-10 LPST
1.258 (31.95)	12	219-12 LPST



**For Medium Height Actuators, Replace "LP" With "M",
For Tape & Reel Add "R" To End Of P/N
EXAMPLES: 219-2MST
219-2LPSTR



	Side Actuated	Side Actuated
SERIES	194	195
Positions	2 - 10 & 12	2 - 10 & 12
Initial Contact Resistance	50 Milliohms Max.	100 Milliohms Max.
Maximum Contact Resistance	100 Milliohms after 7,000 Cycles	100 Milliohms after 2,000 Cycles
Maximum Non-switching Rating	100 mA or 50 VDC	100 mA or 50 VDC
Insulation Resistance	1,000 Megohms	1,000 Megohms
Dielectric Breakdown	Min.: 500 VAC	Min.: 500 VAC
Switch Capacitance	Max.: 5.0 pF	Max.: 5.0 pF
Shock Mil-Std. 202F, Method 213B Condition A	No Damage with 25G Applied	No Damage with 25G Applied
Vibration Mil-Std. 202F, Method 204D Condition B	No Damage at 60 Hz Constant Vibration	No Damage at 60 Hz Constant Vibration
Type of Actuation	Side Actuated	Side Actuated
Circuitry Available	SPST	SPST
Dimensions: inches (mm)		
Center	.100 (2.54)	.100 (2.54)
Length	"A" Dim. (See Table Below)	"A" Dim. (See Table Below)
Width	.385 (9.78)	.385 (9.78)
Height	.311 (7.90)	.311 (7.90)
Contact Plating/Terminal Plating	Gold/Tin	Tin/Tin
Operating Temperature	-40° to +85°C	-40° to +85°C
Options:		
Bottom & Top Sealed	Standard	Standard
Right Angle Mount	-	-
Low Profile Actuator	-	-
RoHS Compliant	Since June 2006	Since June 2006

STANDARD PART NUMBERS FOR 194 AND 195

"A" Overall Dimension	Number of Switch Sections	Series 194 Part Number	Series 195 Part Number
.286 (7.26)	2	194-2MST	195-2MST
.386 (9.80)	3	194-3MST	195-3MST
.486 (12.34)	4	194-4MST	195-4MST
.586 (14.88)	5	194-5MST	195-5MST
.686 (17.42)	6	194-6MST	195-6MST
.786 (19.96)	7	194-7MST	195-7MST
.886 (22.50)	8	194-8MST	195-8MST
.986 (25.04)	9	194-9MST	195-9MST
1.086 (27.58)	10	194-10MST	195-10MST
1.286 (32.66)	12	194-12MST	195-12MST



Economy Slide

Multifunctional Slide

Economy Slide

Auto-Insertable

204	206	208	209/210
2 - 10 & 12	2 - 10 & 12	2 - 10 & 12	2 - 10 & 12
50 Milliohms Max.	50 Milliohms Max.	100 Milliohms Max.	25 Milliohms Max.
100 Milliohms after 2,000 Cycles	100 Milliohms after 10,000 Cycles	500 Milliohms after 2,000 Cycles	25/100 Milliohms after 500/1000 Cycles
Maximum Rise of 30°C @ 5A	Maximum Rise of 30°C @ 5A	100 mA or 50 VDC	100 mA or 50 VDC
1,000 Megohms	1,000 Megohms	1,000 Megohms	1,000 Megohms
Min.: 500 VAC	Min.: 500 VAC	Min.: 500 VAC	Min.: 500 VDC
Max.: 5.0 pF	Max.: 5.0 pF	Max.: 5.0 pF	Max.: 5.0 pF
< 1 microsecond	< 1 microsecond	< 1 microsecond	< 1 microsecond
< 1 microsecond	< 1 microsecond	< 1 microsecond	< 1 microsecond
Slide (Top Actuated)	Slide (Top Actuated)	Slide (Top Actuated)	Slide (Top Actuated)
SPST	SPST; SPDT; 4PST; DPST; DPDT	SPST	SPST
.100 (2.54)	.100 (2.54)	.100 (2.54)	.100 (2.54)
"A" Dim (See Table Below)	"A" Dim (See Table Below)	"A" Dim (See Table Below)	"A" Dim (See Table Below)
.385 (9.78)	.385 (9.78)	.385 (9.78)	.263 (6.68)
.300 (7.62)	.300 (7.62)	.300 (7.62)	.148 (3.76)
Gold/Tin	Gold/Tin	Tin/Tin	(209)-Gold/Tin (210)-Gold Flash/Tin
-55° to +85°C	-55° to +85°C	-55° to +85°C	-40° to +85°C
Available	Available	Available	Standard
---	Available	---	---
---	Available - Contact CTS	Available - Contact CTS	Standard
Since June 2006	Since June 2006	Since June 2006	Since June 2006

STANDARD PART NUMBERS FOR 205 / 206

"A" Overall Dimension	Number of Switch Sections	Actuation	Part Number	Both Bottom & Top Sealed	Low Profile Both Bottom & Top Sealed	Right Angle Mount Sealed Bottom & Top
.156 (3.96)	1	SPST	206-1	206-1ST	206-1LPST	—
.286 (7.26)	2	SPST	205/206-2	205/206-2ST	206-2LPST	206-2RAST
.386 (9.80)	3	SPST	205/206-3	205/206-3ST	206-3LPST	206-3RAST
.486 (12.34)	4	SPST	205/206-4	205/206-4ST	206-4LPST	206-4RAST
.586 (14.88)	5	SPST	205/206-5	205/206-5ST	206-5LPST	206-5RAST
.686 (17.42)	6	SPST	205/206-6	205/206-6ST	206-6LPST	206-6RAST
.786 (19.96)	7	SPST	205/206-7	205/206-7ST	206-7LPST	206-7RAST
.886 (22.50)	8	SPST	205/206-8	205/206-8ST	206-8LPST	206-8RAST
.986 (25.04)	9	SPST	205/206-9	205/206-9ST	206-9LPST	206-9RAST
1.086 (27.58)	10	SPST	205/206-10	205/206-10ST	206-10LPST	206-10RAST
1.286 (32.66)	12	SPST	205/206-12	205/206-12ST	206-12LPST	206-12RAST
.286 (7.26)	1	SPDT	206-121	206-121ST		206-121RAST
.486 (12.34)	2	SPDT	206-122	206-122ST		206-122RAST
.686 (17.42)	3	SPDT	206-123	206-123ST		206-123RAST
.886 (22.50)	4	SPDT	206-124	206-124ST		206-124RAST
1.086 (27.58)	5	SPDT	206-125	206-125ST		206-125RAST
1.286 (32.66)	6	SPDT	206-126	206-126ST		206-126RAST
.286 (7.26)	1	DPST	206-211	206-211ST		206-211RAST
.486 (12.34)	2	DPST	206-212	206-212ST		206-212RAST
.686 (17.42)	3	DPST	206-213	206-213ST		206-213RAST
.886 (22.50)	4	DPST	206-214	206-214ST		206-214RAST
1.086 (27.58)	5	DPST	206-215	206-215ST		206-215RAST
1.286 (32.66)	6	DPST	206-216	206-216ST		206-216RAST
.486 (12.34)	1	DPDT	206-221	206-221ST		206-221RAST
.886 (22.50)	2	DPDT	206-222	206-222ST		206-222RAST
1.286 (32.66)	3	DPDT	206-223	206-223ST		206-223RAST
.486 (12.34)	1	4PST	206-411	206-411ST		206-411RAST
.886 (22.50)	2	4PST	206-412	206-412ST		206-412RAST
1.286 (32.66)	3	4PST	206-413	206-413ST		206-413RAST

STANDARD PART NUMBERS FOR 208


"A" Overall Dimension	No. of Switch Sections	Part No.	Both Bottom & Top Sealed
.156 (3.96)	1	208-1	208-1ST
.286 (7.26)	2	208-2	208-2ST
.386 (9.80)	3	208-3	208-3ST
.486 (12.34)	4	208-4	208-4ST
.586 (14.88)	5	208-5	208-5ST
.686 (17.42)	6	208-6	208-6ST
.786 (19.96)	7	208-7	208-7ST
.886 (22.50)	8	208-8	208-8ST
.986 (25.04)	9	208-9	208-9ST
1.086 (27.58)	10	208-10	208-10ST
1.286 (7.26)	11	208-12	208-12ST

STANDARD PART NUMBERS FOR 209/210

"A" Overall Dimension	No. of Switch Sections	Low Profile* Both Bottom & Top Sealed
.258 (7.26)	2	209/210-2LPST
.358 (9.80)	3	209/210-3LPST
.458 (12.34)	4	209/210-4LPST
.558 (14.88)	5	209/210-5LPST
.658 (17.42)	6	209/210-6LPST

* For Medium Height Actuators Replace "LP" with "M"
EXAMPLE: 209-2MST

THROUGH-HOLE



SERIES	201	262
Description	15mm Composition	10mm Conductive Plastice
Resistance Range	100 Ohms to 5 Megohm	500 Ohms to 2 Megohm
Resistance Tolerance	±20% Standard	±20% Standard
Power Rating, Watts	5000 Ohms and above 1/4 watt @ 55°C derated to no load @ 100°C Below 5000 Ohms 1/4 watt @ 40°C, .2 watt @ 55°C derated to no load @ 85°C	0.15 watts @ 40°C derated to no load @ 100°C
Voltage Rating	350 VDC	350 VDC
Resistance Tapers	Linear	Linear
Angle of Rotation	260° ±5°	265° ±5°
Turning Torque	0.75 to 6 inch-ounces	.3 to 5 inch-ounces
Stop Strength	2.5 inch-pounds	16 inch-pounds
Mounting Styles:		
X= Vertical	Available	Available
U= Horizontal	Available	Available
Operating Temperature	-35° to +85°C	-35° to +85°C
RoHS Compliant	Since June 2006	Since June 2006


STANDARD RESISTOR VALUES FOR 201

Resistor Value in Ohms + 20%	Code	Type and Part Number	
		201X	201U
100	101	201XR101B	201UR101B
250	251	201XR251B	201UR251B
500	501	201XR501B	201UR501B
1000	102	201XR102B	201UR102B
2500	252	201XR252B	201UR252B
5000	502	201XR502B	201UR502B
10K	103	201XR103B	201UR103B
25K	253	201XR253B	201UR253B
50K	503	201XR503B	201UR503B
100K	104	201XR104B	201UR104B
250K	254	201XR254B	201UR254B
500K	504	201XR504B	201UR504B
1.0M	105	201XR105B	201UR105B

STANDARD RESISTOR VALUES FOR 262


Resistance Value in Ohms + 20%	Code	Knob Color	Type and Part Number	
			262X	262U
500	501	Green	262XR501B	262UR501B
1K	102	Yellow	262XR102B	262UR102B
2.5K	252	Red	262XR252B	262UR252B
5K	502	Blue	262XR502B	262UR502B
10K	103	White	262XR103B	262UR103B
25K	253	Black	262XR253B	262UR253B
50K	503	Orange	262XR503B	262UR503B
100K	104	Gray	262XR104B	262UR104B
250K	254	Violet	262XR254B	262UR254B
500K	504	Brown	262XR504B	262UR504B
1.0M	105	Light Blue	262XR105B	262UR105B

PART NUMBER EXAMPLE: 262XR501B



CERMET

OBSOLETE



SERIES	O	303	306	307
Description	B	3mm Surface Mount	6mm Square	6 mm Round
Resistance Range	S	100 Ohms to 1 Megohm	10 Ohms to 2 Megohm	100 Ohms to 1 Megohm
Resistance Tolerance	O	±25%	±25%	±25%
Power Rating, Watts	L	0.1 watt @ 70°C	0.5 watt @ 70°C	0.3 watt @ 70°C
	E	derated to no load @ 100°C	derated to no load @ 125°C	derated to no load @ 100°C
Voltage Rating	T	The lesser of 50V	The lesser of 200V	The lesser of 100V
	E	or $\sqrt{PR} = V$	or $\sqrt{PR} = V$	or $\sqrt{PR} = V$
Resistance Tapers		Linear	Linear	Linear
Angle of Rotation		270°C ±20°	270°C ±10°	270°C ±10°
Turning Torque		19.6 mN·m Max	20 mN·m Max	29.4 mN·m Max
Stop Strength			50 mN·m Max	49 mN·m Max
Mounting Styles:				
X= Vertical - center terminal at rear			Available	Available
J= Vertical - center terminal forward			Available	
K= Vertical - inline terminals			Available	
U= Horizontal		Available	Available	Available
H= Horizontal - inline terminals			Available	
Operating Temperature		-40° to +100°C	-55° to +125°C	-25° to +100°C
Packaging				
Bulk			500/Bag	500/Bag
Tape & Reel - Vertical mount style			1000/Reel (K Mount)	1000/Reel (X Mount)
Tape & Reel - Horizontal mount style		2000/Reel	1000/Reel (H Mount)	800/Reel (U Mount)
		Standard Values for 303	Standard Values for 306	Standard Values for 307
		Resistor value in ohms	Resistor value in ohms	Resistor value in ohms
		Code	Code	Code
			10	
			20	
			50	
	100	101	100	100
	200	201	200	200
	500	501	500	500
	1000	102	1000	1000
	2000	202	2000	2000
	5000	502	5000	5000
	10K	103	10K	10K
	20K	203	20K	20K
	50K	503	50K	50K
	100K	104	100K	100K
	200K	204	200K	200K
	500K	504	500K	500K
	1.0M	105	2.0M	1.0M

PART NUMBER EXAMPLE: 306HC202BR

306	H	C	202	B	R
Series	Horizontal Mount	Knob Type	Resistor Code	Tolerance	Packaging
303	U=303/306/307	C = Cross-slot	(see Resistance Value Code above)	B = 306 ± 20%	Blank=303 T&R
306	H=306			E = 303/307 ± 25%	Blank+306/307 Bulk
307	Vertical Mount				R=306 T&R style H&K
	X=306/307				R= 307 T&R style U&X
	J=306				
	K=306				

IERC HEAT SINKS



FIGURE 1



FIGURE 2



FIGURE 3



FIGURE 4



FIGURE 5



FIGURE 6



FIGURE 7



FIGURE 8

Figure	Part Number	Description	Dimensions - Inches L x W x H	Thermal Resistance (Natural Convection °C/W)
1	BDN09-3CB/A01	Various Semiconductors, Adhesive Backed	0.91 x .091 x .355	26.9
	BDN10-3CB/A01		1.01 x 1.01 x .355	26.4
	BDN10-5CB/A01		1.01 x 1.01 x .555	20.8
	BDN11-3CB/A01		1.11 x 1.11 x .355	20.9
	BDN12-3CB/A01		1.21 x 1.21 x .355	19.6
	BDN12-5CB/A01		1.21 x 1.21 x .555	16.5
	BDN13-3CB/A01		1.31 x 1.31 x .355	16.1
	BDN14-3CB/A01		1.41 x 1.41 x .355	16.2
	BDN15-3CB/A01		1.51 x 1.51 x .355	15.1
	BDN15-5CB/A01		1.51 x 1.51 x .555	11.9
	BDN16-3CB/A01		1.61 x 1.61 x .355	13.5
	BDN17-3CB/A01		1.71 x 1.71 x .355	11.5
	BDN18-3CB/A01		1.81 x 1.81 x .355	10.8
	BDN18-6CB/A01		1.81 x 1.81 x .605	8.1
	BDN21-3CB/A01		2.11 x 2.11 x .355	8.5
Figure	Part Number	Description	Dimensions - Inches L x W x H	Thermal Resistance (°C/W @ 200 LFPM)
2	APR27-27-12CB/A01	Aluminum Forged for Various Semiconductors, Adhesive Backed	1.05 x 1.05 x .45	5.3
	APR27-27-15CB/A01		1.05 x 1.05 x .57	4.4
	APR27-27-20CB/A01		1.05 x 1.05 x .77	3.1
	APR27-27-25CB/A01		1.05 x 1.05 x .97	2.8
	APR35-35-12CB/A01		1.37 x 1.37 x .45	3.5
	APR35-35-15CB/A01		1.37 x 1.37 x .57	2.9
	APR35-35-20CB/A01		1.37 x 1.37 x .77	2.0
	APR35-35-25CB/A01		1.37 x 1.37 x .97	1.8
	APR40-40-12CB/A01		1.56 x 1.56 x .45	2.8
	APR40-40-15CB/A01		1.56 x 1.56 x .57	2.3
	APR40-40-20CB/A01		1.56 x 1.56 x .77	1.6
	APR40-40-25CB/A01		1.56 x 1.56 x .97	1.4
	APR43-43-12CB/A01		1.66 x 1.66 x .45	2.5
	APR43-43-15CB/A01		1.66 x 1.66 x .57	2.0
	APR43-43-20CB/A01		1.66 x 1.66 x .77	1.5
	APR43-43-25CB/A01		1.66 x 1.66 x .97	1.2
	CPR27-27-12U/A01	Copper Forged for Various Semiconductors, Adhesive Backed	1.05 x 1.05 x .45	4.6
	CPR27-27-15U/A01		1.05 x 1.05 x .57	4.0
	CPR27-27-20U/A01		1.05 x 1.05 x .77	2.9
	CPR27-27-25U/A01		1.05 x 1.05 x .97	2.5
	CPR35-35-12U/A01		1.37 x 1.37 x .45	3.0
	CPR35-35-15U/A01		1.37 x 1.37 x .57	2.6
	CPR35-35-20U/A01		1.37 x 1.37 x .77	1.8
	CPR35-35-25U/A01		1.37 x 1.37 x .97	1.7
	CPR40-40-12U/A01		1.56 x 1.56 x .45	2.4
	CPR40-40-15U/A01		1.56 x 1.56 x .57	2.0
	CPR40-40-20U/A01		1.56 x 1.56 x .77	1.6
	CPR40-40-25U/A01		1.56 x 1.56 x .97	1.5
	CPR43-43-12U/A01		1.66 x 1.66 x .45	2.1
	CPR43-43-15U/A01		1.66 x 1.66 x .57	1.9
	CPR43-43-20U/A01		1.66 x 1.66 x .77	1.3
	CPR43-43-25U/A01		1.66 x 1.66 x .97	1.2
Figure	Part Number	Description	Dimensions - Inches L x W x H	Thermal Resistance (Natural Convection °C/.5W)
3	TX0505ND	T0-5, Solder Mount, Dull Nickel Finish	.38 x .38 x .37	N/A
	TX0506-1B	T0-5, 6-32 Stud Mount, Black Cadmium Finish	.38 x .38 x .65	N/A
	TX0506-1BF	T0-5, 6-32 Stud Mount, Black Chemical Film Finish	.38 x .38 x .65	N/A
	TX0506-2B	T0-5, 10-32 Stud Mount, Black Cadmium Finish	.38 x .38 x .65	N/A
	TX0507-1B	T0-5, 6-32 Stud Mount, Black Cadmium Finish	.38 x .38 x .59	41.0
	TX0522B	T0-5, 4-40 Hex Nut Mount, Black Cadmium Finish	.38 x .38 x .47	N/A
	TX0522BF	T0-5, 4-40 Hex Nut Mount, Black Chemical Film Finish	.38 x .38 x .47	N/A
	TXB2-032-037B	T0-5, No Hardware, Black Cadmium Finish	.38 x .38 x .25	41.0
	TXB2P-032-037B	T0-5, 4-40 Screw Mount & Nylon Washer, Black Cadmium Finish	.38 x .38 x .37	41.0
	TXBE-032-031B	T0-5, Solder, Glue, Rivet Mount, Black Cadmium Finish	.38 x .38 x .31	41.0
	TX1806B	T0-18, 4-40 Stud Mount, BeO Washer, Black Cadmium Finish	.22 x .25 x .56	N/A
	TX1807B	T0-18, 4-40 Stud Mount, Black Cadmium Finish	.22 x .25 x .50	54.0
	TX1822B	T0-18, 2-56 x 1/4 Nut Mount, BeO Washer, Black Cadmium Finish	.22 x .25 x .34	N/A
	TXB2-019-028B	T0-18, No Hardware, Black Cadmium Finish	.22 x .22 x .21	54.0
	TXB2P-019-028B	T0-18, 2-56 Screw Mount & Nylon Washer, Black Cadmium Finish	.22 x .22 x .28	54.0
4	TXBF-032-025B	"T0-5, Fan Top, BeCu Material, Black Cadmium Finish	.75 x .75 x .25	40.0
	TXBF-019-025B	"T0-18, Fan Top, BeCu Material, Black Cadmium Finish	.50 x .50 x .25	75.0
Figure	Part Number	Description	Dimensions - Inches L x W x H	Thermal Resistance (Natural Convection °C/W)
5	7-120-BA	T0-5, Aluminum with Black Anodize	.44 x .44 x .50	35.0
6	7-156-BA	T0-18, Aluminum with Black Anodize	.22 x .22 x .40	75.0
7	7-175-BA	T0-5, Aluminum with Black Anodize	.325 x .70 x .25	58.0
8	7-192-BA	T0-126, 127, 202, 218, or 220, Black Anodize	.71 x 1.00 x .50	32.0



Figure	Part Number	Description	Dimensions - Inches L x W x H	Thermal Resistance (Natural Convection °C/W)
9	7-338-1PP-BA	T0-220, Vertical Mount with Pins, Black Anodize	.50 x 1.38 x 1.50	13.0
	7-338-4PP-BA		.50 x 1.38 x 2.50	4.0
	7-339-1PP-BA		1.00 x 1.65 x 1.50	11.0
	7-339-3PP-BA		1.00 x 1.65 x 2.00	5.0
	7-339-4PP-BA		1.00 x 1.65 x 2.50	4.0
10	7-340-1PP-BA	T0-220, Vertical Mount, Black Anodize	.75 x 1.15 x .46	14.0
	7-340-3PP-BA	T0-220, Horizontal Mount, Black Anodize	.75 x 1.15 x .46	14.0
	7-340-4PP-BA	Dual T0-220, Horizontal Mount, Black Anodize	1.50 x 1.15 x .46	7.0
11	7-342-2PP-BA	Six T0-220, Horizontal Mount, Black Anodize	1.50 x 1.62 x .69	4.0
12	7-345-1PP-BA	T0-220, Horizontal/Vertical Mount, Black Anodize	.75 x 2.00 x .553	9.0
	7-345-2PP-BA	Dual T0-220, Universal Mount, Black Anodize	1.50 x 2.00 x .553	4.0
	7-345-3PP-BA	T0-220, Horizontal Mount, Black Anodize	.75 x 2.00 x .553	9.0
13	7-361-BA	T0-220, Horizontal/Vertical Mount, Black Anodize	.71 x .80 x .50	30.0
	7-362-BA	T0-220, Horizontal/Vertical Mount, Black Anodize	.71 x .80 x .34	38.0
	7-363-BA	T0-220, Vertical Mount with Tabs, Black Anodize	.83 x .80 x .50	23.0
14	7-370-BA	T0-126, 127, 202, 218, 220, Black Anodize	1.00 x .85 x .75	20.0
15	7-423-BA	T0-3, Power Cap, Black Anodize	1.06 x 1.56 x .50	32.0
16	LAIC3B2B	T0-3 IC, Military Black Anodize	1.63 x 1.29 x .50	15.0
	LAIC3B3CB	T0-3 IC, Black Anodize	1.63 x 1.29 x .75	11.0
	LAT03B2B	T0-3, Military Black Anodize	1.63 x 1.29 x .50	15.0
	LAT03B3B	T0-3, Military Black Anodize	1.63 x 1.29 x .75	11.0
	LAT03B4CB	T0-3, Black Anodize	1.63 x 1.29 x 1.00	9.0
	LAT03B7B	T0-3, Military Black Anodize	1.63 x 1.29 x .40	19.0
17	PC1-1CB	T0-220, Black Anodize	.75 x .75 x .375	27.3
18	PSB2-1CB	T0-126, 127, 220, Horizontal/Vertical Mount with Tabs, Black Anodize	1.40 x .88 x .25	25.9
	PSB2-1ND	T0-126, 127, 220, Horizontal/Vertical Mount with Tabs, Dull Nickel Finish		
19	PSC2-2CB	T0-220, Black Anodize	.81 x 1.00 x .31	41.7
	PSC2T-2CB	T0-220, Anti-Rotation Tabs, Black Anodize		
20	PA1-1CB	T0-126, 127, 220, Horizontal/Vertical Mount with Tabs, Black Anodize	.71 x 1.00 x .50	28.8
	PA2-1CB	T0-126, 127, 220, Horizontal/Vertical Mount with Tabs, Black Anodize	.71 x 1.00 x .31	30.0
21	PB1-2CB	Dual T0-126, 127, 220, Black Anodize	1.18 x 1.00 x .50	26.0
22	PB1-36CB	T0-126, 127, 220, Vertical Mount with Tabs, Black Anodize	1.33 x 1.00 x .50	20.0
	PB1-36ND	T0-126, 127, 220, Vertical Mount with Tabs, Dull Nickel Finish		
23	PB1ST-69CB	T0-220, Solderable Tabs, Black Anodize	1.18 x 1.00 x .50	20.0
24	HP1-T03-CB	T0-3, Horizontal Mount, Black Anodize	2.50 x 2.50 x .90	17.0
25	LAD66A2B	T0-66, Horizontal Mount, Military Black Anodize	1.31 x .90 x .50	25.0
	LAE66A3CB	T0126, T0220, Horizontal Mount, Black Anodize	1.31 x .90 x .75	20.0
	LAT0127B5CB	T0-220, Horizontal Mount, Black Anodize	1.63 x 1.29 x 1.25	12.0
26	PSE1-2CB	Dual T0-220, Vertical Mount with Tabs, Black Anodize	1.18 x 1.50 x .50	18.5
27	PVC-1B	T0-202, Clip, Black Cadmium	.45 x .38 x .20	39.0
28	RUR671U	T0-92, BeCu Material, Unplated	.59 x .56	>125
29	UP-T03-CB	T0-3, Horizontal Mount, Black Anodize	1.78 x 1.78 x 1.00	9.0
	UP-T03-B	T0-3, Horizontal Mount, Military Black Anodize		
	UP1-T03-CB	T0-3, Horizontal Mount, Black Anodize	1.78 x 1.78 x .50	13.0
	UP1-T03-B	T0-3, Horizontal Mount, Military Black Anodize		
30	UP3-T03-CB	T0-3, Horizontal Mount, Black Anodize	1.50 x 1.38 x .44	19.0

CTS[®] Authorized Distributors

Province	Distributor	Website
Global	All American	www.allamerican.com
	Arrow Electronics	www.arrow.com
	Avnet	www.avnet.com
	Digi-Key Corporation	www.digikey.com
	Future Electronics	www.futureelectronics.com
	JACO Corporation	www.jacoelectronics.com
	Richardson Electronics	www.rell.com
North America Regional	Chris Electronics	www.chriselectronics.com
	Dove Electronics	www.doveonline.com
	Peerless Electronics	www.peerlesselectronics.com
	Utech Electronics, Inc.	www.utech.ca
	IEC-Walker Components Group	www.walkercomponent.com
EUROPE Regional	BFI Optilas	www.bfioptilas.com
	Fast Elettronica Italiana, S.p.A.	www.fastelettronica.com
	Flint Distribution, Ltd.	www.flint.co.uk
	More Electronics ApS	www.mooreelectronics.dk
ASIA Regional	Bansuk Industrial Co.	www.bansukoh.com
	Plexus Components Pte. Ltd.	www.plexus-components.com
	TESCO	www.tescoinc.co.kr

Note - Not all distributors are authorized for all CTS Standard Products.
Please check the CTS website, www.ctscorp.com for detailed contact information.

Your Local CTS Stocking Distributor:

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CTS:](#)
[PVC1B](#)