




5000		GMV		150	100	10 G Ω	250	10	----	15	30	45	55																																										
CAP.(pf)	TOLERANCE	85°C	125°C	I.R. MIN. @ 100 (VDC.)	DWV (VDC)	DC CURRENT (AMPS)	1 MHz	10 MHz	100 MHz	1 GHz	10 GHz																																												
		DC WORKING VOLTAGE					MIN. NO LOAD INSERTION LOSS (dB) @ 25°C PER MIL-STD-220																																																
<table><tr><td colspan="2">REVISION RECORD</td><td colspan="2">0</td><td colspan="2">REDRAWN & REVISED ADDED 008,009. E.C. 05-30-90</td><td colspan="2">10</td><td colspan="2">VARS 005,006,007 & 1MHz COLUMN ADDED. L.E. 11-07-90</td><td colspan="2">11</td><td colspan="2">RDN TO COMP FMT & ADDED METRIC. S.M. 11-08-01</td></tr><tr><td colspan="2"></td><td colspan="2">20000926-3-01</td><td colspan="2">REVISED DWG. DRAWING MADE FOR EACH VAR. S.M. 12-02-02</td><td colspan="2">12</td><td colspan="2"></td><td colspan="2">20021125-1-05</td><td colspan="2">10 (AMPS) WAS 5 (AMPS) L.E. 06-23-04</td></tr><tr><td colspan="2"></td><td colspan="2">20040621-1-05</td><td colspan="2">ADDED AND REVISED NOTES. S.M. 12-14-05</td><td colspan="2">13</td><td colspan="2"></td><td colspan="2">20051122-2-06</td><td colspan="2"></td></tr></table>														REVISION RECORD		0		REDRAWN & REVISED ADDED 008,009. E.C. 05-30-90		10		VARS 005,006,007 & 1MHz COLUMN ADDED. L.E. 11-07-90		11		RDN TO COMP FMT & ADDED METRIC. S.M. 11-08-01				20000926-3-01		REVISED DWG. DRAWING MADE FOR EACH VAR. S.M. 12-02-02		12				20021125-1-05		10 (AMPS) WAS 5 (AMPS) L.E. 06-23-04				20040621-1-05		ADDED AND REVISED NOTES. S.M. 12-14-05		13				20051122-2-06			
REVISION RECORD		0		REDRAWN & REVISED ADDED 008,009. E.C. 05-30-90		10		VARS 005,006,007 & 1MHz COLUMN ADDED. L.E. 11-07-90		11		RDN TO COMP FMT & ADDED METRIC. S.M. 11-08-01																																											
		20000926-3-01		REVISED DWG. DRAWING MADE FOR EACH VAR. S.M. 12-02-02		12				20021125-1-05		10 (AMPS) WAS 5 (AMPS) L.E. 06-23-04																																											
		20040621-1-05		ADDED AND REVISED NOTES. S.M. 12-14-05		13				20051122-2-06																																													
<table><tr><td colspan="2">--TOLERANCES-- Unless Otherwise Specified</td><td colspan="2" rowspan="3">BUSHING STYLE EMI FILTER</td></tr><tr><td colspan="2">DECIMAL ± NOTED</td></tr><tr><td colspan="2">ANGLES ± </td></tr></table>								--TOLERANCES-- Unless Otherwise Specified		BUSHING STYLE EMI FILTER		DECIMAL ± NOTED		ANGLES ± 		Title																																							
--TOLERANCES-- Unless Otherwise Specified		BUSHING STYLE EMI FILTER																																																					
DECIMAL ± NOTED																																																							
ANGLES ± 																																																							
<table><tr><td colspan="2">TUSONIX TUCSON, ARIZONA</td><td colspan="2">Drawn S.M. 11-07-01</td><td colspan="2">Scale 5 X</td></tr><tr><td colspan="2" rowspan="2"></td><td colspan="2">Approved B.Mc 11-07-01</td><td colspan="2"></td></tr><tr><td>A</td><td colspan="2">4400-004</td></tr></table>								TUSONIX TUCSON, ARIZONA		Drawn S.M. 11-07-01		Scale 5 X				Approved B.Mc 11-07-01				A	4400-004																																		
TUSONIX TUCSON, ARIZONA		Drawn S.M. 11-07-01		Scale 5 X																																																			
		Approved B.Mc 11-07-01																																																					
		A	4400-004																																																				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[4400-004LF](#)