



**Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.**

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



SPECIFICATIONS	
Capacitance Value:	1000 pF
Capacitance Tolerance:	GMV
Temp. Characteristic:	X7U
Rating:	100 VDC @ + 125°C
Operating Range:	-55°C TO +125°C
I.R. MIN. @ 100 (VDC.)	10 G
DWV	600 VDC

1. # 8 - 32 - 2B TH"D
HEX NUT SUPPLIED.
2. TUSONIX STANDARD PART
NUMBER: 2425-003-X7U0-102P.
TUSONIX RoHS COMPLIANT PART
NUMBER: 2425-003-X7U0-102P LF.
CUSTOMER MUST SPECIFY STANDARD
OR RoHS PART NUMBER WHEN
ORDERING.
3. PART MARKING: STANDARD: BLACK
INK FOR TRADEMARK AND CAP. CODE.
RoHS PART: GREEN FOR TRADEMARK
AND CAP. CODE.

REVISION RECORD

Original Release C.O. 20050413-3-04	0
--	---

--TOLERANCES--
Unless Otherwise
Specified

DECIMAL $\pm .031$ [0.79]

ANGLES $\pm$ 

TUSONIX
TUCSON, ARIZONA

Title

MINIATURE BUSHING FEED-THRU

Drawn

S.M. 04-18-05

Approved

R.C. 04-18-05

A

2425-003-X7U0-102P

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[2425-003-X7U0-102PLF](#)