




Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



NOTES:

1. SUPPLIED WITH SILVER PLATED HEX NUT AND LOCK WASHER.
2. MOUNTING TORQUE NOT TO EXCEED 5 lb-in.
3. TUSONIX STANDARD PART NUMBER: 2425-018-X5U0-102P. TUSONIX RoHS COMPLIANT PART NUMBER: 2425-018-X5U0-102P LF. CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
4. PART MARKING: STANDARD: BLACK INK FOR TRADEMARK AND CAP. CODE. RoHS PART: GREEN FOR TRADEMARK AND CAP. CODE.

SPECIFICATIONS

Capacitance Value:	1000 pF
Capacitance Tolerance:	+ 100 - 0 %
Temp. Characteristic:	X5U
Rating:	200 VDC @ +85°C/100 VDC @ +125°C
Operating Range:	-55°C TO +125°C
Current (A)	20
INSULATION RESISTANCE	10,000 m Ω (MIN.) @ +25°C
DWV @ 2 SEC. MIN.	600 VDC

REVISION RECORD Original Release C.O. 20000711-3-01 TUSONIX PART NO. DELETED L.E. 12-12-01 20011207-1-02 ADDED NOTES 3 & 4, IR, DWV & CURRENT, S.M. 11-01-05 20051031-1-05	0 1 2	--TOLERANCES-- Unless Otherwise Specified DECIMAL ± .031 [0.79] ANGLES ±	TUSONIX TUCSON, ARIZONA	Title MINIATURE BUSHING FEED-THRU	
				Drawn L.E. 07-12-00	
				Approved H.R. 07-12-00	
				A	2425-018-X5U0-102P

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[2425-018-X5U0-102PLF](#)