




This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



SPECIFICATIONS

TUSONIX STYLE:	2443-008
VALUE:	1500 pF
VALUE TOL.:	± 20%
TEMP. COEF.:	X5S
RATING:	500 WVDC @ 85°C
OPERATING RANGE:	-55°C TO +85°C
DWV (VDC)	1500
I.R. MIN. @ 100 (VDC)	10 G Ω

NOTES:

1. TUSONIX STANDARD PART
NUMBER: 2443-008-X5S0-152M.
TUSONIX RoHS COMPLIANT PART
NUMBER: 2443-008-X5S0-152M LF.
CUSTOMER MUST SPECIFY STANDARD OR
RoHS PART NUMBER WHEN ORDERING.
2. PART MARKING: TRADEMARK,
CAPACITANCE AND TOLERANCE CODE:
STANDARD PART: BLACK INK.
RoHS PART: GREEN INK.
3. SUPPLIED WITH SILVER PLATED
HEX NUT AND LOCK WASHER, BULK
PACKAGED.

REVISION RECORD	0 Original Release C.O. 19980728-3-01 ADDED METRIC, DWV & I.R. ADDED & REVISED NOTES. S.M. 12-15-06	1 20061215-1-01		--TOLERANCES-- Unless Otherwise Specified		Title BUSHING TYPE FEED-THRU CAPACITOR	
				DECIMAL ± .015 [0.38]		Drawn S.M. 07-29-98	
				ANGLES ±		Approved J.Mc. 07-29-98	
				TUSONIX TUCSON, ARIZONA		A 2443-008-X5S0-152M	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[2443-008-X5S0-152M](#)