




This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING **DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING** **DIMENSIONS IN METRIC - []**



OPERATING INFORMATION

STYLE NO.	2461-001
VALUE	1500 pF
VALUE TOL.	+100% / -0%
TEMP. COEF.	X7V
RATING	100VDC@+125°C
OPERATING RANGE	-55°C,+125°C
DWV	600
I.R. MIN @ 100VDC	10 GΩ
TO TUSONIX SPEC. UNLESS STATED OTHERWISE.	

NOTES:

1. TUSONIX STANDARD PART NUMBER: 2461-001-X7V0-152P.
TUSONIX RoHS COMPLIANT PART NUMBER:
2461-001-X7V0-152P LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER
WHEN ORDERING.
2. LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS
PART #: SILVER PLATED.
3. ELECTRODE FINISH: STANDARD PART #: 60/40 SOLDER PLATED.
RoHS PART #: MATTE TIN PLATED.
4. PART MARKING: STANDARD PART: NO MARKING. RoHS PART:
MARKING ON PACKAGING ONLY.

X-2015 Rev-0	REVISION RECORD		A		--TOLERANCES-- Unless Otherwise Specified		Title SHOULDER FEED-THRU		
	Original Release C.O. ECO-659				DECIMAL ± .015 [.38]				
					ANGLES ± 		Drawn L.E. 04-14-09		Scale 4 X
					TUSONIX TUCSON, ARIZONA		Approved R.L. 04-14-09		
							A	2461-001-X7V0-152P	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[2461-001-X7V0-152PLF](#)