




MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



NOTES:

1. TUSONIX STANDARD PART NUMBER: 4260-001.
TUSONIX RoHS COMPLIANT PART NUMBER: 4260-001 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. LEAD FINISH: STANDARD PART #: SOLDER PLATED COPPER. RoHS PART #: SILVER PLATED.
3. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
4. SUPPLIED WITH SILVER PLATED COPPER ALLOY HEX NUT AND INTERNAL TOOTH LOCK WASHER.

5,500	50 VDC	10 GΩ	125 VDC	3 A	7	14	30	55	70	70
MIN. CAP.(pf)	+ 125 °C DC WORKING VOLTAGE	I.R. MIN. @ 100 VDC	DWV	CURRENT	3 MHz	10 MHz	30 MHz	100 MHz	300 MHz	1 GHz
MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220										

X-2015 Rev-0	REVISION RECORD				--TOLERANCES-- Unless Otherwise Specified		Title MULTI LAYER BUSHING STYLE EMI FILTER			
	0	Original Release C.O. 6611	1	RDN TO COMP FMT. S.M. 03-04-02	2	ADDED NOTES 1-4. S.M. 12-06-05	3	20051118-2-08	Drawn S. M. 03-04-02	Scale 4 X
		DIM'S REV., TITLE CHGD. E.C. 5-26-92							Approved T.C. 03-04-02	
									A	4260-001

TUSONIX
TUCSON, ARIZONA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[4260-001LF](#)