


D3313-S mITX

Industrial Series



AMD Embedded G-Series SoC Platform for AMD FT3/FT3B SoC Processor

- ▶ DVI-I, DP V1.2 and Dual Channel LVDS support
- ▶ mSATA and Mini-PCI Express® onboard
- ▶ HW Watchdog
- ▶ Dual GbE LAN, 3x COM, GPIO
- ▶ 12 V & 19-24 V power supply option

POSSIBILITIES START HERE

D3313-S mITX

Industrial Series


The Kontron D3313-S mITX Motherboard is equipped with AMD Embedded G-series processors. Combined with the comprehensive feature set it's the perfect fit for KIOSK, casino gambling, POS,

thin clients, industrial PCs and other applications with high power consumption efficiency and enhanced operating temperature (0 °C - 60 °C) needs.

PRODUCT HIGHLIGHTS

- ▶ DDR3 1333/1600 SDRAM (SO-DIMM)
- ▶ AMD Radeon integrated graphics on board:
DVI-I, DP V1.2 and Dual Channel LVDS support
- ▶ PCIe x4 connector and Mini-PCI Express®
- ▶ HD Audio
- ▶ Dual GbE LAN
- ▶ Serial ATA III onboard
- ▶ mSATA (SATA III) socket support
- ▶ USB 2.0 and USB 3.1 Gen1 onboard
- ▶ 8 Bit GPIO onboard
- ▶ 3 x serial port and 1 x parallel port onboard
- ▶ Designed for fanless operation

- ▶ BIOS-Boot & OS – HW Watchdog onboard
- ▶ Dual-Range DC Power Supply 12 V / 19-24 V



TECHNICAL INFORMATION

SYSTEM	PROCESSOR MEMORY	D3313-S1: AMD Embedded GX-210HA SOC 2x SO DIMM Socket (1.5 V / 1.35 V), max. 16 GByte, Single Channel DDR3-1333 (CL9)
VIDEO	GRAPHICS	D3313-S1: AMD Radeon HD8210E
AUDIO	AUDIO CODEC AUDIO INTERFACE	Realtek ALC 671 5.1-channel, High Definition Audio
NETWORK CONNECTION	ETHERNET	2x Realtek RTL 8111G, 10/100/1000, PXE- & WoL Support, Teaming Support
PERIPHERAL CONNECTION	USB	4x USB 2.0 (Typ A rear) 2x USB 3.1 Gen1 (by header) 2x USB 2.0 (by header) 1x USB 2.0 (internal Typ A plug)
	SERIAL PORT	2x RS232 (DB9 rear)
	OTHER I/Os	1x RS232 (by header) 1x LPT (by header) 1x 8-bit GPIO (by header)
STORAGE & EXPANSION	SATA	1 x PCIe x4 (Gen2); "mechanical open slot" for usage of x16 cards 1 x Mini-PCIe (Gen2) incl. USB2.0; support for halfsize & fullsize cards 1 x mSATA (SATA-III); support for fullsize modules
POWER	CONNECTOR	12 V / 19-24 V (max. 5 A via external DC connector / max. 8 A via internal DC connector)
	INPUT VOLTAGE	Onboard CPU Core Voltage Regulator
FIRMWARE	BIOS	AMI Aptio 4.x UEFI BIOS modified and adapted by Fujitsu Technology Solutions; Recovery BIOS, SM-BIOS (DMI), BIOS Update, Quick Boot, Logo Boot, Quiet Boot, Plug & Play, Automatic DRAM and PCI Configuration, BIOS Support for S.M.A.R.T., Advanced Power Management, configurable LVDS support, integrated HW diagnostic tool, EraseDisk Feature
	WATCHDOG REAL TIME CLOCK	2-Level WD (BIOS Boot WD / OS WD) Integrated

► TECHNICAL INFORMATION

SYSTEM CONTROL & MONITORING	FP HEADER SECURITY	1x Header for Reset button, HDD LED, Power button, Power LED Recovery BIOS, System and BIOS Password, Boot Sequence Control for each drive, Serial Port Access Protection, Boot Sector Virus Warning, Write Protection for Flash BIOS, Harddisk Password incl. "Silent Password" option (no keyboard entry required)
COOLING	FAN	2x PWM Fan (CPU/System) 1x Fanless Heatsink, up to 10 W TDP (optional) 1x Fanless Heatpipe Cooler, up to 15 W TDP (optional)
SOFTWARE	OS SUPPORT	MS Windows XP32, 7-32, 7-64, 10-64 Linux-32, 64
MECHANICAL	DIMENSIONS (L x W)	Mini-ITX 6,7" x 6,7" (170 x 170 mm)
CERTIFICATION	EMC & SAFETY	CE; cTÜVus acc. IEC62368-1 (CSA/UL compliance), CB (TUEV-NCB), FCC-B verified

► MOTHERBOARD VERSIONS

	PROCESSOR	GRAPHICS	MEMORY	DISPLAY OPTIONS
D3313-S1 eKabini	GX-210HA 1.0 GHz Dual Core	Radeon™ HD 8210E 300 MHz	DDR3 / 1333 ⁱ⁾	1x DVI-I max. 1920 x 1200 1x DP V1.2 max. 3840 x 2160 1x LVDS 24Bit Dual Channel max. 1920 x 1200 max. 2 independent displays (DVI-I & DP or DVI-I & LVDS) Supports DirectX11 / DirectX11.1


i) DDR3-1600 modules useable

► POWER SUPPLY REQUIREMENTS

SOURCE	VOLTAGE	MIN. PS LOAD
DC-In (auto range)	12V +/- 10 % or 19-24 V +10 % / -15 %	5 A (external connector) 8 A (internal connector) ^A

A) See TechNotes document for power supply details

CONNECTOR / SOCKET DIAGRAM



TECHNICAL INFORMATION

FEATURES

Board Size: Mini-ITX: 6.7" x 6.7" (170 x 170 mm)
VGA* / DVI / DisplayPort / LVDS / HDMI*
Stereo Audio / Multich. Audio / Buzzer / int. Speaker Support
Dual LAN Gbit / 100 Mbit / 10 Mbit
LAN ASF / AoL / WoL / Boot / DASH Support
SATA / ATA / RAID / mSATA
FireWire™ / USB 2.0 / USB 3.1 Gen1
FAN monitored & controlled CPU / AUX1 / AUX2
TEMP monitored CPU / onboard Sensors / external Sensors

+
+ / + / + / + / +
+ / - / + / -
+ / + / +
- / - / + / + / -
+ / - / - / +
- / + / +
+ / + / -
+ / + / -

SPECIAL FEATURES

Silent Fan / System Guard / Silent Drives
Recovery BIOS / Desk Update / Multi Boot
HDD Password / HW Diagnostic Tool / EraseDisk / TPM
Boot Logo Option
HW Watchdog: BIOS POST WD / BIOS Boot WD / OS WD
Operating Mode 24-7 / 8-5 (hrs per day - days per week)
Motherboard operating temperature range (chassis inside)

+ / + / +
+ / + / +
+ / + / + / -
+
- / + / +
+ / -
0 °C – 60 °C

INTERNAL CONNECTORS

DIMM Sockets (DDR3 1333/1600/1866, SO-DIMM)
PCI Express® x4 Slot (Gen2) / PCI Slot (32Bit, 33 MHz)
Mini PCI Express® Slot (incl.USB 2.0) / Socket for TPM 1.2 module
SATA (600) / ATA / Floppy / CF Card / mSATA (600)
Frontpanel HD Audio (9-Pin "Azalia")** / SPDIF OUT
USB 2.0 channels / USB 3.1 Gen1 channels
Specific socket for internal USB stick (USB 2.0)
Serial Port (COM3) / Parallel Port (LPT)
FAN*** CPU / System (AUX1) / System (AUX2)
SMBus (Case Temperature) / Intrusion (Case Open)
LVDS Dual Channel / Backlight Inverter
Feature Connector (8 Bit General Purpose I/O)
Frontpanel (Power Switch, LEDs, Intel 10 pin header)
Onboard Power Output (+5 V/2 A, +12 V/2 A) for drives
Onboard (internal input) DC-In 12 V / 19-24 V @ 8 A max.

2
1 / -
1 / 1
2 / - / - / - / 1
1 / 1
2 / 2
1
1 / 1
1 / 1 / -
- / 1
1 / 1
1
1
1
1

EXTERNAL CONNECTORS

VGA Sub D* / DVI-I / HDMI* / DisplayPort
Audio In / Line out (or driver configuration)
LAN (RJ-45)
PS/2 Mouse / Keyboard
USB 2.0 / USB 3.1 Gen1
Serial (RS232, FIFO, 16550 compatible)
DC-IN (external input) 12 V/19-24 V @ 5 A max.

- / 1 / - / 1
1 / 1
2
1 / 1
4 / -
2
1

*) Via optional DVI-I / VGA interface connector resp. DVI-I / HDMI interface connector
**) Support for AC'97 audio frontpanel possible via BIOS Setup option
***) CPU fan = 4 pin PWM, system fan = 4 pin PWM or 3 pin (selectable via BIOS Setup)

► ORDERING INFORMATION

ARTICLE	PART NO.	DESCRIPTION
D3313-S1 mITX	F5120-V98	AMD embedded G-Series SOC, AMD Dual-Core GX-210HA (1.0 GHz/9 W)
ACCESSORIES		
FANLESS HEATSINK (9 W) + BACKPLATE	F5000-C006	For D3313-S1
RISERCARD 1X PCIE X4	F5000-R006	D3318
SERIAL PORT CABLE	F5000-K005	400 mm, full size slot bracket
MINI PCIE TO M.2 ADAPTER	F5000-M003	D3436-S
AC ADAPTER	F5000-P006	19 V/65 W
DRIVE POWER CABLE	F5000-K001	For SATA HDD/SATA slimline DVD
SMARTCASE™ S710	F5000-J002	Chassis Kit
FANLESS HEATPIPE COOLER (15 W) + BACKPLATE	F5000-C007	For D3313-S1

► GLOBAL HEADQUARTERS

Kontron Europe GmbH

Gutenbergstraße 2
85737 Ismaning, Germany
Tel.: +49 821 4086-0
Fax: +49 821 4086-111
info@kontron.com

www.kontron.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kontron:](#)

[S26361-F5120-V104](#) [S26361-F5120-V130](#) [S26361-F5120-V98](#)