


SLE210K

Dust Proof



Miniature Power Rocker Switches

C-US UL

SEMKO

RoHS Compliant


Features

1. C-US UL and SEMKO approved products
2. Snap-in panel mounting
3. Compact size is suited for space-saving design.
4. Best suited for power supply of equipment.
5. Dust-proof type
6. 100 A rush current type.
7. Breaking distance is 3 mm or over.

Specifications

Rating	Load	Inductive load				Resistive load
	Inrush current (p.f.=0.6)	125VAC		250VAC		10A 125VAC 10A
		100A	60A	100A	60A	250VAC (p.f.=1.0)
	Break current (p.f.=0.9)	10A	10A	10A	10A	
	Min.	10mA 5VAC/DC				(Resistive load)
	C-US UL	125VAC 6A /250VAC 6A				(Resistive load)
Initial contact resistance		20mΩ max.				(1A 1~2VDC)
Initial dielectric strength		1500VAC 1 minute				
Initial insulation resistance		100MΩ min.				(500VDC)
Electrical life (cycles)		5,000	10,000	5,000	10,000	10,000
Operating force		3.92~12.7N				
Operating temperature range		-25~+85℃				
Strage temperature range		-40~+85℃				

Part Numbering



★ [Blue box] : The combination marked in blue brackets shows made-to-order products.

Marking Color

Frame color•Rocker color	Making color
Black	White

Handling Precautions

1. Soldering Specifications

(1) Manual Soldering



Device : Soldering iron
380℃, Max.; 3 seconds, Max.

※The tab terminals cannot be soldered.

Table of Part Numbers



Frame color and rocker color	Marking color	Switching function	Terminal styles					
				Part number and rating marking side				
Black	White	ON-OFF	Solder terminal	☆SLE210K	★SLE210K-5	SLE210K-6	★SLE210K-7	SLE210K-9
			#187 TAB	SLE210K2	SLE210K2-5	SLE210K2-6	SLE210K2-7	SLE210K2-9
			Right Angle Terminal	★SLE210K4	—	☆SLE210K4-6	★SLE210K4-7	—
			Left Angle Terminal	—	★SLE210K9-5	—	★SLE210K9-7	★SLE210K9-9
			Vertical Mounting Terminal	—	—	★SLE210K11-6	—	—

Solder terminal




Part No.	Switching function	
	Viewed from part No. & rating marking side	
SLE210K		
	ON	OFF
Connecting terminals	2-3 5-6	—


TAB#187 Terminal



Right Angle Terminal





PC Hole Layouts (Top view)




The blue lines show the outline of the switch.

Left Angle Terminal



PC Hole Layouts (Top view)




The blue lines show the outline of the switch.

☆ : Semi-standard products.


★ : Made to order products.

● Terminal numbers are shown on the bottom of the switch.

Vertical Mounting Terminal



Switch Guard **Dedicated for use of rocker switches**



Features

Clear visibility and one-touch mounting to save labor

Application

Best suited for protection of malfunction of miniature rocker switches (panel cutout: 19.2 x 12.9mm)

Specifications


Part Name: Switch guard
Part Number: 140007250027
Color: Black (transparent cover)

※The switch guard cannot be used for the SLE10K series, SLE210K right angle terminal, and SLE210K left angle terminal.


Approvals

UL File No.E43275
SEMKO File No. SE-S-2002358

Packaging Specification




Panel Cut-Out Dimensions



■Precautions for Panel

The edges on the back of the cut-out panel should be squared so that the switch box bites the panel firmly. When the panel is coated, pay attention that the coating will not retain around the edge. Do not reuse the switch that was once mounted on a panel.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nidec:

[SLE210K2-5](#) [SLE210K2-7](#) [SLE210K4-6](#) [SLE210K4-7](#) [SLE210K-5](#) [SLE210K-7](#) [SLE210K2-6](#)