



MANUAL SETTING TYPE OPTICAL ENCODERS **REC16/RES16**

FEATURES

- High resistant to electrostatic noise by using a plastic shaft
- Compact size of 16 mm square
- With mechanical ON/OFF push switch
- Long life
- RoHS compliant



PART NUMBER DESIGNATION



LIST OF PART NUMBERS

Test item	Click	Push switch function	Snap-in holder	Part number
Resolution				
25 (P/R)	With Click	Yes	No	REC16A25-201
			Yes	REC16A25-201-C
	Without Click	No	No	REC16B25-201
			Yes	REC16B25-201-C
			No	RES16B25-201
			Yes	RES16B25-201-C
50 (P/R)	With Click	Yes	No	REC16A50-201
			Yes	REC16A50-201-C
	Without Click	No	No	REC16B50-201
			Yes	REC16B50-201-C
			No	RES16B50-201
			Yes	RES16B50-201-C

REC16/RES16

OPTICAL ENCODERS

STANDARD SPECIFICATIONS

Electrical characteristics

Input voltage		DC5 V ± 5 %
Input current		30 mA maximum
Output wave form		Square wave
Output phases		A, B
Resolution(P/R)		25, 50
Phase difference of outputs A & B		100 μsec minimum Refer to "OUTPUT"
Maximum frequency response		100 Hz
Output signal	“1 (High)”	+ 4.5 V minimum
	“0 (Low)”	+ 0.5 V maximum
Light source		LED
Output Sink Current		3 mA maximum

Switch characteristics

Maximum contact rating	DC15 V, 20 mA
Contact resistance	200 m Ω maximum (Initial value)

Note) Manual setting only.

Environmental characteristics

Operating temp. range	0 $\sim$ 50 $^{\circ}$ C
Storage temp. range	- 20 $\sim$ 80 $^{\circ}$ C
Protection grade	IP40

Mechanical characteristics

Starting torque		1.18 mN·m ± 0.78 maximum (12 ± 8 gf·cm) 〈RES : Without click〉
Click torque		Please refer to Table 1 below 〈REC : With click〉
Click number		25, 50
Shaft loading (Pull-push)		19.6 N maximum (2 kgf)
Switch operation force		7.85 N ± 2.94 N (800 ± 300 gf)
Switch stroke		0.5 mm
Rotational life (Mechanical)		1 million cycles
Shaft loading (When mounting)	Radial	4.90 N maximum (500 gf)
	Axial	2.94 N maximum (300 gf)
Net weight		Approx. 10 g
Strength of tighten screw		1 N·m {10.2 kgf·cm} maximum


<Click torque>

[Table 1]


Part number	Click torque	
	mN·m	gf·cm
REC16A25	6.87 $\pm$ 3.43	70 $\pm$ 35
REC16B25	6.87 $\pm$ 3.43	70 $\pm$ 35
REC16A50	4.91 $\pm$ 1.77	50 $\pm$ 18
REC16B50	3.43 $\pm$ 1.77	35 $\pm$ 18

OUTPUT

Click spot for 25P/R



Click spot for 50P/R



REC16/RES16

OPTICAL ENCODERS

RELIABILITY TEST


The output shall satisfy the criteria below after the following tests.

Test item		Test conditions	
Vibration	Power OFF	Amplitude : 1.52 mm or 98.1 m/s ² (10 G) whichever is smaller. 10 ~ 500 Hz excursion 15 min/cycle, 8 cycles each for X, Z, directions.	
Shock	Power OFF	3 times each in directions (X, Z) at 490 m/s ² (50 G), 11 ms.	
High temperature exposure	Power OFF	80 °C 96 h	To be measured after leaving samples for 1 h at normal temperature and humidity after the test.
	Power ON	50 °C 96 h	
Low temperature exposure	Power OFF	– 20 °C 96 h	
	Power ON	0 °C 96 h	
Humidity	Power OFF	To be measured after wiping out moisture and leaving samples for 1 h at normal temperature and humidity after the test.	
Thermal shock	Power OFF	To be done 10 cycles with the following condition (To be measured after leaving samples for 1 h at normal temperature and humidity after the test.) 80 °C 0.5 h、 – 20 °C 0.5 h	

OUTLINE DIMENSIONS

Unless otherwise specified, tolerance: ± 0.4(Unit: mm)

- Without snap-in holder
REC16A25-201, REC16B25-201, RES16B25-201
REC16A50-201, REC16B50-201, RES16B50-201



※ Connector : A4B-6PA-2DSA
Made by Hirose Electric Co., Ltd.

REC16/RES16

OPTICAL ENCODERS


OUTLINE DIMENSIONS

Unless otherwise specified, tolerance: ± 0.4 (Unit: mm)

With snap-in holder




REC16A25-201-C, REC16B25-201-C, RES16B25-201-C

REC16A50-201-C, REC16B50-201-C, RES16B50-201-C



※ Connector : A4B-6PA-2DSA
Made by Hirose Electric Co., Ltd.


<Accessories>



PIN ASSIGNMENT

Pin No.	With switch	Without switch
1	Power 0 (V)	Power 0 (V)
2	Output "B"	Output "B"
3	For switch	N C
4	For switch	N C
5	Power $\oplus$	Power $\oplus$
6	Output "A"	Output "A"

OUTPUT CIRCUIT



REC16/RES16

OPTICAL ENCODERS

● KNOB FOR SETTING ENCODERS


The knobs are sold separately as an optional item.

You can choose gray or black color.

The hexagon socket head screws are attached. (2 pieces)



Unless otherwise specified, tolerance: ± 0.4 (Unit: mm)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Nidec:](#)

[RES16B50-201-C](#)