





© 2024 PennEngineering

ALL DIMENSIONS IN INCHES

DATE 18-MAR-2024

NOTE : DRAWING NOT TO SCALE

THREAD : .190-32 (#10-32)	MOUNTING HOLE DIA. : .344 +.003 -.000
MATERIAL: 300 Series Stainless Steel	PANEL THICKNESS: .305 MINIMUM
HEAT TREAT: NONE	MAX. PANEL HARDNESS: HRB 70 / HB 125 OR LESS
FINISH: Passivated and/or tested per ASTM A360	MIN CENTERLINE-TO-EDGE: 0.272
DESCRIPTION : PEM® CASTSERT™ Press-in Inserts - Unified	 EMAIL: TECHSUPPORT@PEMNET.COM WWW.PEMNET.COM
PART NO. : CKS-032-1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PEM:](#)

[CKS-032-1](#)