



© 2024 PennEngineering

ALL DIMENSIONS IN INCHES

DATE 18-MAR-2024

NOTE : DRAWING NOT TO SCALE

THREAD :	.086-56 (#2-56)	MOUNTING HOLE DIA. :	.188 +.003 -.000
MATERIAL:	300 Series Stainless Steel	PANEL THICKNESS:	.255 MINIMUM
HEAT TREAT:	NONE	MAX. PANEL HARDNESS:	HRB 70 / HB 125 OR LESS
FINISH:	Passivated and/or tested per ASTM A360	MIN CENTERLINE-TO-EDGE:	0.151

DESCRIPTION :
PEM® CASTSERT™ Press-in Inserts - Unified

PART NO. :
CKS-256-2



PennEngineering®

EMAIL: TECHSUPPORT@PEMNET.COM
WWW.PEMNET.COM

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PEM:](#)

[CKS-256-2](#)