



Laird's unique Phantom antenna operates simultaneously in the 806-896 MHz, 1850-1990 MHz, and 2500-2700 MHz bands. The mechanically robust design is suitable for both indoor and outdoor applications. With wide bandwidth and a low angle radiation pattern that is superior to traditional gain antennas in most applications, the antenna can be used in both ceiling mount and surface mount applications.

The industry standard NMO mounting socket mates with all Laird magnetic, trunk lid, and hole mount configurations. A threaded permanent stud mount model is also available for vandal resistant mounting on brackets, panels, ceilings, or any other type of housing.

## FEATURES AND BENEFITS

- Mechanically-robust for both indoor and outdoor applications
- Suitable for high band 4G applications
- Phantom antenna outperforms a 3-dBi whip in many applications.

## ELECTRICAL SPECIFICATIONS

Operating Frequency (MHz)	806-896	1850-1990	2500-2700
Peak Gain (dBi)	4.0	3.5	3.0
Efficiency – avg (%)	89	73	77
Efficiency – max (%)	93	74	82
VSWR (max)	2.0:1		
Return Loss (dB) – max	-10		
Polarization	Vertical		
Pattern	Omnidirectional		
Nominal Impedance (Ohms)	50		
Max Power - Ambient 25°C (W)	100		

## MECHANICAL SPECIFICATIONS

Dimensions – diameter x height – cm (inches)	3.65 x 8.38 (1.44 x 3.3)
Color	Black or white available
Radome Material	SABIC Lexan
Cable and Mount	MB195 (sold separately)

## ENVIRONMENTAL SPECIFICATIONS

Operating Temperature – °C (°F)	-40 to +85°C (-40 to +185°F)
---------------------------------	------------------------------

## CONFIGURATION


PART NUMBER	COLOR RADOME	HEIGHT	WEIGHT CONNECTOR
TRA8063M3NB-001	Black	8.4 cm (3.3 in.)	0.15 lbs NMO
TRA8063M3PB-001	Black	8.4 cm (3.3 in.)	0.25 lbs N Female
TRA8063M3NW-001	White	8.4 cm (3.3 in.)	0.15 lbs NMO
TRA8063M3PW-001	White	8.4 cm (3.3 in.)	0.25 lbs N Female

**Permanent Mounting Options:** The letter "P" in the above part numbers indicates a permanent mounting option


## RADIATION PATTERN

### Azimuth


850 MHz



1920 MHz




2700 MHz




### Elevation


850 MHz



1920 MHz



2700 MHz



Laird warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations Laird will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the Laird product is installed. Useful lifetime of the original end product may vary but is not to exceed five (5) years from the original date of the end product purchase.

Any information furnished by Laird Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird materials rests with the end user, since Laird and its agents cannot be aware of all potential uses. Laird makes no warranties as to the fitness, merchantability or suitability of any Laird materials or products for any specific or general uses. Laird shall not be liable for incidental or consequential damages of any kind. All Laird products are sold pursuant to the Laird Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request.

© Copyright 2019 Laird Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Logo, and other marks are trademarks or registered trademarks of Laird Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird or any third party intellectual property rights.

sales@lairdconnect.com  
support@lairdconnect.com  
www.lairdconnect.com



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Laird Connectivity:

[TRA8063M3NW-001](#) [TRA8063M3NB-001](#) [TRA8063M3PB-001](#) [TRA8063M3PW-001](#)