

# MOSFET – N-Channel, SUPERFET III, FRFET

**650 V, 30 A, 110 mΩ**

**NTB110N65S3HF**

## Description

SUPERFET III MOSFET is onsemi's brand-new high voltage super-junction (SJ) MOSFET family that is utilizing charge balance technology for outstanding low on-resistance and lower gate charge performance. This advanced technology is tailored to minimize conduction loss, provide superior switching performance, and withstand extreme dv/dt rate.

Consequently, SUPERFET III MOSFET is very suitable for the various power systems for miniaturization and higher efficiency.

SUPERFET III FRFET MOSFET's optimized reverse recovery performance of body diode can remove additional component and improve system reliability.


## Features

- 700 V @  $T_J = 150^\circ\text{C}$
- Typ.  $R_{DS(on)} = 98\text{ m}\Omega$
- Ultra Low Gate Charge (Typ.  $Q_g = 62\text{ nC}$ )
- Low Effective Output Capacitance (Typ.  $C_{oss(eff.)} = 522\text{ pF}$ )
- 100% Avalanche Tested
- These Devices are Pb-Free and are RoHS Compliant


## Applications

- Telecom / Server Power Supplies
- Industrial Power Supplies
- EV Charger
- UPS / Solar

| $V_{DS}$ | $R_{DS(on)}$ MAX | $I_D$ MAX |
|----------|------------------|-----------|
| 650 V    | 110 mΩ @ 10 V    | 30 A      |




N-CHANNEL MOSFET



D<sup>2</sup>PAK  
(TO-263 3-Lead)  
CASE 418AJ

## MARKING DIAGRAM



|               |                           |
|---------------|---------------------------|
| \$Y           | = onsemi Logo             |
| &Z            | = Assembly Plant Code     |
| &3            | = Data Code (Year & Week) |
| &K            | = Lot                     |
| NTB110N65S3HF | = Specific Device Code    |

## ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

# NTB110N65S3HF

## ABSOLUTE MAXIMUM RATINGS (T<sub>C</sub> = 25°C, Unless otherwise noted)

| Symbol                            | Parameter                                                            |                                        | Value       | Unit |
|-----------------------------------|----------------------------------------------------------------------|----------------------------------------|-------------|------|
| V <sub>DSS</sub>                  | Drain to Source Voltage                                              |                                        | 650         | V    |
| V <sub>GSS</sub>                  | Gate to Source Voltage                                               | – DC                                   | ±30         | V    |
|                                   |                                                                      | – AC (f > 1 Hz)                        | ±30         |      |
| I <sub>D</sub>                    | Drain Current                                                        | – Continuous (T <sub>C</sub> = 25 °C)  | 30          | A    |
|                                   |                                                                      | – Continuous (T <sub>C</sub> = 100 °C) | 19.5        |      |
| I <sub>DM</sub>                   | Drain Current                                                        | – Pulsed (Note 1)                      | 69          | A    |
| E <sub>AS</sub>                   | Single Pulsed Avalanche Energy (Note 2)                              |                                        | 380         | mJ   |
| I <sub>AS</sub>                   | Avalanche Current (Note 2)                                           |                                        | 4.4         | A    |
| E <sub>AR</sub>                   | Repetitive Avalanche Energy (Note 1)                                 |                                        | 2.4         | mJ   |
| dv/dt                             | MOSFET dv/dt                                                         |                                        | 100         | V/ns |
|                                   | Peak Diode Recovery dv/dt (Note 3)                                   |                                        | 50          |      |
| P <sub>D</sub>                    | Power Dissipation                                                    | (T <sub>C</sub> = 25 °C)               | 240         | W    |
|                                   |                                                                      | – Derate Above 25 °C                   | 1.92        | W/°C |
| T <sub>J</sub> , T <sub>STG</sub> | Operating and Storage Temperature Range                              |                                        | –55 to +150 | °C   |
| T <sub>L</sub>                    | Maximum Lead Temperature for Soldering, 1/8" from Case for 5 seconds |                                        | 300         | °C   |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Repetitive rating: pulse-width limited by maximum junction temperature.

2. I<sub>AS</sub> = 4.4 A, R<sub>G</sub> = 25 Ω, starting T<sub>J</sub> = 25 °C.

3. I<sub>SD</sub> ≤ 15 A, di/dt ≤ 100 A/μs, V<sub>DD</sub> ≤ 400 V, starting T<sub>J</sub> = 25 °C.

## THERMAL CHARACTERISTICS

| Symbol           | Parameter                                     | Value | Unit |
|------------------|-----------------------------------------------|-------|------|
| R <sub>θJC</sub> | Thermal Resistance, Junction to Case, Max.    | 0.52  | °C/W |
| R <sub>θJA</sub> | Thermal Resistance, Junction to Ambient, Max. | 45    |      |

## PACKAGE MARKING AND ORDERING INFORMATION

| Part Number   | Top Marking   | Package            | Reel Size | Tape Width | Shipping <sup>†</sup> |
|---------------|---------------|--------------------|-----------|------------|-----------------------|
| NTB110N65S3HF | NTB110N65S3HF | D <sup>2</sup> PAK | 330 mm    | 24 mm      | 800 / Tape & Reel     |

<sup>†</sup> For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, [BRD8011/D](#).

# NTB110N65S3HF

## ELECTRICAL CHARACTERISTICS (T<sub>C</sub> = 25°C unless otherwise noted)

| Symbol | Parameter | Test Conditions | Min. | Typ. | Max. | Unit |
|--------|-----------|-----------------|------|------|------|------|
|--------|-----------|-----------------|------|------|------|------|

### OFF CHARACTERISTICS

|                                     |                                           |                                                                       |     |      |      |      |
|-------------------------------------|-------------------------------------------|-----------------------------------------------------------------------|-----|------|------|------|
| BV <sub>DSS</sub>                   | Drain to Source Breakdown Voltage         | V <sub>GS</sub> = 0 V, I <sub>D</sub> = 1 mA, T <sub>J</sub> = 25 °C  | 650 | –    | –    | V    |
|                                     |                                           | V <sub>GS</sub> = 0 V, I <sub>D</sub> = 1 mA, T <sub>J</sub> = 150 °C | 700 | –    | –    | V    |
| ΔBV <sub>DSS</sub> /ΔT <sub>J</sub> | Breakdown Voltage Temperature Coefficient | I <sub>D</sub> = 15 mA, Referenced to 25 °C                           | –   | 0.64 | –    | V/°C |
| I <sub>DSS</sub>                    | Zero Gate Voltage Drain Current           | V <sub>DS</sub> = 650 V, V <sub>GS</sub> = 0 V                        | –   | –    | 10   | μA   |
|                                     |                                           | V <sub>DS</sub> = 520 V, T <sub>C</sub> = 125 °C                      | –   | 97   | –    |      |
| I <sub>GSS</sub>                    | Gate to Body Leakage Current              | V <sub>GS</sub> = ±30 V, V <sub>DS</sub> = 0 V                        | –   | –    | ±100 | nA   |

### ON CHARACTERISTICS

|                     |                                      |                                                              |     |    |     |    |
|---------------------|--------------------------------------|--------------------------------------------------------------|-----|----|-----|----|
| V <sub>GS(th)</sub> | Gate Threshold Voltage               | V <sub>GS</sub> = V <sub>DS</sub> , I <sub>D</sub> = 0.74 mA | 3.0 | –  | 5.0 | V  |
| R <sub>DS(on)</sub> | Static Drain to Source On Resistance | V <sub>GS</sub> = 10 V, I <sub>D</sub> = 15 A                | –   | 98 | 110 | mΩ |
| g <sub>FS</sub>     | Forward Transconductance             | V <sub>DS</sub> = 20 V, I <sub>D</sub> = 15 A                | –   | 18 | –   | S  |

### DYNAMIC CHARACTERISTICS

|                        |                                   |                                                                                    |   |      |   |    |
|------------------------|-----------------------------------|------------------------------------------------------------------------------------|---|------|---|----|
| C <sub>iss</sub>       | Input Capacitance                 | V <sub>DS</sub> = 400 V, V <sub>GS</sub> = 0 V, f = 1 MHz                          | – | 2635 | – | pF |
| C <sub>oss</sub>       | Output Capacitance                |                                                                                    | – | 52   | – | pF |
| C <sub>oss(eff.)</sub> | Effective Output Capacitance      | V <sub>DS</sub> = 0 V to 400 V, V <sub>GS</sub> = 0 V                              | – | 522  | – | pF |
| C <sub>oss(er.)</sub>  | Energy Related Output Capacitance | V <sub>DS</sub> = 0 V to 400 V, V <sub>GS</sub> = 0 V                              | – | 91   | – | pF |
| Q <sub>g(tot)</sub>    | Total Gate Charge at 10 V         | V <sub>DS</sub> = 400 V, I <sub>D</sub> = 15 A, V <sub>GS</sub> = 10 V<br>(Note 4) | – | 62   | – | nC |
| Q <sub>gs</sub>        | Gate to Source Gate Charge        |                                                                                    | – | 18   | – | nC |
| Q <sub>gd</sub>        | Gate to Drain "Miller" Charge     |                                                                                    | – | 25   | – | nC |
| ESR                    | Equivalent Series Resistance      | f = 1 MHz                                                                          | – | 4.6  | – | Ω  |

### SWITCHING CHARACTERISTICS

|                     |                     |                                                                                                               |   |    |   |    |
|---------------------|---------------------|---------------------------------------------------------------------------------------------------------------|---|----|---|----|
| t <sub>d(on)</sub>  | Turn-On Delay Time  | V <sub>DD</sub> = 400 V, I <sub>D</sub> = 15 A,<br>V <sub>GS</sub> = 10 V, R <sub>g</sub> = 4.7 Ω<br>(Note 4) | – | 24 | – | ns |
| t <sub>r</sub>      | Turn-On Rise Time   |                                                                                                               | – | 25 | – | ns |
| t <sub>d(off)</sub> | Turn-Off Delay Time |                                                                                                               | – | 85 | – | ns |
| t <sub>f</sub>      | Turn-Off Fall Time  |                                                                                                               | – | 25 | – | ns |

### SOURCE-DRAIN DIODE CHARACTERISTICS

|                 |                                                          |                                                                                  |   |     |     |    |
|-----------------|----------------------------------------------------------|----------------------------------------------------------------------------------|---|-----|-----|----|
| I <sub>S</sub>  | Maximum Continuous Source to Drain Diode Forward Current |                                                                                  | – | –   | 30  | A  |
| I <sub>SM</sub> | Maximum Pulsed Source to Drain Diode Forward Current     |                                                                                  | – | –   | 69  | A  |
| V <sub>SD</sub> | Source to Drain Diode Forward Voltage                    | V <sub>GS</sub> = 0 V, I <sub>SD</sub> = 15 A                                    | – | –   | 1.3 | V  |
| t <sub>rr</sub> | Reverse Recovery Time                                    | V <sub>GS</sub> = 0 V, I <sub>SD</sub> = 15 A,<br>dI <sub>F</sub> /dt = 100 A/μs | – | 95  | –   | ns |
| Q <sub>rr</sub> | Reverse Recovery Charge                                  |                                                                                  | – | 371 | –   | nC |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Essentially independent of operating temperature typical characteristics.

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance Variation vs. Drain Current and Gate Voltage




Figure 4. Body Diode Forward Voltage Variation vs. Source Current and Temperature




Figure 5. Capacitance Characteristics




Figure 6. Gate Charge Characteristics

TYPICAL PERFORMANCE CHARACTERISTICS (CONTINUED)




Figure 7. Breakdown Voltage Variation vs. Temperature




Figure 8. On-Resistance Variant vs. Temperature




Figure 9. Maximum Safe Operation Area




Figure 10. Maximum Drain Current vs. Case Temperature




Figure 11.  $E_{OSS}$  vs. Drain to Source Voltage

TYPICAL PERFORMANCE CHARACTERISTICS (CONTINUED)




Figure 12. Transient Thermal Response Curve




Figure 13. Gate Charge Test Circuit & Waveform




Figure 14. Resistive Switching Test Circuit & Waveforms




Figure 15. Unclamped Inductive Switching Test Circuit & Waveforms

# NTB110N65S3HF





Figure 16. Peak Diode Recovery  $dv/dt$  Test Circuit & Waveforms

## NTB110N65S3HF

### REVISION HISTORY

| Revision | Description of Changes                            | Date      |
|----------|---------------------------------------------------|-----------|
| 1        | Rebranded the Data Sheet to <b>onsemi</b> format. | 6/26/2025 |


This document has undergone updates prior to the inclusion of this revision history table. The changes tracked here only reflect updates made on the noted approval dates.



SCALE 1:1


**D<sup>2</sup>PAK-3 (TO-263, 3-LEAD)**  
CASE 418AJ  
ISSUE F

DATE 11 MAR 2021



**RECOMMENDED  
MOUNTING FOOTPRINT**

For additional information on our Pb-free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.





0.100 BSC 0.100 BSC


**NOTES:**

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
2. CONTROLLING DIMENSION: INCHES
3. CHAMFER OPTIONAL.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.005 PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY AT DATUM H.
5. THERMAL PAD CONTOUR IS OPTIONAL WITHIN DIMENSIONS E, L1, D1, AND E1.
6. OPTIONAL MOLD FEATURE.
7. ①, ② ... OPTIONAL CONSTRUCTION FEATURE CALL OUTS.


| DIM | INCHES    |       | MILLIMETERS |       |
|-----|-----------|-------|-------------|-------|
|     | MIN.      | MAX.  | MIN.        | MAX.  |
| A   | 0.160     | 0.190 | 4.06        | 4.83  |
| A1  | 0.000     | 0.010 | 0.00        | 0.25  |
| b   | 0.020     | 0.039 | 0.51        | 0.99  |
| c   | 0.012     | 0.029 | 0.30        | 0.74  |
| c2  | 0.045     | 0.065 | 1.14        | 1.65  |
| D   | 0.330     | 0.380 | 8.38        | 9.65  |
| D1  | 0.260     | ---   | 6.60        | ---   |
| E   | 0.380     | 0.420 | 9.65        | 10.67 |
| E1  | 0.245     | ---   | 6.22        | ---   |
| e   | 0.100 BSC | ---   | 2.54 BSC    | ---   |
| H   | 0.575     | 0.625 | 14.60       | 15.88 |
| L   | 0.070     | 0.110 | 1.78        | 2.79  |
| L1  | ---       | 0.066 | ---         | 1.68  |
| L2  | ---       | 0.070 | ---         | 1.78  |
| L3  | 0.010 BSC | ---   | 0.25 BSC    | ---   |
| M   | 0°        | 8°    | 0°          | 8°    |



DETAIL C  
TIP LEADFORM  
ROTATED 90° CW




VIEW A-A




VIEW A-A  
OPTIONAL CONSTRUCTIONS

**GENERIC MARKING DIAGRAMS\***




IC



Standard



Rectifier



SSG

XXXXXX = Specific Device Code  
A = Assembly Location  
WL = Wafer Lot  
Y = Year  
WW = Work Week  
W = Week Code (SSG)  
M = Month Code (SSG)  
G = Pb-Free Package  
AKA = Polarity Indicator

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

|                         |                                            |                                                                                                                                                                                  |
|-------------------------|--------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98AON56370E</b>                         | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>D<sup>2</sup>PAK-3 (TO-263, 3-LEAD)</b> | <b>PAGE 1 OF 1</b>                                                                                                                                                               |

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)