







IMPEDANCE (Z)			
Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	126 Ω	240 Ω	362 Ω
Minimum	- Ω	192 Ω	- Ω




FERRITE CORE DIMENSIONS (SPEC):mm [Inches]

A	12.00 [.472]	+	0.30 [.012]
B	5.60 [.220]	+	0.30 [.012]
C	25.00 [.984]	+	0.50 [.020]

WEIGHT/1000: 10.80 kgs 23.81 Lbs.

NOTES: UNLESS OTHERWISE SPECIFIED

1. COSMETIC SPECIFICATION REFER TO WI-QA-038.



DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
REV	DESCRIPTION	DATE	INT				
A	NEW RELEASE	05/07/2018	Jcai	PROJECT/PART NUMBER: 28B0470-200 DATE: 05/07/2018 SCALE: 2.5:1 CAD # 28B0470-200-A TOOL # B0470			
REV	DESCRIPTION	DATE	INT				
				REV	PART TYPE: FERRITE CORE	DRAWN BY: Jcai	MATERIAL: Ferrite

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[28B0470-200](#)