







IMPEDANCE (Z)			
Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	54 Ω	120 Ω	232 Ω
Minimum	- Ω	96 Ω	- Ω

Z vs. FREQUENCY
(REF. ONLY)



FREQUENCY (MHz)

AGILENT E4991A Impedance/Material Analyzer
HP 16092A Test Fixture REF #3188


FERRITE CORE DIMENSIONS (SPEC): mm/inches

A	15.88 [.625]	±	0.30 [.012]
B	7.87 [.310]	±	0.30 [.012]
C	10.00 [.394]	±	0.40 [.016]

WEIGHT/1000 7.23 kgs [15.94 Lbs]

NOTES:

1. COSMETIC SPECIFICATION REFER TO WI-QA-038.



DIMENSIONS ARE IN mm[INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
				PROJECT/PART NUMBER: 28B0625-300			
				DATE: 01/24/19	SCALE: 2 : 1	MATERIAL: FERRITE	
A	NEW RELEASE	01/24/19	Jcai	CAD # 28B0625-300-A	TOOL # B0625		
REV	DESCRIPTION	DATE	INT				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[28B0625-300](#)