



SECTION A-A

DETAIL "A"



DETAIL "A"
(TYP.)

SCALE DRAWING 1:1



28N0525-600

ELECTRICAL TESTING

TEST:	NET Z	NET Z
# TURNS	1	1
AWG	—	—
FREQUENCY	25 MHz	100 MHz
NOMINAL	59 Ω	91 Ω
MINIMUM	—	72 Ω
WEIGHT/K	10.09 KGS	


NOTES: UNLESS OTHERWISE SPECIFIED

1. COSMETIC SPECIFICATION REFER TO WI-QA-038.



CORE DIMENSIONS:

A	13.34 [.525]	±	0.38 [.015]
B	7.49 [.295]	±	0.38 [.015]
C	14.35 [.565]	±	0.40 [.016]
D	3.81 [.150]	±	0.13 [.005]
E	5.72 [.225]	±	0.25 [.010]

DIMENSIONS ARE IN mm [INCHES].				<p>This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.</p> 			
REV	DESCRIPTION	DATE	INT				
PROJECT/PART NUMBER:				28N0525-600		REV	PART TYPE:
DATE: 04/13/2020				CAD # 28N0525-600-A		A	BALUN
NEW RELEASE				04/13/2020		WS	DRAWN BY:
							WS
						SCALE: 2 : 1	MATERIAL:
						TOOL # N0525A	Ferrite

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[28N0525-600](#)