



RoHS



Z vs. FREQUENCY
(REF. ONLY)





FREQUENCY (MHz)

AGILENT E4991A Impedance/Material Analyzer
HP 16092A-Test Fixture


FERRITE CORE DIMENSIONS (SPEC): mm [in.]

A	45.09 [1.775]	+	0.90 [.035]
B	34.42 [1.355]	+	0.64 [.025]
C	28.58 [1.125]	+	0.64 [.025]
D	6.35 [.250]	+	0.25 [.010]
E	0.84 [.033]	+	0.25 [.010]
F	7.62 [.300]	+	-



NOTES: UNLESS OTHERWISE SPECIFIED

1. COSMETIC SPECIFICATION REFER TO WI-QA-038.



WEIGHT/1000 35.92 kgs. 79.18 Lbs.

DIMENSIONS ARE IN mm[INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
REV	DESCRIPTION	DATE	INT				
H	UPDATE LOGO	08/29/16	QIU	PROJECT/PART NUMBER: 28S2022-000			
G	CORRECT Z SPECS AT 25 MHZ	08/13/03	JRK				
F	UPDATE FORMAT & Z SPECS ADD CURVE	07/07/03	JRK				
E	UPDATE PRINT FOR ELECTRONIC DATABASE	11/06/00	JAJ				
D	UPDATED P/N FOR NEW CATALOG	09/27/95	JBE				
C	UPDATED IMPEDANCE SPECS	05/22/95	JBE	DATE:	12/15/94	SCALE:	1.5 : 1
B	STANDARD FORMAT	12/01/95	JBE	CAD #	28S2022-000-H	TOOL #	S2022
A	ORIGINAL DRAFT	12/15/94	JBE	SHEET: FERRITE			
REV	DESCRIPTION	DATE	INT				

Laird

REV H PART TYPE: CNZ SPLIT FERRITE CORE DRAWN BY: JBE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[28S2022-000](#)