



RoHS



IMPEDANCE (Z)			
Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	115 Ω	250 Ω	520 Ω
Minimum	- Ω	200 Ω	- Ω



FREQUENCY (MHz)
AGILENT E4991A Impedance/Material Analyzer
HP 16092A-Test Fixture


FERRITE CORE DIMENSIONS (SPEC): mm [in]

A	38.10 [1.500]	+	0.76 [.030]
B	26.67 [1.050]	+	0.76 [.030]
C	25.40 [1.000]	+	0.51 [.020]
D	6.35 [.250]	+	0.25 [.010]
E	0.84 [.033]	+	0.25 [.010]
F	7.62 [.300]	+	0.25 [.010]

WEIGHT/1000 30.56 kgs. 67.38 Lbs.

NOTES: UNLESS OTHERWISE SPECIFIED

1. COSMETIC SPECIFICATION REFER TO WI-QA-038.



DIMENSIONS ARE IN mm[INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
REV	DESCRIPTION	DATE	INT				
H	UPDATE LOGO	08/29/16	QIU	PROJECT/PART NUMBER: 28S2023-000			
G	UPDATE FORMAT & Z SPECS ADD CURVE CHANGE TOLS ON F DIMENSION	07/07/03	JRK				
F	CORRECT DIM F	07/16/01	JRK	REV H PART TYPE: FERRITE SPLIT RIBBON DRAWN BY: DJB			
E	UPDATE PRINT FOR ELECTRONIC DATABASE UPDATE Z SPECS & REMOVED NOTE "2"	11/09/00	JAJ				
D	ADDED GROSS ELECT. TEST & NOTES	04/03/97	BAC	DATE: 12/17/90 SCALE: 2 : 1 MATERIAL: FERRITE			
C	UPDATE P/N FOR NEW CATALOG	09/27/95	JBE				
B	UPDATE	11/04/94	JBE	TOOL # S2023			
A	ORIGINAL DRAFT	12/17/90	DJB				
REV	DESCRIPTION	DATE	INT	28S2023-000-H			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[28S2023-000](#)