

MHLL5040-000

PHYSICAL DIMENSIONS:



A	50.0[1.969]	$\frac{+}{-}$	0.50[.0197]
B	40.0[1.575]	$\frac{+}{-}$	0.50[.0197]
C	0.20[.008]	$\frac{+}{-}$	0.02[.0008]
D	0.35[.014]		MAX

RoHS

ELECTRICAL CHARACTERISTICS:

Initial Permeability(u') (13.56MHz)	130±20%
Initial Permeability(u'') (13.56MHz)	5 Max


PRODUCTS SHAPE AND DIMENSIONS



MEASURED BY ANGILENT E4991A , 1Ts .

NOTES: UNLESS OTHERWISE SPECIFIED

1. OPERATING TEMPERATURE RANGE -40°C TO 85°C .
2. FLEXIBLE FERRITE SHEET.
3. D IS MEASURED AFTER REMOVING PAPER LINER OF ADHESIVE

DIMENSIONS ARE IN mm [INCHES].				<p>This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.</p> <div></div>				
PROJECT/PART NUMBER:				REV	PART TYPE:	DRAWN BY:		
MHLL5040-000				C	CO-FIRE	QU		
B	CHANGE u' FROM 112~208	03/27/14	QU	DATE:	11/20/13	SCALE:	NTS	SHEET: 1 of 1
A	ORIGINAL DRAFT	11/20/13	QU	CAD #	MHI 15040-000-C	TOOL #	-	
REV	DESCRIPTION	DATE	INT					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[MHLL5040-000](#)