


NA12065-B00H

PHYSICAL DIMENSIONS:

A	120.0[4.724]	$\pm 0.50[.020]$
B	65.0[2.559]	$\pm 0.50[.020]$
C	0.05[0.003]	TYP.
D	0.19[0.007]	MAX.

PRODUCTS SHAPE AND DIMENSIONS




ELECTRICAL CHARACTERISTICS:

Initial Permeability(μ')
(128KHz)

1400 $\pm$ 20%

Complex permeability vs. Frequency



MEASURED BY ANGILENT E4991A , 1Ts .

NOTES: UNLESS OTHERWISE SPECIFIED

1. OPERATING TEMPERATURE RANGE -40°C TO 125°C .
2. CORE MATERIAL: NANOCRYSTALLINE, -40°C TO 200°C
3. ADHESIVE MATERIAL: 3M 467MP, -40°C TO 125°C
4. COVER TAPE MATERIAL: POLYIMIDE, -40°C TO 125°C
5. ALL MATERIAL MEET RoHS & HF REQUIREMENT
6. MEET UL94-V0 BASE ON LAIRD INTERNAL TEST
ACCORDING TO UL94 VERTICAL BURN TEST STANDARD

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
				PROJECT/PART NUMBER:	NA12065-B00H	REV	A
				DATE:	01/12/2023	SCALE:	NTS
				CAD #	NA12065-B00H-A	TOOL #	-
						SHEET:	1 of 1
A	NEW RELEASE	01/12/23	YC				
REV	DESCRIPTION	DATE	INT				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[NA12065-B00H](#)