

Tgard[™] 20 Thermally Conductive Insulators



LOW COST, MEDIUM PERFORMANCE INSULATOR MATERIAL

The Tgard[™] 20 is designed to solve over heating issues such as lower component efficiency, premature component failures, size limitations and other performance problems for today's computer power supplies.

The Tgard[™] 20 is a film-based product designed to resist cut through in screw mounting applications while providing a more consistent breakdown voltage over other insulator constructions.

The phase change coating on the film core provides an excellent mating surface for low pressure clip mounting applications.

PERFORMANCE CAPABILITIES

- High dielectric breakdown of 9,000 volts
- Film base resistance cut through
- Thermal resistance of 0.60°C-in²/ watt @ 25 psi pressure

FEATURES AND BENEFITS

- Reinforced with moderate temperature resistant film
- High voltage resistant film
- Total thermal resistance of 3.4°C/watt on TO-220
- Non-blocking for ease of use
- Designed for computer power supplies

APPLICATIONS

- Switching mode power supplies for:
- Computers
- Consumer electronics
- UPS units

global solutions: local support ...

Americas: +1.800.843.4556 Europe: +49.8031.2460.0 Asia: +86.755.2714.1166

CLV-customerservice@lairdtech.com www.lairdtech.com/thermal



Tgard[™] 20 Thermally Conductive Insulators

PROPERTY	TEST METHOD	METRIC VALUES	IMPERIAL VALUES	
ELECTRICAL PROPERTIES				
Dielectric Withstand Voltage	ASTM D149	4,500 volts DC	4,500 volts DC	
Dielectric Breakdown Voltage	ASTM D149	>9,000 volts AC	>9,000 volts AC	
Volume Resistivity	ASTM D257	>10 ¹² ohm-cm	>10 ¹² ohm-in	
Dielectric Constant @ 1 MHz	ASTM D257	1,8	1.8	
MECHANICAL PROPERTIES				
Thickness		0,076 mm	0.003 inch	
Substrate Film Thickness		0,051 mm	0.002 inch	
Tensile Strength	ASTM D412	138 MPa	20 kpsi	
Elongation	ASTM D412	130%	130%	
Operating Temperature Range		-40 - 150°C	-40 - 302°F	
Color		White	White	
UL Flammability Rating	UL 94	V0	V0	

PRESSURE, PSI (KPA)	UNITS	10 (69)	25 (172)	50 (345)	100 (689)	200 (1379)
TOTAL THERMAL RESISTA	NCE					
Modified ASTM D5470	°C-in²/watt	0.65	0.60	0.60	0.60	0.60
Modified ASTM D5470	°C-cm²/watt	4,2	3,9	3,9	3,9	3,9
TO-220	°C/watt	3.8	3.4	3.4	3.4	3.4
STANDARD THICKNESS: STANDARD ROLL SIZE: 3 mils (0,076 mm) 12" x 300' (304 mm x 91 meters)			IE-CUT PART tandard and onfigurations	S: custom available		

Data for design engineer guidance only. Observed performance varies in application. Engineers are reminded to test the material in application.

THR-DS-TGARD-20 032515

Any information furnished by Laird Technologies, Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Technologies materials rests with the end user, since Laird Technologies and its agents cannot be aware of all potential uses. Laird Technologies makes no warranties as to the fitness, merchantability or suitability of any Laird Technologies materials or products for any specific or general uses. Laird Technologies shall not be liable for incidental or consequential damages of any kind. All Laird Technologies, Inc. All Right Reserved. Laird, Laird Technologies, the Laird Technologies, to consequential technologies, or any fitting compart there of Chine product or service names may be the property of third parties. Nothing herein provides a license under any Laird Technologies or any third party intellectual property rights. A15561-00 REV 8, 7/02/09

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Laird Performance Materials:

A15557-01A15559-03A15433107A15428107A15037007A15434007A15436007A15435007A15427007A15434107A15437007A15432007A15436107A15432107A15440107A15430007A15441107A15435107A15431007A15428007A15431107A15038007A15036107A15441007A15437107A15036007A15427107A15433007A15430107A15037107A15037107A15037107A15037107A15037107A15037107