



TYS4020220M-10

PHYSICAL DIMENSIONS:

A	4.00	± 0.20
B	4.00	± 0.20
C	2.00	MAX.
D	1.20	± 0.30
E	1.60	± 0.30





RECOMMENDED SOLDERING CONDITIONS



ELECTRICAL SPECIFICATION


	Min	Nom	Max
INDUCTANCE (uH) L @ 100 KHz/1V ± 20%	17.6	22.0	26.4
DCR (Ω)		0.350	0.455

Saturation Current(A)	1.05
SRF (MHz)	15
Temperature Rise Current (A)	0.62




RoHS

CHARACTERISTICS OF TEMPERATURE RISE



CURRENT VS INDUCTANCE DROP IN RATES



NOTES: UNLESS OTHERWISE SPECIFIED

1. OPERATING TEMPERATURE RANGE: -40°C TO +125°C (INCLUDING SELF-HEATING) .
2. STORAGE TEMPERATURE RANGE (PACKAGING CONDITIONS): -10°C TO +40°C AND RH 70% (MAX.)
3. UNLESS OTHERWISE SPECIFIED, THE STANDARD ATMOSPHERIC CONDITIONS FOR MEASUREMENT/TEST AS:
A. AMBIENT TEMPERATURE: 20±15°C.
B. RELATIVE HUMIDITY: 65%±20%.
4. DEFINITION OF SATURATION CURRENT (ISAT): DC CURRENT AT WHICH THE INDUCTANCE DROPS ≤30% FROM ITS VALUE WITHOUT CURRENT.
5. DEFINITION OF TEMPERATURE RISE CURRENT (IRMS): DC CURRENT THAT CAUSES THE TEMPERATURE RISE (ΔT ≤40°C) FROM 20°C AMBIENT.

DIMENSIONS ARE IN mm .				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
				PROJECT/PART NUMBER: TYS4020220M-10			
C	CHANGE DIMENSIONS: D/E	01/11/18	QIU	DATE: 09/06/12	SCALE: NTS	SHEET: 1 of 1	
B	CHANGE LOGO	08/06/15	QIU				
A	ORIGINAL DRAFT	09/06/12	QIU				
REV	DESCRIPTION	DATE	INT	TYS4020220M-10-C			

Laird

PART TYPE: POWER INDUCTOR
DRAWN BY: QIU

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[TYS4020220M-10](#)