TYS4020330M-10

PHYSICAL DIMENSIONS:


 $A 4.00 \pm 0.20$

 $B 4.00 \pm 0.20$


C 2.00 MAX.


 $D 1.20 \pm 0.30$

 $E 1.60 \pm 0.30$




LAND PATTERNS FOR REFLOW SOLDERING









CHARACTERISTICS OF TEMPERATURE RISE



CURRENT VS INDUCTANCE DROP IN RATES



RECOMMENDED SOLDERING CONDITIONS



ELECTRICAL SPECIFICATION

	Min	Nom	Max		
INDUCTANCE (uH) L @ 100 KHz/1V ± 20%	26.4	33.0	39.6		
DCR (Ω)		0.550	0.715		

Saturation Current(A)	0.85
SRF (MHz)	11
Temperature Rise Current (A)	0.49

NOTES: UNLESS OTHERWISE SPECIFIED

1.OPERATING TEMPERATURE RANGE: -40°C TO +125°C (INCLUDING SELF-HEATING) .

2.STORAGE TEMPERATURE RANGE (PACKAGING CONDITIONS): -10°C TO +40°C AND RH 70% (MAX.)

3.UNLESS OTHERWISE SPECIFIED, THE STANDARD ATMOSPHERIC CONDITIONS FOR MEASUREMENT/TEST AS: A. AMBIENT TEMPERATURE: 20±15°C.

B. RELATIVE HUMIDITY: 65%±20%.

4.DEFINITION OF SATURATION CURRENT (ISAT): DC CURRENT AT WHICH THE INDUCTANCE DROPS ≤30% FROM ITS VALUE WITHOUT CURRENT.

5.DEFINITION OF TEMPERATURE RISE CURRENT (IRMS): DC CURRENT THAT CAUSES THE TEMPERATURE RISE ($\Delta \text{T} \leq 40\,^{\circ}\text{C}$) FROM 20 $^{\circ}\text{C}$ AMBIENT.

		DIMENSIONS ARE IN mm . This print is the property of Laird								
					Tech. and is loaned in confidence subject to return upon request ar		_!	=	J.	
					with the understanding that no copies shall be made without the		Laird			
ı					written consent of Laird Tech. All					
ı					rights to design or invention are reserved.					
					PROJECT/PART NUMBER:	REV	PART TYP	PE:	DRAWN BY:	
ı	С	CHANGE DIMENSIONS: D/E	01/11/18	QIU	TYS4020330M-10	С	POW		QIU	
	В	CHANGE LOGO	08/06/15	QIU	DATE: 00 /06 /40 SC	CALE: NTS		SHEET:	<u> </u>	
	Α	ORIGINAL DRAFT	09/06/12	QIU	O9/06/12					
	REV	DESCRIPTION	DATE	INT	TYS4020330M-10-C	,	-	1	of 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Laird Performance Materials:

TYS4020330M-10