


HI1812V101R-10

PHYSICAL DIMENSIONS:

A	4.50 [.177]	$\pm$ 0.25 [.010]
B	3.20 [.126]	$\pm$ 0.25 [.010]
C	2.30 [.091]	$\pm$ 0.25 [.010]
D	0.65 [.026]	$\pm$ 0.45 [.018]





ELECTRICAL CHARACTERISTICS:


Z @ 100MHz (Ω)	DCR (Ω)	Rated Current
Nominal	100	
Minimum	75	
Maximum	125	0.007 8000 mA

NOTES: UNLESS OTHERWISE SPECIFIED

1. TAPED AND REELED per CURRENT EIA SPECIFICATIONS 13" REELS, 2500 PCS/REEL.
2. TERMINATION FINISH IS 100% TIN.
3. COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.
4. OPERATEING TEMPERATURE TEMP: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$ (INCLUDING SELF-HEATING)




LAND PATTERNS FOR REFLOW SOLDERING



(For wave soldering, add 0.762 [.030] to this dimension)

RECOMMENDED SOLDERING CONDITIONS



DIMENSIONS ARE IN mm [INCHES]				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
D	ADD OPERATING TEMPERATURE UPDATE LAIRD LOGO AND REFLOW CURVE	08/05/13	QU	PROJECT/PART NUMBER: HI1812V101R-10			
C	UPDATE THE DCR AND D	11/06/09	JUN	REV	D	PART TYPE:	CO-FIRE
B	UPDATE COMPANY LOGO, ADD ROHS SYMBOL	01/23/08	JRK	DATE:	04/02/04	SCALE:	—
A	ORIGINAL DRAFT	04/02/04	TMB	CAD #	—	SHEET:	1 of 1
REV	DESCRIPTION	DATE	INT	HI1812V101R-10-D			

Laird

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[HI1812V101R-10](#)