




HZ0603A102R-10


PHYSICAL DIMENSIONS:

A	1.60 [.063]	+ 0.15	[.006]
B	0.80 [.031]	+ 0.15	[.006]
C	0.80 [.031]	+ 0.15	[.006]
D	0.36 [.014]	+ 0.15	[.006]



AGILENT E4991A RF Impedance/Material Analyzer
HP 16092A Test Fixture.

LAND PATTERNS FOR REFLOW SOLDERING



(For wave soldering, add 0.762
[0.030] to this dimension)

RoHS


ELECTRICAL CHARACTERISTICS:

Z @ 100MHz (Ω)	DCR (Ω)	Rated Current
Nominal	1000	
Minimum	750	
Maximum	1250	0.60
		190 mA

NOTES: UNLESS OTHERWISE SPECIFIED

1. TAPED AND REELED per CURRENT EIA SPECIFICATIONS 7" REELS, 4000 PCS/REEL.
2. PREHEATED BEFORE SOLDERING.
3. COMPONENTS SHOULD BE ADEQUATELY
4. THE OPERATEING TEMPERATURE: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$.

RECOMMENDED SOLDERING CONDITIONS



DIMENSIONS ARE IN mm [INCHES]				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.	
PROJECT/PART NUMBER: HZ0603A102R-10				REV A	PART TYPE: CO-FIRE
DATE: 03/01/11				SCALE: -	SHEET: 1 of 1
REV A	DESCRIPTION ORIGINAL DRAFT	DATE 03/01/11	QU QU	TOOL # -	

Laird

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[HZ0603A102R-10](#)