




LI0402E600R-10

PHYSICAL DIMENSIONS:

A	1.01 [.040]	$\pm$	0.18 [.007]
B	0.50 [.020]	$\pm$	0.20 [.008]
C	0.50 [.020]	$\pm$	0.20 [.008]
D	0.30 [.012]		MAX.




AGILENT E4991A RF Impedance/Material Analyzer
HP 16194A Test Fixture. TEST REF. 3235

ELECTRICAL CHARACTERISTICS:			
Z @ 100MHz (Ω)	DCR (Ω)	Rated Current	
Nominal	60		
Minimum	45		
Maximum	75	0.30	500 mA

NOTES: UNLESS OTHERWISE SPECIFIED


1. TAPED AND REELED per CURRENT EIA SPECIFICATIONS 7" REELS, 10,000 PCS/REEL, PAPER TAPE.
2. TERMINATION FINISH IS 100% TIN.
3. COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.
4. OPERATING TEMP. RANGE: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$. (INCLUDING SELF-HEATING)

LAND PATTERNS FOR REFLOW SOLDERING



(For wave soldering, add 0.763 [.030] to this dimension.)

RECOMMENDED SOLDERING CONDITIONS



RoHS

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
D	ADD OPERATING TEMPERATURE UPDATE LAIRD LOGO AND REFLOW CURVE	08/05/13	QU	PROJECT/PART NUMBER: LI0402E600R-10			
C	UPDATE COMPANY LOGO	07/09/08	JRK				
B	CHG REEL QTY FROM 4000, ADD PAPER TAPE TO NOTE #1, ADD ROHS SYMBOL	11/14/07	JRK	DATE	04/05/04	SCALE	NTS
A	ORIGINAL DRAFT	04/05/04	TMB	CD #	LI0402E600R-10-D	TOOL #	-
REV	DESCRIPTION	DATE	INT	SHEET: 1 of 1			

Laird

REV D PART TYPE: CO-FIRE DRAWN BY: TMB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[LI0402E600R-10](#)