



MGV201610R47M-10

PHYSICAL DIMENSIONS:

A	2.00	±	0.20
B	1.60	±	0.20
C	1.00		Max.
D	0.50	±	0.30


LAND PATTERNS FOR REFLOW SOLDERING



ELECTRICAL SPECIFICATION @ 25°C

	Min	Norm	Max
INDUCTANCE (uH) L @ 1MHz/1mA ±20%	0.376	0.47	0.564
DCR (Ω)		0.033	0.040
Saturation Current Isat (A)		4.40	4.00
Heating Current Irms (A)		3.50	3.15

RoHS



NOTES:

1. OPERATING TEMPERATURE RANGE: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$.
2. STORAGE TEMPERATURE RANGE: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$.
3. Isat MEANS THAT MAX DC CURRENT WILL CAUSE APPROXIMATELY 30% INDUCTANCE REDUCTION FROM INITIAL VALUE.
4. Irms MEANS THAT MAX DC CURRENT WILL CAUSE COIL TEMPERATURE RISE APPROXIMATELY 40°C AT AMBIENT $25 \pm 5^{\circ}\text{C}$.

DIMENSIONS ARE IN mm.				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved. Laird			
PROJECT/PART NUMBER:				REV	PART TYPE:	DRAWN BY:	
MGV201610R47M-10				A	CHOKE INDUCTOR	QIU	
DATE: 06/13/17				SCALE:	NTS		SHEET:
A	ORIGINAL DRAFT	06/13/17	QIU	CAD #	TOOL # -		1 of 1
REV	DESCRIPTION	DATE	INT	MGV201610R47M-10-A			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Laird Performance Materials:

[MGV201610R47M-10](#)