


MI0805M221R-10

PHYSICAL DIMENSIONS:

A	2.00 [.079]	+ 0.20 [.008]
B	1.25 [.049]	+ 0.20 [.008]
C	0.90 [.035]	+ 0.20 [.008]
D	0.51 [.020]	+ 0.25 [.010]




ELECTRICAL CHARACTERISTICS:

	Z @ 100MHz (Ω)	DCR (Ω)	Rated Current
Nominal	220		
Minimum	165		
Maximum	275	0.05	2500 mA


NOTES: UNLESS OTHERWISE SPECIFIED

1. TAPED AND REELED per CURRENT EIA SPECIFICATIONS 7" REELS, 4000 PCS/REEL, PAPER TAPE.
2. TERMINATION FINISH IS 100% TIN.
3. COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.
4. OPERATING TEMP. RANGE: $-55^{\circ}\text{C} \sim +125^{\circ}\text{C}$. (INCLUDING SELF-HEATING)
5. COSMETIC SPECIFICATION REFER TO WI-QA-124.


Z vs. FREQUENCY
IMPEDANCE UNDER DC BIAS



|Z|, R, AND XL vs. FREQUENCY




LAND PATTERNS FOR REFLOW SOLDERING



(For wave soldering, add 0.762 [.030] to this dimension)

RECOMMENDED SOLDERING CONDITIONS



DIMENSIONS ARE IN mm [INCHES].

This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.

Laird

E	CHANGE NOTE 4	01/16/18	QIU	PROJECT/PART NUMBER:	MI0805M221R-10	REV	E	PART TYPE:	CO-FIRE	DRAWN BY:	TMB
D	ADD OPERATING TEMPERATURE	08/05/13	QU	DATE:	04/05/04	SCALE:	-	SHEET:	1 of 1		
C	UPDATE LAIRD LOGO AND REFLOW CURVE	03/04/10	JRK	CAD #	MI0805M221R-10-E	TOOL #	-				
B	CHANGE TO PAPER TAPE	8/20/08	JRK								
A	UPDATE COMPANY LOGO ADD ROHS	04/05/04	TMB								
REV	ORIGINAL DRAFT	DATE	INT								
	DESCRIPTION										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[MI0805M221R-10](#)