

## Nextreme™ Performance Chiller

The Nextreme NRC2400 Recirculating Chiller features premium components and environmentally friendly refrigerants in a user-friendly design. It is designed to cool well below ambient and dissipate heat away from thermally sensitive equipment. Featuring variable speed motors for the compressor and condensing fan, the Nextreme NRC2400 offers a high coefficient of performance and low-noise operation. The Nextreme NRC2400 comes with several standard features and additional options allow for application-specific configurations. Power cord is **not** supplied with the unit and **must be ordered separately**.




## Features

- Reliable Performance
- Environmentally Friendly
- User-Friendly
- Application Specific Configurations

## Applications

- Industrial Lasers
- Additive Manufacturing
- Electron Microscopes
- Semiconductor Fabrication
- Laboratory Testing



## Cooling Power Operating Points

### 100% Water (20°C Ambient Air)

Cooling Power (Qc) = 2,800 Watts  
Fluid Setpoint = 20 °C  
Fluid ΔT @ 15.0 L/min = 2.7 °C

### 100% Water (30°C Ambient Air)




Cooling Power (Qc) = 2,600 Watts  
Fluid Setpoint = 20 °C  
Fluid ΔT @ 15.0 L/min = 2.5 °C

### 60/40 Water-Glycol (20°C Ambient Air)

Cooling Power (Qc) = 2,650 Watts  
Fluid Setpoint = 20 °C  
Fluid ΔT @ 15.0 L/min = 2.8 °C

### 60/40 Water-Glycol (30°C Ambient Air)

Cooling Power (Qc) = 2,450 Watts  
Fluid Setpoint = 20 °C  
Fluid ΔT @ 15.0 L/min = 2.6 °C



Technical Specifications

Performance

Nominal Cooling Capacity <sup>1</sup>	2,800 W
Setpoint Range	-10°C to 40°C
Temperature Stability <sup>3</sup>	±0.10°C
Nominal Operating Flowrate (60 Hz) <sup>1</sup>	15.0 L/min @ 2.6 Bar
Nominal Operating Flowrate (50 Hz) <sup>1</sup>	15.0 L/min @ 1.5 Bar
Refrigerant	R 513A
Sound Pressure Level at Nominal Cooling Capacity (50 Hz) <sup>1</sup>	65 dBA
Sound Pressure Level at Nominal Cooling Capacity (60 Hz) <sup>1</sup>	66 dBA

Operation

Coolant	Water or Water/Glycol
Operating Temperature <sup>2</sup>	15°C to 40°C
Storage temperature range (w/o coolant)	-25°C to 70°C
Humidity range	30% to 80%
Storage Humidity range	5% to 95%, non-condensing
Altitude	< 2,000 meters
Input Voltage	220 - 240 VAC
Frequency	50 / 60 Hz
Current	< 8.4 Amps
Maximum Forward Pressure	4.1 Bar
Compliance	ANSI / UL / CSA / IEC EN 61010-1 Edition 3

Physical

Height	750 mm
Length	520 mm
Width	480 mm
Weight	54 kg
Coolant Capacity	5 Liters
Couplings	1/2 in NPT

Standard Features

Variable Speed Motors	Variable speed compressor and condensing fans for quiet operation and improved energy efficiency.
Semi-Closed Fluid System	Sealed fluid system with breathable reservoir cap (similar to an automobile). This prevents evaporative losses, introduction of bacteria, and the need for components to prevent fluid from draining back into the system when installed below the application.
Optical Fluid Level Switch	Fluid level sensing with no moving parts.
RS-232 Communications	Complete control integration of chiller into higher level assembly control system.
Supply Pressure Sensing	Pressure sensing for applications sensitive to high operating conditions.

Accessory Kits

Feature	Kit Part Number	Description
Flow Control Valve and Flow Sensing Kit	387004277	Externally installed valve for reducing the overall flow to the application. Full flow continues through the chiller to maintain high heat transfer rates and temperature stability. Flow meter for measuring coolant flow rate. Installed external to the chiller with both a local display and connectivity to chiller LCD display.
Water Filter Kit	387004279	Hot swappable, 5-micron water filter for filtering particulates from the coolant circuit.


## Cord Options

These power cords have been tested and validated on Nextreme devices.

Power cord is not supplied with the unit and must be ordered separately.

MFG Part Number	Plug Type	Standard	Style	Cable Length	Rating	Color	Connector
387005324	Universal	None	Flying Leads	2.0 m	250VAC, 16A* / 20A**	Black	C19

\* IEC \*\* UL



## Notes

Nominal capacity rating is given at a 20°C (68°F) setpoint, 20°C (68°F) ambient temperature, sea level. For ambient conditions outside this range, please contact Laird Thermal Systems. Typical for nominal capacity rating. Contact LTS applications engineering for application specific performance.

Any information furnished by Tark Thermal Solutions and its agents, whether in specifications, data sheets, product catalogues or otherwise, is believed to be (but is not warranted as being) accurate and reliable, is provided for information only and does not form part of any contract with Tark Thermal Solutions. All specifications are subject to change without notice. Tark Thermal Solutions assumes no responsibility and disclaims all liability for losses or damages resulting from use of or reliance on this information. All Tark products are sold subject to the Tark Thermal Solutions Terms and Conditions of sale (including Tark's limited warranty) in effect from time to time, a copy of which will be furnished upon request.

© Copyright 2025 Tark Thermal Solutions, Inc. All rights reserved.

Nextreme™ is a trademark of Tark Thermal Solutions, Inc. All other marks are owned by their respective owners.

Revision: 03 Date: 11-24-2024

Print Date: 05-12-2025

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Thermal Systems:](#)

[385911-015](#)