

Specification Sheet

Part Number: 110-80004

Tensions and provides clean, flush cuts for 50lb. to 250lb. cable ties, including wide strap ties.

Impact-resistant housing and durable components for extended service life.

Easy-to-adjust tension knob offers 33 different settings for precise, repeatable applications.

Advanced ergonomic design minimizes necessary hand force and “kickback” to reduce repetitive-motion injuries.



Article Number	110-80004
----------------	-----------

Type	EVO9HT
------	--------

Color	Black (BK) Red (RD)
-------	---------------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton's EVO 9 manual cable tie application tool combines durability, precision and control with unparalleled comfort. Manufactured with high-performance materials and components, the EVO 9 cuts cable ties with up to 250-lb tensile strength. Its innovative, ergonomic design minimizes the stress on hands and wrists and “kickback” that occur with traditional tools, reducing the risk of repetitive-motion injuries. The HT model offers high tension while the SP model features a smaller grip.
---------------------	--

Short Description	EVO 9HT High Tension Mechanical Hand Tool, Tension Range 27 lb to 116 lb, 1/pkg
Global Part Name	EVO9HT-MET/PL-BK/RD
Length L (Imperial)	7.5
Length L (Metric)	191
Width W (Imperial)	1.3
Width W (Metric)	33
Cable Ties	T120, T150, T250, T255, WS
Height H (Imperial)	5.3
Height H (Metric)	135
Cable Tie Width Max (Imperial)	0.5
Material	Metal (MET) Plastic (PL)
Material Shortcut	MET PL
UV Resistant (Yes/No)	No
Reach Compliant (Article 33)	No

ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8205599000

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)