


TO SNAP-FIT IN A  $.125 \pm .002$   
[3.18±0.05] DIA. HOLE, IN A  
.062 [1.57] THICK BOARD



TO SELF-THREAD INTO A #4 OR M3  
THREADED HOLE, WITH .063 [1.6]  
MINIMUM ENGAGEMENT



#### NOTES:

1. MATERIAL: NYLON 6/6 (RMS-01).
2. COLOR: NATURAL.

PART NO.	DIM. "A"
MSPMST-2-01	1/8 [3.2]
MSPMST-3-01	3/16 [4.8]
MSPMST-4-01	1/4 [6.4]
MSPMST-5-01	5/16 [7.9]
MSPMST-6-01	3/8 [9.5]
MSPMST-7-01	7/16 [11.1]
MSPMST-8-01	1/2 [12.7]
MSPMST-9-01	9/16 [14.3]
MSPMST-10-01	5/8 [15.9]

A	RELEASED FOR PRODUCTION	SM 08/10/04
R E V	DESCRIPTION	ENGR. DATE

TITLE:

MINI SUPPORT POST, MICRO, SELF-THREADING

CREATED USING SOLIDWORKS  TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC.=±1/64 ANG.=±1°	FILE #: MSPMST  SHEET: 1 OF 2  RE: RICHCO, INC.	DWN: SM/RT  DT: 06/30/04  RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060	APP: RT  CHKD: RDG  PRELIMINARY  PART #  SEE TABLE	PRINT TYPE  CA
---	---	--	--	-------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[MSPMST-2-01](#) [MSPMST-10-01](#) [MSPMST-3-01](#) [MSPMST-4-01](#) [MSPMST-5-01](#) [MSPMST-6-01](#) [MSPMST-7-01](#)  
[MSPMST-8-01](#) [MSPMST-9-01](#)