





PART NO.	HOLE DIAMETER	PANEL THICKNESS	HEAD DIAMETER "A"±.020	TO ACCOMMODATE BUNDLE DIA. "B" REF	OVERALL HEIGHT "C"±.010	"D"		
PGSB-0305	.189±.003 [4.8]	.063-.067 [1.6-1.7]	.26 [6.5]	.125 [3.2]	.24 [6]	.051 [1.3]		
PGSB-1	.250±.003 [6.35]	.062 [1.57] MAX	.312 [7.9]		.312 [7.9]	.063 [1.6]		
PGSB-2	.312±.003 [7.9]		.375 [9.5]	.187 [4.7]	.312 [7.9]	.063 [1.6]		
PGSB-3				.240 [6.1]	.237 [6]	.050 [1.27]		
PGSB-4	.375±.002 [9.5]	.031-.125 [0.8-3.2]	.468 [11.9]	.187 [4.7]	.406 [10.3]	.055 [1.4]		
PGSB-5				.250 [6.35]				
PGSB-0710	.394±.003 [10]	.031-.063 [0.8-1.6]	.472 [12]	.284 [7.2]	.260 [6.6]	.051 [1.3]		
PGSB-6	.437±.002 [11.1]	.031-.125 [0.8-3.2]	.531 [13.5]	.270 [6.85]	.406 [10.3]	.055 [1.4]		
PGSB-7				.312 [7.9]				
PGSB-8				.250 [6.35]				
PGSB-9	.468±.002 [11.9]	.062 [1.57] MAX	.578 [14.7]	.343 [8.7]	.250 [6.35]	.050 [1.27]		
PGSB-10	.500±.002 [12.7]	.031-.125 [0.8-3.2]		.250 [6.35]	.406 [10.3]	.063 [1.6]		
PGSB-11		.312 [7.9]						
PGSB-12		.062 [1.57] MAX	.562 [14.3]	.375 [9.5]	.250 [6.35]			
PGSB-1013	.512±.003 [13]	.031-.118 [0.8-3]	.591 [15]	.402 [10.2]	.354 [9]	.051 [1.3]		
PGSB-13	.531±.002 [13.5]	.062 [1.57] MAX	.593 [15.1]	.406 [10.3]	.250 [6.35]	.063 [1.6]		
PGSB-14	.562±.002 [14.3]	.031-.125 [0.8-3.2]	.656 [16.7]	.312 [7.9]	.406 [10.3]			
PGSB-15				.391 [9.9]				
PGSB-16				.437 [11.1]				
PGSB-17	.625±.002 [15.9]		.718 [18.2]	.250 [6.35]				
PGSB-18				.437 [11.1]				
PGSB-19								
PGSB-19		.062 [1.57] MAX	.703 [17.85]	.500 [12.7]	.250 [6.35]			
PGSB-1316	.630±.003 [16]	.055-.139 [1.4-3.5]	.709 [18]	.504 [12.8]	.413 [10.5]	.059 [1.5]		
PGSB-20	.687±.002 [17.5]	.031-.125 [0.8-3.2]	.781 [19.8]	.500 [12.7]	.406 [10.3]	.063 [1.6]		
PGSB-21				.562 [14.3]				
PGSB-1519	.748±.003 [19]	.039-.130 [1-3.3]	.854 [21.7]	.602 [15.3]	.433 [11]	.059 [1.5]		
PGSB-22	.750±.002 [19.1]	.031-.125 [0.8-3.2]	.843 [21.4]	.500 [12.7]	.406 [10.3]	.063 [1.6]		
PGSB-23				.562 [14.3]				
PGSB-24								
PGSB-24		.062 [1.57] MAX	.828 [21]	.625 [15.9]	.250 [6.35]			
PGSB-25	.781±.002 [19.8]		.859 [21.8]					
PGSB-1822	.866±.003 [22]	.035-.091 [0.9-2.3]	.976 [24.8]	.717 [18.2]	.453 [11.5]	.059 [1.5]		
PGSB-26	.875±.002 [22.2]	.031-.125 [0.8-3.2]	.953 [24.2]	.500 [12.7]		.063 [1.6]		
PGSB-27				.562 [14.3]				
PGSB-28				.625 [15.9]				
PGSB-29				.687 [17.45]				
PGSB-30		.062 [1.57] MAX	.937 [23.8]	.750 [19.1]	.250 [6.35]			
PGSB-31	1.000±.002 [25.4]	.031-.125 [0.8-3.2]	1.125 [28.6]	.766 [19.45]	.453 [11.5]			
PGSB-32	1.097±.004 [27.86]		1.218 [31]	.812 [20.6]				
PGSB-33				.875 [22.2]				
PGSB-34				.937 [23.8]				
PGSB-2428	1.102±.003 [28]	.039-.130 [1-3.3]	1.240 [31.5]	.945 [24]	.441 [11.2]	.059 [1.5]		
PGSB-2530	1.181±.003 [30]	.039-.122 [1-3.1]	1.319 [33.5]	.984 [25]	.453 [11.5]	.071 [1.8]		
PGSB-2634	1.347±.003 [34.2]	.039-.126 [1-3.2]	1.496 [38]	1.031 [26.2]		.059 [1.5]		
PGSB-35	1.250±.002 [31.75]	.031-.125 [0.8-3.2]	1.312 [33.3]	.937 [23.8]		.063 [1.6]		
PGSB-36	1.375±.002 [34.9]		1.468 [37.3]	1.000 [25.4]				
PGSB-37	1.500±.002 [38.1]		1.609 [40.9]	1.062 [27]				
PGSB-38				1.125 [28.6]				
PGSB-39				1.312 [33.3]				
PGSB-40	1.750±.002 [44.45]		1.875 [47.6]	1.375 [34.9]				
PGSB-41	2.000±.002 [50.8]		2.125 [54]	1.640 [41.7]				
PGSB-42				1.750 [44.5]				
PGSB-43	2.250±.003 [57.2]	.250 [6.35] MAX	2.480 [63]	1.850 [47]	.720 [18.2]			



- NOTES:
1. MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01)
2. COLOR: BLACK.
COLOR WHITE AVAILABLE BY SPECIAL ORDER ONLY.
3. PARTS MAY APPEAR WITH ONE OR TWO LOCKING MECHANISMS PER SIDE.

PGSB-42		2.000±.002 [50.8]	2.125 [54]		1.750 [44.5]		TITLE: SNAP BUSHINGS CLOSED																														
PGSB-43		2.250±.003 [57.2]	.250 [6.35] MAX		2.480 [63]	1.850 [47]					.720 [18.2]																										
<table><tr><td>G</td><td>SEE CO 200371 FOR CHANGES</td><td>SK</td><td>05/27/09</td></tr><tr><td>F</td><td>SEE CO 200338 FOR CHANGES</td><td>SK</td><td>03/12/09</td></tr><tr><td>E</td><td>SEE CO 200332 FOR CHANGES</td><td>SK</td><td>02/24/09</td></tr><tr><td>D</td><td>SEE CO 200323 FOR CHANGES</td><td>SK</td><td>02/10/09</td></tr><tr><td>REV.</td><td>DESCRIPTION</td><td>ENGR.</td><td>DATE</td></tr></table>								G	SEE CO 200371 FOR CHANGES	SK	05/27/09	F	SEE CO 200338 FOR CHANGES	SK	03/12/09	E	SEE CO 200332 FOR CHANGES	SK	02/24/09	D	SEE CO 200323 FOR CHANGES	SK	02/10/09	REV.	DESCRIPTION	ENGR.	DATE	CREATED USING SOLIDWORKS		FILE #: PGSB		DWN: SK		APP: SK		FINAL	
								G	SEE CO 200371 FOR CHANGES	SK	05/27/09																										
								F	SEE CO 200338 FOR CHANGES	SK	03/12/09																										
								E	SEE CO 200332 FOR CHANGES	SK	02/24/09																										
								D	SEE CO 200323 FOR CHANGES	SK	02/10/09																										
								REV.	DESCRIPTION	ENGR.	DATE																										
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC.=±1/64 ANG.=±1°		SHEET: 1 OF 1		SHEET SIZE: B		DT: 11/17/08		CHKD: SJ		PART #		PRINT TYPE																									
		RE: RICHCO, INC.				RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060				SEE TABLE		CA																									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[PGSB-41](#) [PGSB-3](#) [PGSB-5](#) [PGSB-0710](#) [PGSB-1013](#) [PGSB-1519](#) [PGSB-2428](#) [PGSB-2530](#) [PGSB-2634](#) [PGSB-43](#)