



NOTES:

1. BODY MATERIAL: NYLON 66 UL94 V-2 (RMS-01);
2. BODY COLOR: BLACK;
3. TAPE: 0.16[0.0063] THICK, DOUBLE SIDED ADHESIVE TAPE (RMS-414);
4. APPLICATION: RECOMMENDED MAX. CABLE THICKNESS 1.0MM, MAX. CABLE WIDTH 5.8MM;
5. ALTERNATE UNITS FOR REFERENCE ONLY.

A	RELEASED FOR PRODUCTION	J.T 12.01.10
R E V	DESCRIPTION	ENGR. DATE
FINAL		
PART #		PRINT TYPE
MCC-1-01A-BK		CA

TITLE:

MICRO CABLE CLAMP

CREATED USING SOLIDWORKS	FILE #: MCC	DWN: J.T	APP: J.T	FINAL	
TOLERANCES UNLESS NOTED	SHEET: 1 OF 1	SHEET SIZE: A	DT: 03.08.10	CHKD: A.F	PART #
0~6.0: ±0.2 6.01~18.0: ±0.3 18.01~30.0: ±0.4 ANG.=±1°	RE: RICHCO	RICHCO		WWW.RICHCO-INC.COM (+86) 592-6884500	MCC-1-01A-BK
					PRINT TYPE CA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[MCC-1-01A-BK](#)