


MATERIAL: NYLON 66 UL94 V-2 (RMS-01) COLOR: NATRUAL PART NO.	MATERIAL: NYLON 66 UL94 V-0 (RMS-19) COLOR: NATURAL PART NO.	"A"	"L"
PSE-3M-01	PSE-3M-19	3.0	6.9
PSE-4M-01	PSE-4M-19	4.0	7.9
PSE-5M-01	PSE-5M-19	5.0	8.9
PSE-6M-01	PSE-6M-19	6.0	9.9
PSE-7M-01	PSE-7M-19	7.0	10.9
PSE-7.3M-01	PSE-7.3M-19	7.3	11.2
PSE-8M-01	PSE-8M-19	8.0	11.9



DIMENSIONS	TOLERANCE
$\text{DIM} \leq 6.0$	± 0.2
$6.0 < \text{DIM} \leq 18.0$	± 0.3
$18 < \text{DIM} \leq 30$	± 0.4
$30 < \text{DIM} \leq 50$	± 0.5
$50 < \text{DIM} \leq 80$	± 0.6
$80 < \text{DIM} \leq 120$	± 0.8
$\text{DIM} > 120$	TBD

01	SEE CO220111 FOR CHANGES	J.T 07.06.12
A-B	SEE VERSION A-B	J.T 07.06.12
R E V	DESCRIPTION	ENGR. DATE

TITLE: CARD SPACER				DWG IN MM	
CREATED USING SOLIDWORKS TOLERANCES UNLESS NOTED DIM ±: SEE TABLE ANG. = ±1°	FILE #: PSE SHEET: 1 OF 1 RE: RICHCO --	DWN: J.T DT: 07.06.12	APP: J.T CHKD: A.F	PART # SEE TABLE	PRINT TYPE CA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[PSE-4M-01](#) [PSE-4M-19](#) [PSE-6M-01](#) [PSE-6M-19](#) [PSE-7M-01](#) [PSE-7M-19](#) [PSE-8M-01](#) [PSE-8M-19](#)