


Specification Sheet

Part Number: T18RA50



Cable ties can be easily recycled to meet environmental management objectives.

HellermannTyton 18 lb. cable ties are available in natural, black, and other colors (upon request) to support color coded wire management schemes.

Bandoliers of 50 or reels of 5000 cable ties are available, enabling maximum user efficiency in hand-held, bench-mount, or automated processes.

Cable Tie for AT2000, 18lb Tensile Strength, PA66, Natural, 50/bandolier, 500/pkg

Article Number	120-05001
Type	T18RA50
Color	Natural (NA)
Quantity Per	pack
Product Description	HellermannTyton's AT2000 is designed to use 18 lb. cable ties and will fasten bundles up to 3/4" diameter. Engineered specifically for automatic cable tie assembly, these ties are offered in varying material compositions and colors, so manufacturers can select the ties that meet the application requirements and industry best practices.
Short Description	Cable Tie for AT2000, 18lb Tensile Strength, PA66, Natural, 50/bandolier, 500/pkg

Global Part Name	T18RA50-PA66-NA
------------------	-----------------

Minimum Tensile Strength (Imperial)	18
-------------------------------------	----

Minimum Tensile Strength (Metric)	80
-----------------------------------	----

Length L (Imperial)	4.0
---------------------	-----

Length L (Metric)	4.8
-------------------	-----

Variant	bandolier
---------	-----------

Width W (Imperial)	0.1
--------------------	-----

Width W (Metric)	2.5
------------------	-----

Bundle Diameter Min (Imperial)	0.03
--------------------------------	------

Bundle Diameter Min (Metric)	0.7
------------------------------	-----

Bundle Diameter Max (Imperial)	0.79
--------------------------------	------

Bundle Diameter Max (Metric)	20.0
------------------------------	------

Power supply unit	Electrical
-------------------	------------

Material	Polyamide 6.6 (PA66)
----------	----------------------

Material Shortcut	PA66
-------------------	------

Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139 CAGE Code 53421
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com