

Specification Sheet

Part Number: MB20M4



For use with 18 through 50 pound cable ties to provide stability when securing bundles.

Low profile design offers use in space constrained areas.

Secures with a single screw providing quick installation.

Cable Tie Anchor Mount, 0.81 x .49", 0.193" Hole Dia, 0.18" Max Tie Width, PA66, Black, 1000/pkg

Article Number	151-00301
----------------	-----------

Type	MB2
------	-----

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton cable tie screw mounts are used with 18 through 50 pound cable ties to provide stability when securing bundles. The low profile design allows for use in space constrained areas. The mounts are installed quick and easy by securing a single screw.
---------------------	---

Short Description	Cable Tie Anchor Mount, 0.81 x .49", 0.193" Hole Dia, 0.18" Max Tie Width, PA66, Black, 1000/pkg
-------------------	--

Global Part Name	MB2-PA66-BK
------------------	-------------

Length L (Imperial)	0.81
Length L (Metric)	20.6
Fixation Method	Screw Mount
Width W (Imperial)	0.49
Width W (Metric)	12.5
Cable Ties	T18 - T50
Height H (Imperial)	.13
Height H (Metric)	3.30
Cable Tie Width Max (Imperial)	0.18
Cable Tie Width Max (Metric)	4.6
Mounting Hole Diameter D (Imperial)	0.193 "
Mounting Hole Diameter D (Metric)	4.9 mm
Mounting Hole Diameter D Max (Metric)	4.9
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66

Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)