

Specification Sheet

Part Number: 553-50209

Slide Slit and optional center slits for easy wire insertion.

Smooth surface for clean and legible printing.

Supplied on a ladder style carrier so that markers can be kitted after printing.

A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.



ShrinkTrak Labels, 1-Sided, Unslit, 1.5" (38.1mm), PO-X, White 150/box

Article Number

553-50209

Type

HST39-13WH

Color

White (WH)

Quantity Per

pack

Product Description

HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.

Short Description

ShrinkTrak Labels, 1-Sided, Unslit, 1.5" (38.1mm), PO-X, White 150/box

Global Part Name	HST39-13WH-PO-X-WH
------------------	--------------------

Variant	Thin-Wall
---------	-----------

Width W (Imperial)	1.9
--------------------	-----

Width W (Metric)	48.26
------------------	-------

Thickness T (Imperial)	.003
------------------------	------

Thickness T (Metric)	.0762
----------------------	-------

Height H (Imperial)	2.26
---------------------	------

Height H (Metric)	57.4
-------------------	------

Width of Liner (Metric)	76.2
-------------------------	------

Width of Liner (Imperial)	3.0
---------------------------	-----

Outside Diameter OD (Imperial)	1.5
--------------------------------	-----

Outside Diameter OD (Metric)	38.1
------------------------------	------

Outside Diameter Max (Imperial)	1.5
---------------------------------	-----

Outside Diameter Max (Metric)	38.1
-------------------------------	------

Wall Thickness WT (Imperial)	0.04
------------------------------	------

Wall Thickness WT (Metric)	1.01
----------------------------	------

Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
US MIL SPEC	MIL-STD-202G Method 215K SAE-AS81531 SAE-AMS-DTL-23053/5 Class 1 and 3
Flammability	UL 224 VW-1
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-67°F to +275°F (-55°C to +135°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	SAE - AS81531 UL 224 125 °C 600V VW-1 SAE - AMS - DTL-23053/5 Class 1 and 3
Package Quantity (Imperial)	150
Package Quantity (Metric)	150
Customs Number	3917320000

Labels per Column	1
-------------------	---

Labels per Row	1
----------------	---

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)